



[Click Here to Request a Large Quantity Quote](#)

[3.3 to 9 Volt Table Top Switching Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
2289159	Globtek	GT21089-1005-T3	5	2	10	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CSA/TUV/CE	\$7.95
196218	Globtek	TR9CA2000C12CP-Y(R)	5	2	10	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CE	\$16.95
2235760	Globtek	GT-21089-1305	5	2.6	13	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/CCC/CE	\$7.95
2227815	Globtek	TR9CA2000LLP-Y-D	5	2.6	13	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CCC/CE	\$7.95
2256982	MEAN WELL	GST18A05-P1J	5	3	15	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.20
1940387	MEAN WELL	GS18A05-P1J	5	3	15	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$11.95
2270887	Arndt	SQ15W5P-10	5	3	15	NOT INCLUDED, RECOMMEND 2271583	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL	\$6.95
2292423	Globtek	GT-41062-1805-T3	5	3.4	17	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/CE/CCC	\$8.49
2257168	MEAN WELL	GST25A05-P1J	5	4	20	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.40

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
1940571	MEAN WELL	GS25A05-P1J	5	4	20	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.95
2227807	Sceptre Power	PS-5050APL05	5	5	25	INCLUDED	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CE	\$12.95
2224278	MEAN WELL	GST40A05-P1J	5	5	25	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$15.40
2224059	Sparkle Power	AD025DGAA1-J25	5	5	25	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CE	\$10.95
2234249	Arndt	FY0506000	5	6	30	INCLUDED	100 to 240	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CE/FCC	\$8.49
2224358	MEAN WELL	GST60A05-P1J	5	6	30	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$17.10
2144956	Jameco Reliapro	GQ65-060330-E1	6	3.3	19.8	NOT INCLUDED, RECOMMEND 1951123	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/TUV/CE	\$9.49
2257176	MEAN WELL	GST25A07-P1J	7.5	2.93	22	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.40
2257002	MEAN WELL	GST18A09-P1J	9	2	18	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.20
2257184	MEAN WELL	GST25A09-P1J	9	2.55	23	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$10.95
2257272	MEAN WELL	GST25B09-P1J	9	2.55	23	NOT INCLUDED, RECOMMEND 2271583	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$10.95
2224294	MEAN WELL	GST40A09-P1J	9	4.45	40	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.95

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
2224374	MEAN WELL	GST60A09-P1J	9	6	54	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$14.95