



[Click Here to Request a Large Quantity Quote](#)

[Multiple Output Table Top Switching Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
196270	Jameco Reliapro	PSU25A-13-R	5	2.5	25	INCLUDED	100 to 240	47 to 63	DIN Male	4-pin mini DIN	N/A	UL/CUL/CE	\$27.95
2230740	Jameco Reliapro	GPSN25A-13	5	2.5	30	INCLUDED	100 to 240	50 to 60	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CE	\$34.95
2229511	Ault	SC200	5	4	32	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	DIN Male	5-pin DIN	N/A	UL/CSA/TUV/CE	\$15.95
2250951	MEAN WELL	GP50A13D-R1B	5	4	50	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	DIN Male	5-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC	\$41.80