



[Click Here to Request a Large Quantity Quote](#)

[15 to 24 Volt Table Top Switching Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
2257029	MEAN WELL	GST18A15-P1J	15	1.2	18	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.20
2257117	MEAN WELL	GST18B15-P1J	15	1.2	18	NOT INCLUDED, RECOMMEND 2271583	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.20
2257205	MEAN WELL	GST25A15-P1J	15	1.66	25	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.40
1940619	MEAN WELL	GS25A15-P1J	15	1.66	25	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.95
2257299	MEAN WELL	GST25B15-P1J	15	1.66	25	NOT INCLUDED, RECOMMEND 2271583	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$10.95
2224315	MEAN WELL	GST40A15-P1J	15	2.67	40	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$15.40
2271223	Jameco Reliapro	G99-KPL060H-L035	15	4	60	NOT INCLUDED, RECOMMEND 2271575	100 to 240	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CE/FCC/CCC	\$13.95
2224391	MEAN WELL	GST60A15-P1J	15	4	60	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$17.10
1954295	MEAN WELL	GS60A15-P1J	15	4	60	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CE	\$14.95

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
2223478	MEAN WELL	GST90A15-P1M	15	6	90	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$28.10
2223591	MEAN WELL	GST120A15-R7B	15	7	105	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$41.00
2226433	MEAN WELL	GST160A15-R7B	15	9.6	144	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC	\$49.60
2226484	MEAN WELL	GST220A15-R7B	15	13.4	201	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$70.30
2226530	MEAN WELL	GST280A15-C6P	15	15	255	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	MOLEX 39-01-2060	6-Pin Molex	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$85.50
2257037	MEAN WELL	GST18A18-P1J	18	1	18	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$9.49
2257213	MEAN WELL	GST25A18-P1J	18	1.38	25	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$10.49
2257301	MEAN WELL	GST25B18-P1J	18	1.38	25	NOT INCLUDED, RECOMMEND 2271583	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.40
2292327	Arndt	PA1030-180T1A	18	1.67	30.06	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Stripped & Tinned	18 AWG SPT-1	N/A	UL/CUL/CE/FCC	\$8.95
2224323	MEAN WELL	GST40A18-P1J	18	2.22	40	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.95
2224403	MEAN WELL	GST60A18-P1J	18	3.33	60	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$17.10

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
2223486	MEAN WELL	GST90A19-P1M	19	4.74	90	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$28.10
2226548	MEAN WELL	GST280A20-C6P	20	20	260	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	MOLEX 39-01-2060	6-Pin Molex	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$85.50
2257045	MEAN WELL	GST18A24-P1J	24	0.75	18	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.20
1940635	MEAN WELL	GS25A24-P1JU	24	1.04	25	INCLUDED	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.95
2257221	MEAN WELL	GST25A24-P1J	24	1.04	25	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.40
2190346	MEAN WELL	GS25A24-P1J	24	1.04	25	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$10.95
2257379	MEAN WELL	GST36B24-P1J	24	1.5	36	NOT INCLUDED, RECOMMEND 2271583	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$14.10
2224331	MEAN WELL	GST40A24-P1J	24	1.67	40	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$15.40
230798	Globtek	TR9CI2100LCP-Y-MED-R	24	2.1	50.4	NOT INCLUDED, RECOMMEND 2271759	90 to 264	47 to 63	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CSA/TUV/CE	\$49.95
2229984	Jameco Reliapro	KPL-060M-2.1-VI	24	2.5	60	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CEC	\$13.95
2229992	Jameco Reliapro	KPL-060M-2.5-VI	24	2.5	60	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CEC	\$12.95
2224411	MEAN WELL	GST60A24-P1J	24	2.5	60	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$17.10

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
1952214	MEAN WELL	GS60A24-P1J	24	2.5	60	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CEC	\$16.25
2271311	Jameco Reliapro	GM95-240375-F	24	3.75	90	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CE/CCC	\$20.95
2223494	MEAN WELL	GST90A24-P1M	24	3.75	90	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$28.10
2271231	Jameco Reliapro	G99-ABU120M-N039	24	5	120	NOT INCLUDED, RECOMMEND 2271575	100 to 240	47 to 63	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CE/FCC/CCC	\$31.95
2223646	MEAN WELL	GST120A24-P1M	24	5	120	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$41.00
2223611	MEAN WELL	GST120A24-R7B	24	5	120	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$41.00
2226450	MEAN WELL	GST160A24-R7B	24	6.67	160	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC	\$49.60
2099286	MEAN WELL	GS220A24-R7B	24	9.2	220	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CE/PFC	\$57.95
2226505	MEAN WELL	GST220A24-R7B	24	9.2	221	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$70.30
2226556	MEAN WELL	GST280A24-C6P	24	24	280.08	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	MOLEX 39-01-2060	6-Pin Molex	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$85.50