



[Click Here to Request a Large Quantity Quote](#)

[27 to 54 Volt Table Top Switching Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
<a href="#">2257061</a>	MEAN WELL	GST18A48-P1J	48	0.375	18	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$12.20
<a href="#">2202562</a>	Phihong	PSA18U-480	48	0.38	18	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/CE/CCC	\$3.95
<a href="#">2230820</a>	Condor Power Supplies Inc.	CENB1050A4803F01	48	1.1	52.8	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Locking Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL	\$10.39
<a href="#">2224420</a>	MEAN WELL	GST60A48-P1J	48	1.25	60	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$17.10
<a href="#">2223507</a>	MEAN WELL	GST90A48-P1M	48	1.87	90	NOT INCLUDED, RECOMMEND 2271575	90 to 264	47 to 63	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$28.10
<a href="#">2271319</a>	Jameco Reliapro	GM95-480200-F	48	2	96	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/TUV/CE/CCC	\$19.95
<a href="#">2223620</a>	MEAN WELL	GST120A48-R7B	48	2.5	120	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$41.00

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
<a href="#">2226468</a>	MEAN WELL	GST160A48-R7B	48	3.34	160	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC	\$49.60
<a href="#">2226513</a>	MEAN WELL	GST220A48-R7B	48	4.6	221	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	DIN Male	4-pin DIN	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$70.30
<a href="#">2226564</a>	MEAN WELL	GST280A48-C6P	48	48	280.32	NOT INCLUDED, RECOMMEND 2271575	85 to 264	47 to 63	MOLEX 39-01-2060	6-Pin Molex	N/A	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$85.50
<a href="#">2273007</a>	Li Tone Electronics (LTE)	65E-S7-1	56	1.16	65	NOT INCLUDED, RECOMMEND 2271575	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CE/FCC	\$11.95