



[Click Here to Request a Large Quantity Quote](#)

12 to 14.3 Volt Table Top Switching Power Supplies

| Jameco Part # | Manufacturer | Manufacturer Part # | Primary Output Voltage (VDC) | Output Current (A) | Maximum Output Power (W) | AC Power Cord | Input Voltage (VAC) | Input Frequency | Output Connector Type | Output Connector Diameters | Polarity | Agency Approvals | Price 1 |
|-------------------------|------------------------|---------------------|------------------------------|--------------------|--------------------------|---------------------------------|---------------------|-----------------|-----------------------|----------------------------|-----------------|---------------------------------|---------|
| 2227823 | Globtek | TR9CE1250LCP-Y | 12 | 1.25 | 15 | NOT INCLUDED, RECOMMEND 2271575 | 100 to 240 | 50 to 60 | Cylindrical Female | 2.5mm x 5.5mm | Center Positive | UL/CUL/TUV/CCC/CE | \$12.95 |
| 1954244 | MEAN WELL | GS15A-3P1J | 12 | 1.25 | 15 | NOT INCLUDED, RECOMMEND 2271575 | 90 to 264 | 47 to 63 | Cylindrical Female | 2.1mm x 5.5mm right angle | Center Positive | UL/CUL/TUV/CB/CE/FCC/EN/EAC | \$15.00 |
| 2229491 | Dee Van Enterprise Usa | DSA-0151D-12-2.1 | 12 | 1.5 | 18 | NOT INCLUDED, RECOMMEND 2271575 | 100 to 125 | 50 to 60 | Cylindrical Female | 2.1mm x 5.5mm | Center Positive | UL/CSA/TUV/CE | \$7.49 |
| 2229482 | Dee Van Enterprise Usa | DSA-0151D-12-2.5 | 12 | 1.5 | 18 | NOT INCLUDED, RECOMMEND 2271575 | 100 to 125 | 50 to 60 | Cylindrical Female | 2.5mm x 5.5mm | Center Positive | UL/CSA/TUV/CE | \$8.95 |
| 2257011 | MEAN WELL | GST18A12-P1J | 12 | 1.5 | 18 | NOT INCLUDED, RECOMMEND 2271575 | 85 to 264 | 47 to 63 | Cylindrical Female | 2.1mm x 5.5mm | Center Positive | UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC | \$12.20 |
| 2270895 | Phihong | PSA18U-120 | 12 | 1.5 | 18 | NOT INCLUDED, RECOMMEND 2271583 | 100 to 240 | 50 to 60 | DIN Male | 4-Pin | N/A | UL/CUL/TUV/CE | \$8.95 |
| 2227381 | Delta Electronics | EADP-24MB | 12 | 2 | 24 | NOT INCLUDED, RECOMMEND 2271583 | 100 to 240 | 50 to 60 | Cylindrical Female | 2.5mm x 5.5mm | Center Positive | UL/CUL/CCC/CE | \$7.95 |
| 2257192 | MEAN WELL | GST25A12-P1J | 12 | 2.08 | 25 | NOT INCLUDED, RECOMMEND 2271575 | 85 to 264 | 47 to 63 | Cylindrical Female | 2.1mm x 5.5mm | Center Positive | UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC | \$12.40 |
| 2257361 | MEAN WELL | GST36B12-P1J | 12 | 3 | 36 | NOT INCLUDED, RECOMMEND 2271583 | 85 to 264 | 47 to 63 | Cylindrical Female | 2.1mm x 5.5mm | Center Positive | UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC | \$14.10 |

| Jameco Part # | Manufacturer | Manufacturer Part # | Primary Output Voltage (VDC) | Output Current (A) | Maximum Output Power (W) | AC Power Cord | Input Voltage (VAC) | Input Frequency | Output Connector Type | Output Connector Diameters | Polarity | Agency Approvals | Price 1 |
|-------------------------|---------------------|---------------------|------------------------------|--------------------|--------------------------|---------------------------------|---------------------|-----------------|-----------------------|----------------------------|-----------------|---------------------------------|---------|
| 2224307 | MEAN WELL | GST40A12-P1J | 12 | 3.34 | 40 | NOT INCLUDED, RECOMMEND 2271575 | 90 to 264 | 47 to 63 | Cylindrical Female | 2.1mm x 5.5mm | Center Positive | UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC | \$15.40 |
| 2271239 | Jameco Reliapro | G99-KPL060F-L253 | 12 | 5 | 60 | NOT INCLUDED, RECOMMEND 2271575 | 100 to 240 | 47 to 63 | Cylindrical Female | 2.5mm x 5.5mm | Center Positive | UL/CUL/TUV/CE/FCC/CCC | \$14.95 |
| 2208956 | Jameco Reliapro | KPL-060F-VI | 12 | 5 | 60 | NOT INCLUDED, RECOMMEND 2271575 | 100 to 240 | 50 to 60 | Cylindrical Female | 2.1mm x 5.5mm | Center Positive | UL/CUL/TUV/CE | \$13.95 |
| 2236543 | Lite-On Electronics | PA-1600-2A-LF | 12 | 5 | 60 | NOT INCLUDED, RECOMMEND 2271575 | 100 to 240 | 50 to 60 | Cylindrical Female | 2.5mm x 5.5mm | Center Positive | UL/CUL/TUV/CE | \$11.95 |
| 2272991 | EDAC | EA1050A-120 | 12 | 5 | 60 | NOT INCLUDED, RECOMMEND 2271575 | 100 to 240 | 50 to 60 | DIN Male | 4-pin DIN | N/A | UL/CUL/TUV/CE/FCC/CCC | \$12.95 |
| 2224382 | MEAN WELL | GST60A12-P1J | 12 | 5 | 60 | NOT INCLUDED, RECOMMEND 2271575 | 90 to 264 | 47 to 63 | Cylindrical Female | 2.1mm x 5.5mm | Center Positive | UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC | \$17.10 |
| 1952370 | MEAN WELL | GS60A12-P1J | 12 | 5 | 60 | NOT INCLUDED, RECOMMEND 2271575 | 90 to 264 | 47 to 63 | Cylindrical Female | 2.1mm x 5.5mm | Center Positive | UL/CUL/TUV/CEC | \$14.95 |
| 2223460 | MEAN WELL | GST90A12-P1M | 12 | 6.67 | 80 | NOT INCLUDED, RECOMMEND 2271575 | 90 to 264 | 47 to 63 | Cylindrical Female | 2.5mm x 5.5mm | Center Positive | UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC | \$28.10 |
| 2223582 | MEAN WELL | GST120A12-R7B | 12 | 8.5 | 102 | NOT INCLUDED, RECOMMEND 2271575 | 85 to 264 | 47 to 63 | DIN Male | 4-pin DIN | N/A | UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC | \$41.00 |
| 2226425 | MEAN WELL | GST160A12-R7B | 12 | 11.5 | 138 | NOT INCLUDED, RECOMMEND 2271575 | 85 to 264 | 47 to 63 | DIN Male | 4-pin DIN | N/A | UL/CUL/TUV/CB/CE/FCC/EN/EAC | \$49.60 |
| 2226476 | MEAN WELL | GST220A12-R7B | 12 | 15 | 180 | NOT INCLUDED, RECOMMEND 2271575 | 85 to 264 | 47 to 63 | DIN Male | 4-pin DIN | N/A | UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC | \$70.30 |

| Jameco Part # | Manufacturer | Manufacturer Part # | Primary Output Voltage (VDC) | Output Current (A) | Maximum Output Power (W) | AC Power Cord | Input Voltage (VAC) | Input Frequency | Output Connector Type | Output Connector Diameters | Polarity | Agency Approvals | Price 1 |
|-------------------------|--------------|---------------------|------------------------------|--------------------|--------------------------|---------------------------------|---------------------|-----------------|-----------------------|----------------------------|----------|---------------------------------|---------|
| 2226521 | MEAN WELL | GST280A12-C6P | 12 | 21 | 252 | NOT INCLUDED, RECOMMEND 2271575 | 85 to 264 | 47 to 63 | MOLEX 39-01-2060 | 6-Pin Molex | N/A | UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC | \$85.50 |