



[Click Here to Request a Large Quantity Quote](#)

[AC to DC Switching 2 Wire Table Top Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
<a href="#">2179577</a>	Delta Electronics	ADP-12GB-2.5	5	2.5	12	NOT INCLUDED, RECOMMEND 2271583	100 to 240	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL	\$4.49
<a href="#">2202870</a>	Arndt	EADP-20NB	5	4	20	INCLUDED	100 to 120	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/CEC	\$6.95
<a href="#">2203848</a>	Arndt	G32DD-050400-A	5	4	20	INCLUDED	100 to 120	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive		\$6.95
<a href="#">2203821</a>	Arndt	AD6550LF	5	4	20	INCLUDED	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/CECV	\$6.49
<a href="#">2203830</a>	Arndt	HK-AD-050U400-DH	5	4	20	NOT INCLUDED, RECOMMEND 2271583	100 to 120	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/FCC	\$4.95
<a href="#">2231435</a>	Arndt	094-0224-000	9	1.1	10	NOT INCLUDED, RECOMMEND 2271583	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm right angle	Center Positive	UL/CUL/TUV/CE/CCC	\$5.49
<a href="#">2231451</a>	ENG Electric Company	3A-122DU12	12	1	12	INCLUDED	100 to 120	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/CEC	\$7.95
<a href="#">2289471</a>	Jameco Reliapro	SA06-15S12R-U	12	1.25	15	NOT INCLUDED, RECOMMEND 2271583	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC	\$7.95
<a href="#">2188570</a>	Arndt	MPGS-U0241202000D2	12	2	24	NOT INCLUDED, RECOMMEND 2271583	100 to 240	50 to 60	Cylindrical Female	2.5mm x 5.5mm	Center Positive	UL/CUL/FCC	\$7.95
<a href="#">2257281</a>	MEAN WELL	GST25B12-P1J	12	2.08	25	NOT INCLUDED, RECOMMEND 2271583	85 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$9.90
<a href="#">2236754</a>	Arndt	PS-2.1-12-3-DC-S1	12	3	36	INCLUDED	100 to 120	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/FCC	\$5.49

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Input Frequency	Output Connector Type	Output Connector Diameters	Polarity	Agency Approvals	Price 1
<a href="#">2167445</a>	Jameco Reliapro	K36V120300E2	12	3	36	NOT INCLUDED, RECOMMEND 2271583	100 to 240	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CSA/EN	\$12.95
<a href="#">2227401</a>	Arndt	ADA017	12	3	36	NOT INCLUDED, RECOMMEND 2271583	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL	\$7.95
<a href="#">2230168</a>	Arndt	EADP-36FB	12	3	36	NOT INCLUDED, RECOMMEND 2271583	100 to 240	50 to 60	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL	\$5.95
<a href="#">1940547</a>	MEAN WELL	GS25B24-P1J	24	1.04	25	NOT INCLUDED, RECOMMEND 2271583	90 to 264	47 to 63	Cylindrical Female	2.1mm x 5.5mm	Center Positive	UL/CUL/TUV/CB/CE/FCC/EN/EAC/CCC	\$9.49