



[Click Here to Request a Large Quantity Quote](#)

[AC-to-DC Unregulated Wall Adapters](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Family	Input Voltage (VAC)	Input Frequency	Maximum Input Current (A)	Output Connector Type	Output Connector Diameters	Polarity	Price 1
<a href="#">2231443</a>	Arndt	950-00143	5	0.8	4	ARNDT	120	50Hz to 60Hz		Cylindrical Female	2.5mm x 5.5mm	Center Positive	\$3.90
<a href="#">1953612</a>	Jameco Reliapro	DDU050100M2270	5	1	5		120	60 Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$10.95
<a href="#">168605</a>	Jameco Reliapro	DDU050100H4660	5	1	5		120	60 Hz		Cylindrical Female	2.5mm x 5.5mm	Center Positive	\$10.95
<a href="#">2289151</a>	Arndt	FE4823-050E120	5	1.2	6		120	60 Hz		Cylindrical Female	2.5mm x 5.5mm	Center Positive	\$11.95
<a href="#">2270991</a>	Arndt	AX06V300	6	0.3	1.8	ARNDT	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$4.49
<a href="#">101266</a>	Jameco Reliapro	DBU060050E3860	6	0.5	3	DBU	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$6.95
<a href="#">2234741</a>	Jameco Reliapro	DBU060050-2.5	6	0.5	3	DBU	120	50Hz to 60Hz		Cylindrical Female	2.5mm x 5.5mm	Center Positive	\$6.95
<a href="#">220943</a>	Jameco Reliapro	DCU060120G2401	6	1.2	7.2	DCU	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Negative	\$9.95
<a href="#">100845</a>	Jameco Reliapro	DBU0900200Z6101	9	0.2	1.8	DBU	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$6.95
<a href="#">2215460</a>	Fujitsu	MA14L-2001-0012	9	0.2	1.8	MA14	120	50Hz to 60Hz		Cylindrical Female	1.3mm x 3.5mm	Center Positive	\$3.95
<a href="#">2230432</a>	Arndt	35-9-300C	9	0.3	2.7	ARNDT	120	50Hz to 60Hz		Cylindrical Female	2.5mm x 5.5mm	Center Positive	\$5.05
<a href="#">133891</a>	Jameco Reliapro	DBU090030	9	0.3	2.7	DBU	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$6.95
<a href="#">189238</a>	Jameco Reliapro	DBU090030H4540	9	0.3	2.7	DBU	120	50Hz to 60Hz		Cylindrical Female	2.5mm x 5.5mm	Center Positive	\$6.95
<a href="#">2295479</a>	MG Electronics	MGT9DC300	9	0.3	2.74		120	60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Negative	\$5.75

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Family	Input Voltage (VAC)	Input Frequency	Maximum Input Current (A)	Output Connector Type	Output Connector Diameters	Polarity	Price 1
<a href="#">100853</a>	Jameco Reliapro	DCU090050Z7480	9	0.5	4.5	DCU	120	50Hz to 60Hz	0.071	Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$7.95
<a href="#">15561</a>	Jameco Reliapro	DCU090050A2011	9	0.5	4.5	DCU	120	50Hz to 60Hz		DC Power Plug Male	3.5mm	Tip Positive	\$7.95
<a href="#">163628</a>	Jameco Reliapro	DCU090050Z7483-R	9	0.5	4.5	DCU	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Negative	\$7.95
<a href="#">236937</a>	Jameco Reliapro	DCU090050G6440	9	0.5	4.5	DCU	120	50Hz to 60Hz		Cylindrical Female	2.5mm x 5.5mm right angle	Center Positive	\$7.95
<a href="#">1953647</a>	Jameco Reliapro	GPU410900500WDOO	9	0.5	4.5		120	60 Hz		Cylindrical Female	2.5mm x 5.5mm	Center Positive	\$10.95
<a href="#">100175</a>	Jameco Reliapro	DCU090060Z6652	9	0.6	5.4	DCU	120	50Hz to 60Hz		Cylindrical Female	2.5mm x 5.5mm	Center Positive	\$7.95
<a href="#">202180</a>	Jameco Reliapro	DCU090060F2091	9	0.6	5.4	DCU	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$6.95
<a href="#">2229280</a>	OEM	AD091AL	9	1	9	AD	120	50Hz to 60Hz		Cylindrical Female	2.5mm x 5.5mm	Center Positive	\$6.95
<a href="#">127505</a>	Jameco Reliapro	DDU090100	9	1	9	DDU	120	50Hz to 60Hz		Cylindrical Female	2.5mm x 5.5mm	Center Positive	\$8.95
<a href="#">164929</a>	Jameco Reliapro	DDU090100C2550	9	1	9	DDU	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Negative	\$8.95
<a href="#">364576</a>	Jameco Reliapro	DDU090100J0490	9	1	9		120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$8.95
<a href="#">2271071</a>	CUI	48-9-1000D	9	1	9		120	50Hz to 60Hz		Wires		Center Positive	\$6.95
<a href="#">100095</a>	Jameco Reliapro	DBU120020	12	0.2	2.4	DBU	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$5.95
<a href="#">158043</a>	Jameco Reliapro	DBU120020E2261	12	0.2	2.4	DBU	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm right angle	Center Positive	\$5.95
<a href="#">220898</a>	Jameco Reliapro	DCU120020G2420	12	0.2	2.4		120	60 Hz		Cylindrical Female	2.1mm x 5.5mm	Center Negative	\$7.95
<a href="#">2236789</a>	Jameco Reliapro	DCU120020-G2421	12	0.2	2.4		120	60 Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$6.95
<a href="#">2231689</a>	Arndt	41-12-300	12	0.3	3.6	ARNDT	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$4.95

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Family	Input Voltage (VAC)	Input Frequency	Maximum Input Current (A)	Output Connector Type	Output Connector Diameters	Polarity	Price 1
<a href="#">2227743</a>	Arndt	MW41-1230	12	0.3	3.6	ARNDT	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Reversible	\$6.95
<a href="#">127976</a>	Jameco Reliapro	DCU120030D7162	12	0.3	3.6	DCU	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$7.95
<a href="#">2230301</a>	Arndt	RAD-1200400C	12	0.4	4.8	ARNDT	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$5.95
<a href="#">2229781</a>	ENG Electric Company	91-54909	12	0.5	6	AD	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 2.5mm	Center Positive	\$3.95
<a href="#">2227858</a>	Arndt	L4D-120050R	12	0.5	6	ARNDT	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$4.49
<a href="#">102496</a>	Jameco Reliapro	DCU120050E8601	12	0.5	6	DCU	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$7.95
<a href="#">102277</a>	Jameco Reliapro	DCU120050E2631	12	0.5	6	DCU	120	50Hz to 60Hz		Cylindrical Female	2.5mm x 5.5mm	Center Positive	\$7.95
<a href="#">15368</a>	Jameco Reliapro	DCU120050Z8693	12	0.5	6	DCU	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Negative	\$7.95
<a href="#">114825</a>	Jameco Reliapro	DCU120050D4740	12	0.5	6	DCU	120	50Hz to 60Hz		Wires	Stripped & Tinned		\$7.95
<a href="#">2228893</a>	CUI	DPD120050-P5	12	0.5	6	DPD	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$5.49
<a href="#">2227840</a>	Dee Van Enterprise Usa	DV-1250	12	0.5	6	DV	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$4.95
<a href="#">162996</a>	Jameco Reliapro	DDU120050F0980	12	0.5	6		120	60 Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$12.95
<a href="#">2217799</a>	Arndt	AD-1280G	12	0.8	9.6	ARNDT	120	50Hz to 60Hz		Cylindrical Female	2.5mm x 5.5mm	Center Positive	\$3.95
<a href="#">129331</a>	Jameco Reliapro	DDU120080F2412	12	0.8	9.6	DDU	120	50Hz to 60Hz		Cylindrical Female	2.5mm x 5.5mm	Center Positive	\$8.95
<a href="#">117479</a>	Jameco Reliapro	DDU120080E6450	12	0.8	9.6	DDU	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$8.95
<a href="#">121232</a>	Jameco Reliapro	DDU120080F2271	12	0.8	9.6	DDU	120	50Hz to 60Hz		DC Power Plug Male	3.5mm	Tip Positive	\$7.95
<a href="#">2158160</a>	Arndt	GPU481200800WD00	12	0.8	9.6	GPU	120	50Hz to 60Hz		Cylindrical Female	2.5mm x 5.5mm	Center Positive	\$5.95

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	Family	Input Voltage (VAC)	Input Frequency	Maximum Input Current (A)	Output Connector Type	Output Connector Diameters	Polarity	Price 1
<a href="#">2215742</a>	Arndt	T012LF1209	12	1	12	ARNDT	120	50Hz to 60Hz	0.5	Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$4.95
<a href="#">100870</a>	Jameco Reliapro	DDU120100Z7972	12	1	12	DDU	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$9.95
<a href="#">105478</a>	Jameco Reliapro	DDU120100Z2993	12	1	12	DDU	120	50Hz to 60Hz		Cylindrical Female	2.5mm x 5.5mm	Center Positive	\$9.95
<a href="#">15392</a>	Jameco Reliapro	DDU120100E7302	12	1	12	DDU	120	50Hz to 60Hz		DC Power Plug Male	3.5mm	Tip Positive	\$9.95
<a href="#">170245</a>	Jameco Reliapro	DDU120100H4480	12	1	12		120	60 Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$14.95
<a href="#">1953663</a>	Jameco Reliapro	DDU120100M2250	12	1	12		120	60 Hz		Cylindrical Female	2.5mm x 5.5mm	Center Positive	\$14.95
<a href="#">2179770</a>	Westell	MT12-4120100-A1	12	1	12		120	50Hz to 60Hz		Cylindrical Female	2.5mm x 5.5mm	Center Positive	\$5.95
<a href="#">2211135</a>	Fellowes	A-48-628(R.2)	12	1	12		120	50Hz to 60Hz		Cylindrical Female	2.5mm x 5.5mm	Center Positive	\$3.95
<a href="#">196779</a>	Jameco Reliapro	DDU120120G0031	12	1.2	14.4	DDU	120	50Hz to 60Hz		Cylindrical Female	2.5mm x 5.5mm	Center Positive	\$10.95
<a href="#">2192747</a>	Arndt	MW48-1201250	12	1.25	15	ARNDT	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$4.95
<a href="#">101291</a>	Jameco Reliapro	DDU120150	12	1.5	18	DDU	120	50Hz to 60Hz		Cylindrical Female	2.5mm x 5.5mm	Center Positive	\$12.95
<a href="#">203036</a>	Jameco Reliapro	DDU120150H4530	12	1.5	18	DDU	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Negative	\$11.95
<a href="#">136881</a>	Jameco Reliapro	DFU120150K1961	12	1.5	18	DFU	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$12.95
<a href="#">2218003</a>	Jameco Reliapro	DFU120200R-2.1	12	2	24	DFU	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$11.95
<a href="#">308099</a>	Jameco Reliapro	DDU135100H3210	13.5	1	13.5	DDU	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$9.95
<a href="#">123932</a>	Jameco Reliapro	DDU140070Z7470	14	0.7	9.8	DDU	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$8.95
<a href="#">190001</a>	Jameco Reliapro	DCU150050E3021	15	0.5	7.5	DCU	120	50Hz to 60Hz		Cylindrical Female	2.1mm x 5.5mm	Center Positive	\$7.95

