



[Click Here to Request a Large Quantity Quote](#)

[Motors-Stepper](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Coil Type	Voltage Rating (DC)	Current (mA)	Step Angle	Phase Resistance (Ohms)	Phase Inductance (mH)	Holding Torque (g-cm)	Shaft Diameter (inch)	Shaft Length (inch)	Motor Size (Diameter x Length) (inch)	Price 1
2245626	Jameco Reliapro	1124176	Bipolar	1.8	1500	1.8	1.2	1.6	2243	0.2	0.86	1.66 x 1.34	\$7.95
2245618	Jameco Reliapro	1124278	Bipolar	2.25	1500	1.8	1.5	3.3	4079	0.2	0.86	1.66 x 1.57	\$9.95
2245634	Jameco Reliapro	1144108	Bipolar	3.24	1200	1.8	2.7	5	2400	0.2	0.63	1.66 x 1.6	\$9.95
2234839	Jameco Reliapro	42BYG44B	Bipolar	4	1000	1.8	4	10	3600	0.2	0.312	1.65 x 1.68	\$15.95
2270927	Oriental Motor	PX245-01AA	Bipolar	4	1200	1.8	3.3	2.4	2192	0.2	0.85	1.66 x 1.82	\$13.95
2245597	Jameco Reliapro	1124144	Bipolar	4.5	1500	1.8	3	6	200	0.2	0.83	1.66 x 2	\$12.95
2245589	Jameco Reliapro	1124142	Bipolar	4.5	1500	1.8	3	6	6800	0.2	0.86	1.66 x 2	\$12.95
237578	Jameco Reliapro	57BYG061-R	Bipolar	6	500	1.8	12	24	3569	0.25	0.83	2.29 x 1.61	\$34.95
155460	Jameco Reliapro	42BYG023-R	Bipolar	12	400	1.8	30	36	2100	0.2	0.6	1.7 x 1.3	\$17.95
2158531	Shinano Kenshi	STP-42D201-37	Bipolar	12	1700	1.8	1.55	5	3200	0.19	1.49	1.65 x 1.49	\$4.95
2245642	Jameco Reliapro	1123005	Bipolar	14	400	1.8	35	44	2200	0.2	0.87	1.67 x 1.34	\$9.95
2158557	Mitsumi Electronics Corporation	M25SP-5N LF(50 OHMS)	Bipolar	24	550	7.5	50	n/a	183	0.08	0.22	1.25 x 0.53	\$1.25
2209254	NMB Technologies	PM55L-048-ZXX3	Bipolar	24	800	7.5	5.5	n/a	1600	0.25	0.62	2.16 x 1	\$1.95
237825	Jameco Reliapro	25BY4801	Unipolar	5	500	1.8	10	n/a	110	0.08	0.35	0.98 x 0.56	\$8.95
237607	Jameco Reliapro	57BYGH001-R	Unipolar	5	1000	1.8	5	n/a	3976	0.2	0.25	2.24 x 1.61	\$27.95
2138812	Jameco Reliapro	35BY48L030-01	Unipolar	7	350	7.5	20	11	450	0.078	0.47	1.37 x 0.85	\$7.49
2234476	Fulling Motor USA	35BYHJ30-36A	Unipolar	12	259	7.5	50	74	6000	0.2	0.53	1.37 x 1.37	\$5.95
155433	Jameco Reliapro	42BYG228-R	Unipolar	12	400	1.8	30	23	2000	0.2	0.6	1.7 x 1.5	\$18.95
238538	Jameco Reliapro	42BYGH404-R	Unipolar	12	400	1.8	30	25	3400	0.2	0.95	1.67 x 1.89	\$19.95