



[Click Here to Request a Large Quantity Quote](#)

[Switches-Rocker](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Pins	Contact Form	Switch Function	Current Rating	Actuator Type	Body Color	Color - Actuator/Cap	Termination Style	Length (inch)	Width (inch)	Price 1
<a href="#">2267023</a>	Mountain Switch	103-7003-EVX	2	3PDT	ON-ON	5 @ 125 VAC	Rocker	Red	Black	PC terminal	1.16	0.365	\$2.95
<a href="#">2268167</a>	Jameco Valuepro	R13-66C-10-BBNN	2	4PDT	ON-NONE-ON	16 @ 125 VAC	Rocker	Black	Red	0.187" Quick Connect	0.826	0.59	\$1.59
<a href="#">2266991</a>	Jameco Valuepro	103-7000	2	4PDT	ON-ON	5 @ 125 VAC	Rocker	Red	Black	PC terminal RA	0.85	0.5	\$2.95
<a href="#">2267007</a>	Mountain Switch	103-7001-EVX	2	DPDT	ON-(ON)	5 @ 125 VAC	Rocker	Red	Black	PC terminal RA	0.5	0.45	\$1.95
<a href="#">2267991</a>	Jameco Valuepro	R13-104-B-G	2	DPDT	ON-OFF-ON	16 @ 125 VAC	Illuminated Rocker	Black	Green	0.25" Quick Connect	1.18	1.18	\$1.59
<a href="#">2181183</a>	C&K	ET21J1ABE2	2	DPDT	ON-ON	0.02 @ 125 VAC	Rocker	Red	Black	PC Pin	0.913	0.36	\$3.95
<a href="#">2268071</a>	Jameco Valuepro	R13-49B-05-BB	2	DPDT	ON-ON	10 @ 125 VAC	Rocker	Black	Black	Solder Lug	1.18	0.787	\$1.25
<a href="#">2268031</a>	Mountain Switch	R13-136B-05-BR	2	DPDT	ON-ON	10 @ 125 VAC	Rocker	Black	Red	Solder Lug	0.905	0.905	\$1.25
<a href="#">2268055</a>	Mountain Switch	R13-104C-01-BB	2	DPDT	ON-ON	16 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	1.18	1.18	\$1.09
<a href="#">2267127</a>	Mountain Switch	103-7021-EVX	2	DPDT	ON-ON	5 @ 125 VAC	Paddle	Red	Black	PC terminal RA	1.565	0.662	\$1.95
<a href="#">2269871</a>	Mountain Switch	103-7012	2	DPDT	ON-ON	5 @ 125 VAC	Rocker	Red	Black	Solder Lug	1.15	0.275	\$1.49
<a href="#">2267135</a>	Mountain Switch	103-7022-EVX	2	DPDT	ON-ON	5 @ 125 VAC	Rocker	Red	Black	Solder Lug	1.168	0.372	\$2.95
<a href="#">2269759</a>	Jameco Valuepro	112-R13-73C-02-Y	2	DPST	ON-OFF	10 @ 125 VAC	Illuminated Rocker	Black	Amber	0.187" Quick Connect	0.826	0.59	\$1.95
<a href="#">2181271</a>	Otto	K2ABHLCADA	2	DPST	ON-OFF	10 @ 125 VAC	Illuminated Rocker	Black	Black with Green LED	0.16" Quick Connect	0.65	1.06	\$12.95
<a href="#">2269751</a>	Jameco Valuepro	112-R13-73C-02-R	2	DPST	ON-OFF	10 @ 125 VAC	Illuminated Rocker	Black	Red	0.187" Quick Connect	0.826	0.59	\$1.95
<a href="#">316153</a>	Jameco Valuepro	R13-73C-R-02-R	2	DPST	ON-OFF	10 @ 125 VAC	Illuminated Rocker	Black	Red	0.187" Quick Connect	0.83	0.59	\$1.75
<a href="#">2158522</a>	Jameco Valuepro	GP1231100M00	2	DPST	ON-OFF	10 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	0.827	0.59	\$1.49

Jameco Part #	Manufacturer	Manufacturer Part #	Pins	Contact Form	Switch Function	Current Rating	Actuator Type	Body Color	Color - Actuator/Cap	Termination Style	Length (inch)	Width (inch)	Price 1
<a href="#">316111</a>	Jameco Valuepro	R13-73A2-B-02-R	2	DPST	ON-OFF	12 @ 125 VAC	Rocker	Black	Black	0.187" Quick Connect	0.83	0.594	\$1.75
<a href="#">2276479</a>	Marquardt Switch	1555.3109-00	2	DPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Black with Green Neon	0.25" Quick Connect	1.18	0.59	\$2.75
<a href="#">2267439</a>	Mountain Switch	103-7080-EV	2	DPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Green	0.25" Quick Connect	1.24	0.992	\$2.49
<a href="#">2267503</a>	Mountain Switch	103-R13-240B-01G-E	2	DPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Green	0.25" Quick Connect	1.24	1.15	\$1.09
<a href="#">2267631</a>	Mountain Switch	103-R13-244B-02R-EV	2	DPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Red	0.187" Quick Connect	0.925	0.925	\$1.59
<a href="#">2267415</a>	Mountain Switch	103-7077-EV	2	DPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.22	1.18	\$1.09
<a href="#">2267431</a>	Mountain Switch	103-7079-EV	2	DPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.24	0.992	\$2.49
<a href="#">2267607</a>	Mountain Switch	103-R13-240B-01R-EV	2	DPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.24	1.15	\$1.95
<a href="#">2267599</a>	Mountain Switch	103-R13-240B-01R	2	DPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.24	1.15	\$1.25
<a href="#">2267423</a>	Mountain Switch	103-7078-EV	2	DPST	ON-OFF	16 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	1.24	0.992	\$1.09
<a href="#">2267223</a>	Mountain Switch	103-7045-EVX	2	DPST	ON-OFF	16 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	1.71	0.964	\$3.29
<a href="#">2269695</a>	Jameco Valuepro	R13-104A-01-BB	2	DPST	ON-OFF	16 @ 125 VAC	Round Rocker	Black	Black	0.25" Quick Connect	1.18	1.18	\$1.09
<a href="#">2267647</a>	Mountain Switch	103-R13-245B-02G-EV	2	DPST	ON-OFF	8 @ 125 VAC	Illuminated Rocker	Black	Green	0.187" Quick Connect	1.18	1.18	\$1.09
<a href="#">2267655</a>	Mountain Switch	103-R13-245B-02R-EV	2	DPST	ON-OFF	8 @ 125 VAC	Illuminated Rocker	Black	Red	0.187" Quick Connect	1.18	1.18	\$1.49
<a href="#">2267639</a>	Mountain Switch	103-R13-245A-02-EV	2	DPST	ON-OFF	8 @ 125 VAC	Rocker	Black	Black	0.187" Quick Connect	1.18	1.18	\$0.89
<a href="#">2267039</a>	Mountain Switch	103-7008-EVX	2	SPDT	ON-(ON)	5 @ 125 VAC	Paddle	Red	Black	Solder Lug	1.16	0.365	\$1.59
<a href="#">2267095</a>	Mountain Switch	103-7016-EVX	2	SPDT	ON-(ON)	5 @ 125 VAC	Paddle	Red	Black	Solder Lug	1.75	0.357	\$1.95
<a href="#">2267087</a>	Mountain Switch	103-7015-EVX	2	SPDT	ON-(ON)	5 @ 125 VAC	Rocker	Red	Black	Solder Lug	1.166	0.373	\$1.95
<a href="#">2285503</a>	C&K	7101J1ASE2	2	SPDT	ON-NONE-ON	4 @ 125 VAC	Rocker	Red	Black	PC Terminal	0.5	0.275	\$4.95
<a href="#">2172738</a>	Jameco Valuepro	1901	2	SPDT	ON-OFF	6 @ 125 VAC	Rocker	Black	Black	PC Pin	0.829	0.377	\$0.65

Jameco Part #	Manufacturer	Manufacturer Part #	Pins	Contact Form	Switch Function	Current Rating	Actuator Type	Body Color	Color - Actuator/Cap	Termination Style	Length (inch)	Width (inch)	Price 1
<a href="#">2268351</a>	Jameco Valuepro	R13-66HPA-02-BB	2	SPDT	ON-OFF-(ON)	16 @ 125 VAC	Paddle	Black	Black	0.187" Quick Connect	0.826	0.59	\$1.25
<a href="#">2267543</a>	Mountain Switch	103-R13-211D-02-EV	2	SPDT	ON-OFF-ON	10 @ 125 VAC	Rocker	Black	Black	0.187" Quick Connect	0.866	0.866	\$0.99
<a href="#">1945241</a>	Illinois Tool Works	163-009-029	2	SPDT	ON-OFF-ON	16 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	1.185	0.55	\$1.75
<a href="#">2268215</a>	Mountain Switch	103-R13-238D-01W-EV	2	SPDT	ON-OFF-ON	16 @ 125 VAC	Rocker	Black	White	0.25" Quick Connect	1.24	0.728	\$1.09
<a href="#">2276863</a>	Eledis	3A11-BFST-SE22	2	SPDT	ON-OFF-ON	5 @ 125 VAC	Rocker	Red	Black	Solder Lug	0.78	0.622	\$0.79
<a href="#">2268159</a>	Jameco Valuepro	R13-241D05BB	2	SPDT	ON-OFF-ON	6 @ 125 VAC	Rocker	Black	Black	Solder Lug	0.944	0.807	\$1.95
<a href="#">2181255</a>	C&K	7101J1V6BE2	2	SPDT	ON-ON	0.02 @ 125 VAC	Rocker	Red	Black	PC Pin	0.765	0.362	\$2.49
<a href="#">2268151</a>	Mountain Switch	R13-228C-05-BB	2	SPDT	ON-ON	10 @ 125 VAC	Rocker	Black	Black	Solder Lug	1.133	0.708	\$1.75
<a href="#">2268303</a>	Jameco Valuepro	R13-136C-05-BB	2	SPDT	ON-ON	10 @ 125 VAC	Rocker	Black	Black	Solder Lug	1.18	0.787	\$1.09
<a href="#">2269783</a>	Jameco Valuepro	112-R13-136C-05-B	2	SPDT	ON-ON	10 @ 125 VAC	Rocker	Black	Black	Solder Lug	1.18	0.787	\$1.25
<a href="#">2267191</a>	Mountain Switch	103-7037-EV	2	SPDT	ON-ON	10 @ 125 VAC	Rocker	Black	Red	0.25" Quick Connect	1.18	0.551	\$1.59
<a href="#">2268319</a>	Jameco Valuepro	R13-136C-05-BR	2	SPDT	ON-ON	10 @ 125 VAC	Rocker	Black	Red	Solder Lug	1.18	0.787	\$1.09
<a href="#">2280583</a>	C&K	C121J13S205QF	2	SPDT	ON-ON	15 @ 125 VAC	Rocker	Black	Black	0.25" Quick Conenct	0.82	0.68	\$1.95
<a href="#">2267391</a>	Mountain Switch	103-7074-EVX	2	SPDT	ON-ON	16 @ 125 VAC	Illuminated Rocker	Black	Yellow	0.25" Quick Connect	1.31	0.988	\$1.09
<a href="#">2276511</a>	C&K	CR101J12S215QF	2	SPDT	ON-ON	16 @ 125 VAC	Rocker	Black	Black	0.187" Quick Connect	0.78	0.78	\$1.09
<a href="#">2267479</a>	Mountain Switch	103-R13-135C-02-EV	2	SPDT	ON-ON	16 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	0.906	0.906	\$1.75
<a href="#">2267623</a>	Mountain Switch	103-R13-244A-02-EV	2	SPDT	ON-ON	16 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	0.925	0.925	\$1.59
<a href="#">2268183</a>	Mountain Switch	103-R13-205C3-01-EV	2	SPDT	ON-ON	16 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	1.24	0.728	\$1.09

Jameco Part #	Manufacturer	Manufacturer Part #	Pins	Contact Form	Switch Function	Current Rating	Actuator Type	Body Color	Color - Actuator/Cap	Termination Style	Length (inch)	Width (inch)	Price 1
<a href="#">2267575</a>	Mountain Switch	103-R13-238C-01B-EV	2	SPDT	ON-ON	16 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	1.24	0.728	\$1.09
<a href="#">2267383</a>	Mountain Switch	103-7073-EV	2	SPDT	ON-ON	16 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	1.31	0.988	\$1.09
<a href="#">2267671</a>	Mountain Switch	103T13238VO/WEV	2	SPDT	ON-ON	16 @ 125 VAC	Rocker	Black	White	0.25" Quick Connect	1.24	0.728	\$1.09
<a href="#">2267583</a>	Mountain Switch	103-R13-238C-01W-EV	2	SPDT	ON-ON	16 @ 125 VAC	Rocker	Black	White	0.25" Quick Connect	1.24	0.728	\$0.89
<a href="#">2267079</a>	Mountain Switch	103-7014-EVX	2	SPDT	ON-ON	5 @ 125 VAC	Paddle	Red	Black	PC terminal RA	1.425	0.365	\$1.95
<a href="#">2267031</a>	Mountain Switch	103-7005-EVX	2	SPDT	ON-ON	5 @ 125 VAC	Rocker	Red	Black	Solder Lug	1.16	0.365	\$1.95
<a href="#">2267071</a>	Mountain Switch	103-7013-EVX	2	SPDT	ON-ON	5 @ 125 VAC	Rocker	Red	Black	Solder Lug	1.168	0.373	\$1.75
<a href="#">2269815</a>	Jameco Valuepro	R13-213C-03-B	2	SPDT	ON-ON	6 @ 125 VAC	Rocker	Black	Black	0.110" Quick Connect	0.799	0.566	\$1.25
<a href="#">2178566</a>	CW Industries	GRS-4012-0050	2	SPDT	ON-ON	8 @ 125 VAC	Rocker	Black	Red	0.187" Quick Connect	0.823	0.59	\$1.75
<a href="#">2276767</a>	TE Connectivity	2-1571076-1	2	SPST	OFF-(ON)	16 @ 125 VAC	Rocker	Black	Black	0.187" Quick Connect	0.845	0.584	\$1.95
<a href="#">2269743</a>	Jameco Valuepro	112-R13-73B-02-Y	2	SPST	ON-OFF	10 @ 125 VAC	Illuminated Rocker	Black	Amber	0.187" Quick Connect	0.826	0.59	\$1.09
<a href="#">2269847</a>	Jameco Valuepro	R13-66B2S-02	2	SPST	ON-OFF	10 @ 125 VAC	Illuminated Rocker	Black	Black with Green Neon	0.187" Quick Connect	0.826	0.59	\$0.99
<a href="#">2268015</a>	Mountain Switch	R13-228B-05-BGG-N1	2	SPST	ON-OFF	10 @ 125 VAC	Illuminated Rocker	Black	Green	Solder Lug	1.14	0.724	\$0.99
<a href="#">2269767</a>	Jameco Valuepro	112-R13-73B-02-R	2	SPST	ON-OFF	10 @ 125 VAC	Illuminated Rocker	Black	Red	0.187" Quick Connect	0.826	0.59	\$1.59
<a href="#">316128</a>	Jameco Valuepro	R13-73B-R-02	2	SPST	ON-OFF	10 @ 125 VAC	Illuminated Rocker	Black	Red	0.187" Quick Connect	0.83	0.59	\$1.49
<a href="#">2267183</a>	Mountain Switch	103-7036-EV	2	SPST	ON-OFF	10 @ 125 VAC	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.18	0.551	\$1.59
<a href="#">2268127</a>	Jameco Valuepro	R13-228B-05-BRR-N1	2	SPST	ON-OFF	10 @ 125 VAC	Illuminated Rocker	Black	Red	Solder Lug	1.133	0.708	\$0.99
<a href="#">2268343</a>	Jameco Valuepro	R13-66APA-02-BB	2	SPST	ON-OFF	10 @ 125 VAC	Paddle	Black	Black	0.187" Quick Connect	0.826	0.59	\$0.99
<a href="#">2276759</a>	C&K	8941K469	2	SPST	ON-OFF	10 @ 125 VAC	Paddle	Black	Red	0.25" spade tab	1.93	0.745	\$1.25
<a href="#">316014</a>	Jameco Valuepro	R13-66A-B-02-R	2	SPST	ON-OFF	10 @ 125 VAC	Rocker	Black	Black	0.187" Quick Connect	0.826	0.59	\$0.99

Jameco Part #	Manufacturer	Manufacturer Part #	Pins	Contact Form	Switch Function	Current Rating	Actuator Type	Body Color	Color - Actuator/Cap	Termination Style	Length (inch)	Width (inch)	Price 1
<a href="#">2267535</a>	Mountain Switch	103-R13-211A-02-EV	2	SPST	ON-OFF	10 @ 125 VAC	Rocker	Black	Black	0.187" Quick Connect	0.866	0.866	\$0.99
<a href="#">2218839</a>	Jameco Valuepro	RS-105A-BB-3-UL	2	SPST	ON-OFF	10 @ 125 VAC	Rocker	Black	Black	0.187" Quick Connect	0.905	0.905	\$0.99
<a href="#">2276495</a>	Apem Components	MR110-C5N-BRNWC	2	SPST	ON-OFF	10 @ 125 VAC	Rocker	Black	Black	0.189 Quick Connect	0.83	0.59	\$0.99
<a href="#">2269799</a>	Jameco Valuepro	R13-89A-01	2	SPST	ON-OFF	10 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	1.18	0.551	\$1.09
<a href="#">2267199</a>	Mountain Switch	103-7038-EV	2	SPST	ON-OFF	10 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	1.18	0.551	\$1.09
<a href="#">2277751</a>	Carling Technologies	RSCA211-RB-B-E-N	2	SPST	ON-OFF	10 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	1.24	0.67	\$1.09
<a href="#">2234345</a>	Jameco Valuepro	HM-RS-03	2	SPST	ON-OFF	10 @ 125 VAC	Rocker	Black	Black	5.5" Wires	0.824	0.588	\$1.49
<a href="#">2276487</a>	Omron	A8L-11-12N1	2	SPST	ON-OFF	10 @ 125 VAC	Rocker	Black	Black	PC terminal	0.83	0.59	\$1.75
<a href="#">316022</a>	Jameco Valuepro	R13-66A-R-02-R	2	SPST	ON-OFF	10 @ 125 VAC	Rocker	Black	Red	0.187" Quick Connect	0.826	0.59	\$0.99
<a href="#">577221</a>	Cherry	RRA22H3BBBNN	2	SPST	ON-OFF	10 @ 125 VAC	Round Rocker	Black	Black	0.187" Quick Connect	0.906	0.783	\$1.49
<a href="#">2267375</a>	Mountain Switch	103-7072-EV	2	SPST	ON-OFF	15 @ 125 VAC	Illuminated Rocker	Black	Green	0.25" Quick Connect	1.25	0.677	\$0.79
<a href="#">2268223</a>	Mountain Switch	103-R13-72A-EV	2	SPST	ON-OFF	15 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	1.26	0.677	\$0.89
<a href="#">2267519</a>	Mountain Switch	103-R13-112LP-02Y-E	2	SPST	ON-OFF	16 @ 125 VAC	Illuminated Paddle	Black	Black with Yellow LED	0.187" Quick Connect + Solder	0.91	0.91	\$2.49
<a href="#">2267287</a>	Mountain Switch	103-7055-EV	2	SPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Black with Green LED	0.187" Quick Connect	0.905	0.905	\$1.09
<a href="#">2267999</a>	Mountain Switch	103-R13-205L-01G-EV	2	SPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Black with Green LED	0.25" Quick Connect	1.24	1.15	\$1.09
<a href="#">2267295</a>	Mountain Switch	103-7056-EV	2	SPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Black with Red LED	0.187" Quick Connect	0.905	0.905	\$1.25
<a href="#">2268207</a>	Mountain Switch	103-R13-205L-01R-EV	2	SPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Black with Red LED	0.25" Quick Connect	1.24	0.728	\$1.59
<a href="#">2267559</a>	Mountain Switch	103-R13-238B-01G-EV	2	SPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Green	0.25" Quick Connect	1.24	0.728	\$1.09

Jameco Part #	Manufacturer	Manufacturer Part #	Pins	Contact Form	Switch Function	Current Rating	Actuator Type	Body Color	Color - Actuator/Cap	Termination Style	Length (inch)	Width (inch)	Price 1
<a href="#">2269735</a>	Jameco Valuepro	R13-91B-01-BG	2	SPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Green	0.25" Quick Connect	1.3	0.551	\$1.59
<a href="#">2267239</a>	Mountain Switch	103-7048-EV	2	SPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Green	0.25" Quick Connect	1.3	0.551	\$1.95
<a href="#">2267231</a>	Mountain Switch	103-7046-EV	2	SPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Green	0.25" Quick Connect	1.3	0.551	\$1.59
<a href="#">2267463</a>	Mountain Switch	103-7084-EV	2	SPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Green	0.25" Quick Connect	1.38	0.551	\$1.59
<a href="#">2267271</a>	Mountain Switch	103-7052-EV	2	SPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Orange	0.187" Quick Connect	0.905	0.905	\$0.79
<a href="#">2267247</a>	Mountain Switch	103-7049-EV	2	SPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Orange	0.25" Quick Connect	1.3	0.551	\$1.59
<a href="#">2267279</a>	Mountain Switch	103-7053-EV	2	SPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Red	0.187" Quick Connect	0.905	0.905	\$0.95
<a href="#">2267487</a>	Mountain Switch	103-R13-205B-01R-EV	2	SPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.24	0.728	\$1.59
<a href="#">2267567</a>	Mountain Switch	103-R13-238B-01R-EV	2	SPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.24	0.728	\$1.59
<a href="#">2267255</a>	Mountain Switch	103-7050-EV	2	SPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.3	0.551	\$1.25
<a href="#">2269823</a>	Jameco Valuepro	R13-91B-01-BR	2	SPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.3	0.551	\$1.59
<a href="#">2268023</a>	Mountain Switch	103-7047-EV	2	SPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.3	0.551	\$1.09
<a href="#">2267399</a>	Mountain Switch	103-7075-EV	2	SPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.31	0.988	\$2.49
<a href="#">2267447</a>	Mountain Switch	103-7082-EV	2	SPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.38	0.551	\$1.59
<a href="#">2267359</a>	Mountain Switch	103-7065-EV	2	SPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.637	1.005	\$0.99
<a href="#">2267351</a>	Mountain Switch	103-7064-EV	2	SPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.637	1.005	\$0.99
<a href="#">2267455</a>	Mountain Switch	103-7083-EV	2	SPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Yellow	0.25" Quick Connect	1.38	0.551	\$1.09
<a href="#">2267407</a>	Mountain Switch	103-7076-EV	2	SPST	ON-OFF	16 @ 125 VAC	Illuminated Rocker	Black	Yellow & Red	0.25" Quick Connect	1.31	0.988	\$1.09

Jameco Part #	Manufacturer	Manufacturer Part #	Pins	Contact Form	Switch Function	Current Rating	Actuator Type	Body Color	Color - Actuator/Cap	Termination Style	Length (inch)	Width (inch)	Price 1
<a href="#">2231355</a>	Bulgin	R13-135A-02	2	SPST	ON-OFF	16 @ 125 VAC	Rocker	Black	Black	0.187" Quick Connect	0.57	0.91	\$1.49
<a href="#">2267263</a>	Mountain Switch	103-7051-EV	2	SPST	ON-OFF	16 @ 125 VAC	Rocker	Black	Black	0.187" Quick Connect	0.905	0.905	\$0.55
<a href="#">2201914</a>	Clarostat/Honeywell	028-01011-00	2	SPST	ON-OFF	16 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	1.18	0.547	\$0.55
<a href="#">2267471</a>	Mountain Switch	103-R13-91A-EV	2	SPST	ON-OFF	16 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	1.31	0.55	\$1.05
<a href="#">2268007</a>	Mountain Switch	103-7081-EV	2	SPST	ON-OFF	16 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	1.38	0.551	\$0.89
<a href="#">2267343</a>	Mountain Switch	103-7063-EVX	2	SPST	ON-OFF	16 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	1.637	1.005	\$0.89
<a href="#">2267207</a>	Mountain Switch	103-7043-EVX	2	SPST	ON-OFF	16 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	1.71	0.964	\$2.49
<a href="#">2267527</a>	Mountain Switch	103-R13-205A2-01-EV	2	SPST	ON-OFF	16 @ 125 VAC	Rocker	Black	Black/Red	0.25" Quick Connect	1.24	0.728	\$1.59
<a href="#">2267551</a>	Mountain Switch	103-R13-238A-01W-EV	2	SPST	ON-OFF	16 @ 125 VAC	Rocker	Black	White	0.25" Quick Connect	1.24	0.728	\$1.59
<a href="#">2276503</a>	ZF	CRE22F2FBBNE	2	SPST	ON-OFF	20 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	1.24	0.645	\$1.25
<a href="#">2269831</a>	Jameco Valuepro	R13-238A-01	2	SPST	ON-OFF	20 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	1.24	0.728	\$1.09
<a href="#">2208198</a>	Jameco Valuepro	RS-001G-A-BB-4	2	SPST	ON-OFF	6 @ 125 VAC	Rocker	Black	Black	0.15" Quick Connect	0.59	0.41	\$0.75
<a href="#">621270</a>	GC Electronics	35-1851-BU	2	SPST	ON-OFF	6 @ 125 VAC	Rocker	Black	Black	Solder	2.51	0.82	\$3.95
<a href="#">2268199</a>	Jameco Valuepro	R13-213A-03-BR	2	SPST	ON-OFF	6 @ 125 VAC	Rocker	Black	Red	Solder Lug	0.799	0.566	\$1.49
<a href="#">2269791</a>	Jameco Valuepro	112-R13-241A-05	2	SPST	ON-OFF	6 @ 125 VAC	Round Rocker	Black	Black	Solder Lug	0.944	0.807	\$1.59
<a href="#">2267327</a>	Mountain Switch	103-7062-EV	2	SPST	ON-OFF	8 @ 125 VAC	Illuminated Rocker	Black	Red	0.187" Quick Connect	1.73	0.475	\$0.89
<a href="#">2276471</a>	Marquardt Switch	1801.1908	2	SPST	ON-OFF	8 @ 125 VAC	Rocker	Black	Black	0.187" Quick Connect	0.826	0.59	\$1.25
<a href="#">316451</a>	Jameco Valuepro	R13-243A-02	2	SPST	ON-OFF	8 @ 125 VAC	Rocker	Black	Black	0.187" Quick Connect	0.83	0.374	\$0.99
<a href="#">2267319</a>	Mountain Switch	103-7061-EV	2	SPST	ON-OFF	8 @ 125 VAC	Rocker	Black	Black	0.187" Quick Connect	1.73	0.475	\$0.79
<a href="#">2267311</a>	Mountain Switch	103-7060-EVX	2	SPST	ON-OFF	8 @ 125 VAC	Rocker	Black	Black	Solder Lug	1.61	0.512	\$0.79
<a href="#">2267303</a>	Mountain Switch	103-7059-EVX	2	SPST	ON-OFF	8 @ 125 VAC	Rocker	Black	Black with Raised Dot	Solder Lug	1.61	0.716	\$0.79

Jameco Part #	Manufacturer	Manufacturer Part #	Pins	Contact Form	Switch Function	Current Rating	Actuator Type	Body Color	Color - Actuator/Cap	Termination Style	Length (inch)	Width (inch)	Price 1
<a href="#">316048</a>	Jameco Valuepro	R13-66B-G-02	2	SPST	ON-OFF	9 @ 125 VAC	Illuminated Rocker	Black	Green	0.187" Quick Connect	1.093	0.512	\$1.49
<a href="#">2268039</a>	Jameco Valuepro	R13-66L-02-BBGG-L1	2	SPST	ON-ON	16 @ 125 VAC	Illuminated Rocker	Black	Black with Green LED	Solder Lug	0.826	0.59	\$1.59
<a href="#">2290511</a>	Bulgin	H8601VBBR	2	SPST-NO	OFF-(ON)	16 @ 125 VAC	Curved Rocker	Black	Red	0.187" Quick Connect	0.83	0.59	\$1.95
<a href="#">2285295</a>	C&K	7201J1ZSI	3	DPDT	ON-NONE-ON	5 @ 125 VAC	Rocker	Red	Orange	Solder Lug	0.45	1.156	\$3.95
<a href="#">2267615</a>	Mountain Switch	103-R13-240D-01-EV	3	DPDT	ON-OFF-ON	16 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	1.24	1.15	\$1.25
<a href="#">2267215</a>	Mountain Switch	103-7044-EVX	3	DPDT	ON-OFF-ON	16 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	1.71	0.964	\$2.49
<a href="#">2267143</a>	Mountain Switch	103-7023-EVX	3	DPDT	ON-OFF-ON	5 @ 125 VAC	Rocker	Red	Black	PC terminal RA	1.27	0.372	\$2.49
<a href="#">2267919</a>	Mountain Switch	1055-RA1165	3	DPDT	ON-OFF-ON	6 @ 125 VAC	Rocker	Blue	Black	Solder Lug	1.16	0.472	\$1.09
<a href="#">2267015</a>	Mountain Switch	103-7002-EVX	3	DPDT	ON-ON	5 @ 125 VAC	Paddle	Red	Black	Solder Lug	1.16	0.365	\$1.59
<a href="#">617473</a>	GC Electronics	35-695-BU	3	SPDT	(ON)-OFF-(ON)	16 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	1.236	0.659	\$3.95
<a href="#">2180973</a>	TE Connectivity	A105J1AV2B0	3	SPDT	(ON)-OFF-(ON)	5 @ 125 VAC	Rocker	Red	Black	PC Pin	0.662	0.359	\$0.75
<a href="#">2181722</a>	C&K	7105J1V3QE2	3	SPDT	(ON)-OFF-(ON)	5 @ 125 VAC	Rocker	Red	Black	PC Pin	0.765	0.362	\$2.95
<a href="#">2267111</a>	Mountain Switch	103-7018-EVX	3	SPDT	(ON)-OFF-(ON)	5 @ 125 VAC	Rocker	Red	Black	PC terminal	0.666	0.371	\$1.95
<a href="#">2267055</a>	Mountain Switch	103-7010-EVX	3	SPDT	(ON)-OFF-(ON)	5 @ 125 VAC	Rocker	Red	Black	PC terminal	1.1	0.37	\$2.49
<a href="#">2279159</a>	Jameco Valuepro	RLS-102-A1	3	SPDT	ON-NONE-ON	6 @ 125 VAC	Rocker	Blue	Black	Solder Lug	0.52	0.31	\$1.25
<a href="#">2267167</a>	Mountain Switch	103-7032-EVX	3	SPDT	ON-OFF-(ON)	0.02 @ 125 VAC	Rocker	White	Black	SMD	0.741	0.582	\$0.99
<a href="#">2277695</a>	Apem Components	SY238CD6X-1179	3	SPDT	ON-OFF-(ON)	4 @ 125 VAC	Rocker	Black	Black	PC terminal	0.633	0.436	\$2.95
<a href="#">2267063</a>	Mountain Switch	103-7011-EVX	3	SPDT	ON-OFF-(ON)	5 @ 125 VAC	Paddle	Red	Black	PC terminal RA	1.74	0.365	\$1.95
<a href="#">2267119</a>	Mountain Switch	103-7019-EVX	3	SPDT	ON-OFF-(ON)	5 @ 125 VAC	Paddle	Red	Black	Solder Lug	1.16	0.365	\$1.95



Jameco Part #	Manufacturer	Manufacturer Part #	Pins	Contact Form	Switch Function	Current Rating	Actuator Type	Body Color	Color - Actuator/Cap	Termination Style	Length (inch)	Width (inch)	Price 1
<a href="#">2277759</a>	C&K	E107J2V31KE2	3	SPDT	ON-OFF-(ON)	7.5 @ 125 VAC	Paddle	Red	Black	PC terminal	1.156	0.345	\$1.09
<a href="#">2267175</a>	Mountain Switch	103-7034-EVX	3	SPDT	ON-OFF-ON	0.02 @ 125 VAC	Rocker	White	Black	SMD	0.741	0.582	\$0.99
<a href="#">2182418</a>	Dialight	570-12/574-1212-0104-007	3	SPDT	ON-OFF-ON	0.05 @ 125 VAC	Rocker	Blue	Black	PC Pin	0.627	0.383	\$0.39
<a href="#">2267367</a>	Mountain Switch	103-7066-EVX	3	SPDT	ON-OFF-ON	12 @ 125 VAC	Illuminated Rocker	Black	Red	0.25" Quick Connect	1.81	0.976	\$1.25
<a href="#">316072</a>	Jameco Valuepro	R13-66D-02	3	SPDT	ON-OFF-ON	16 @ 125 VAC	Rocker	Black	Black	0.187" Quick Connect	0.826	0.59	\$1.09
<a href="#">2267591</a>	Mountain Switch	103-R13-238D-01B-EV	3	SPDT	ON-OFF-ON	16 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	1.24	0.728	\$1.09
<a href="#">2267495</a>	Mountain Switch	103-R13-205D3-01-EV	3	SPDT	ON-OFF-ON	16 @ 125 VAC	Rocker	Black	Black	0.25" Quick Connect	1.24	0.728	\$0.89
<a href="#">2267047</a>	Mountain Switch	103-7009-EVX	3	SPDT	ON-OFF-ON	5 @ 125 VAC	Paddle	Red	Black	PC terminal	1.3	0.365	\$1.95
<a href="#">2286103</a>	C&K	E101J2V21BE9	3	SPDT	ON-ON	0.4 @ 20 VAC/DC	Rocker	Red	Gray	PC Pins	1.15	0.345	\$6.95
<a href="#">2180931</a>	TE Connectivity	A101J1ZQO	3	SPDT	ON-ON	5 @ 125 VAC	Rocker	Red	Black	PC Pin	0.659	0.366	\$0.99
<a href="#">2093626</a>	Marquardt Switch	1858.0103	4	DPST	ON-OFF	10 @ 125 VAC	Rocker	Black	Black	Solder Lug	0.83	0.59	\$1.95
<a href="#">2267663</a>	Mountain Switch	103-R13-245C-02-EV	6	DPDT	ON-ON	8 @ 125 VAC	Rocker	Black	Black	0.187" Quick Connect	1.18	1.18	\$1.25
<a href="#">2296511</a>	C&K	7201J1V3QE2	6	SPDT	ON-NONE-ON	5 @ 250 VAC	Rocker	Red	Black	PC terminal	0.5	0.45	\$8.95
<a href="#">2287143</a>	Eaton	SR4MLLFAXXAXXXX	10	DPDT	(ON)-ON-(ON)	12 @ 24 VDC	Rocker	Black	Illuminated Amber	Blade Contact	2.05	0.42	\$14.95
<a href="#">2287127</a>	Eaton	SK4MLLFAXXAXXXX	10	DPDT	ON-ON-ON	12 @ 24 VDC	Rocker	Black	Illuminated Amber	Blade Contact	2.05	0.42	\$19.95
<a href="#">2287119</a>	Eaton	SM4MKKFGXXGXXXX	10	DPST	ON-NONE-(ON)	12 @ 24 VDC	Rocker	Black	Illuminated Green	Blade Contact	2.05	0.42	\$14.95
<a href="#">2287175</a>	Eaton	SMKMLLFAXXAXXXX	10	SPDT	(ON)-NONE-ON	12 @ 24 VDC	Rocker	Black	Illuminated Amber	Blade Contact	2.05	0.42	\$14.95
<a href="#">2287167</a>	Eaton	SMEMKXDGXXXXXXXX	10	SPDT	(ON)-NONE-ON	12 @ 24 VDC	Rocker	Black	Illuminated Green	Blade Contact	2.05	0.42	\$14.95
<a href="#">2287151</a>	Eaton	SAEMKXDGXXXXXXXX	10	SPDT	ON-NONE-ON	12 @ 24 VDC	Rocker	Black	Illuminated Green	Blade Contact	2.05	0.42	\$10.95

Jameco Part #	Manufacturer	Manufacturer Part #	Pins	Contact Form	Switch Function	Current Rating	Actuator Type	Body Color	Color - Actuator/Cap	Termination Style	Length (inch)	Width (inch)	Price 1
<a href="#">2287159</a>	Eaton	SDKMLLFAXXAXXXX	10	SPDT	ON-OFF-ON	12 @ 24 VDC	Rocker	Black	Illuminated Amber	Blade Contact	2.05	0.42	\$19.95
<a href="#">2287135</a>	Eaton	SDKMKKFGXXGXXXX	10	SPDT	ON-OFF-ON	12 @ 24 VDC	Rocker	Black	Illuminated Green	Blade Contact	2.05	0.42	\$12.95