



[Click Here to Request a Large Quantity Quote](#)

[AC to DC Medical Table-Top Regulated Switching Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Primary Output Voltage (VDC)	Output Current (A)	Maximum Output Power (W)	AC Power Cord	Input Voltage (VAC)	Family	Input Frequency	Maximum Input Current (A)	Agency Approvals	Output Connector Type	Price 1
2179606	Globtek	TR9CB2500LCP-Y-MED	6	2.5	15	NOT INCLUDED, RECOMMEND 2271759	100 to 240		50 to 60	0.6	UL/CUL/TUV/CE	Cylindrical Female	\$14.95
230683	Globtek	TR9CE1250LCP-Y-MED(R)	12	1.25	15	NOT INCLUDED, RECOMMEND 2271575	90 to 264		47 to 63	1.5	UL/CSA/TUV/CE	Cylindrical Female	\$29.95
2189759	MEAN WELL	GSM60A12-P1J	12	5	60	NOT INCLUDED, RECOMMEND 2271575	80 to 264	GSM60	47 to 63	1.4		Cylindrical Female	\$21.90
2214230	MEAN WELL	GSM60B12-P1J	12	5	60	NOT INCLUDED, RECOMMEND 2271583	80 to 264		47 to 63	1.4	UL/CUL/TUV/CB/CE/FCC/EN/EAC	Cylindrical Female	\$19.95
2214264	MEAN WELL	GSM60B24-P1J	24	2.5	60	NOT INCLUDED, RECOMMEND 189587	80 to 264	GSM60	47 to 63	1.4	UL/CUL/CE/FCC/TUV/CB	Cylindrical Female	\$21.90
2189783	MEAN WELL	GSM60A24-P1J	24	2.5	60	NOT INCLUDED, RECOMMEND 2271575	80 to 264	GSM60	47 to 63	1.4		Cylindrical Female	\$21.90