



[Click Here to Request a Large Quantity Quote](#)

[Trimmer Potentiometers 3009 Series & Equivalents](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Manufacturer Series	Family	Resistance (Ohms)	Power Rating	Tolerance (%)	Type	Number of Turns	Actuator Type	Price 1
<a href="#">768861</a>	Bourns	89PHR10 (3009P-1-101)	3009	P	100	0.75 W	10	3/4" Rectangular	15	Side Slot	\$1.49
<a href="#">768870</a>	BI Technologies	89PHR2 (3009P-1-202)	3009	P	2000	0.75 W	10	3/4" Rectangular	15	Side Slot	\$1.49
<a href="#">2195489</a>	BI Technologies	89PHR20K (3009P-1-203)	3009	P	20000	0.75 W	10	3/4" Rectangular	20	Side Slot	\$1.49
<a href="#">768909</a>	BI Technologies	89PHR50K (3009P-1-503)	3009	P	50000	0.75 W	10	3/4" Rectangular	15	Side Slot	\$1.49
<a href="#">696124</a>	BI Technologies	89PHR100K (3009P-1-104)	3009	P	100000	0.75 W	10	3/4" Rectangular	15	Side Slot	\$1.49
<a href="#">2178371</a>	BI Technologies	89WHR10 (3009W-1-100)	3009	W	10	0.75 W	10	3/4" Rectangular	15	Side Slot	\$1.49
<a href="#">2178451</a>	BI Technologies	89WHR50 (3009W-1-500)	3009	W	50	0.75 W	10	3/4" Rectangular	15	Side Slot	\$1.09
<a href="#">2195569</a>	BI Technologies	89WHR100 (3009W-1-101)	3009	W	100	0.75 W	10	3/4" Rectangular	20	Side Slot	\$1.09
<a href="#">2195500</a>	BI Technologies	89WHR1K (3009W-1-102)	3009	W	1000	0.75 W	10	3/4" Rectangular	20	Side Slot	\$1.09
<a href="#">2195526</a>	BI Technologies	89WHR50K /3009W-1-503LF	3009	W	50000	0.75 W	10	3/4" Rectangular	20	Side Slot	\$1.09
<a href="#">2198401</a>	BI Technologies	76PR100K (3009W-1-104)	3009	W	100000	0.75 W	10	3/4" Rectangular	15	Side Slot	\$1.09
<a href="#">2195833</a>	BI Technologies	89XHR100-274A(3009x-1-100)	3009	X	100	0.75 W	10	3/4" Rectangular	20	Side Slot, .32"L Shaft	\$1.09
<a href="#">2195577</a>	BI Technologies	89XHR100 (3009Y-1-101)	3009	Y	100	0.75 W	10	3/4" Rectangular	20	Side Slot	\$1.09
<a href="#">2195534</a>	BI Technologies	89XHR500 (3009Y-1-501)	3009	Y	500	0.75 W	10	3/4" Rectangular	20	Side Slot	\$1.09