



[Click Here to Request a Large Quantity Quote](#)

[Trimmer Potentiometers 3266 Series & Equivalents](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Manufacturer Series	Family	Resistance (Ohms)	Power Rating	Tolerance (%)	Type	Number of Turns	Actuator Type	Price 1
2291663	Jameco Valuepro	3266P-1-102VP/LF	3266	P	1000	0.25 W	10	1/4" Square	12	Side Slot	\$2.95
2291671	Jameco Valuepro	3266P-1-502VP/LF	3266	P	5000	0.25 W	10	1/4" Square	12	Side Slot	\$2.95
769098	Spectrol/Vishay Corporation	64PR10K (3266P-1-103LF)	3266	P	10000	0.25 W	10	1/4" Square	12	Side Slot	\$2.95
1156226	BI Technologies	64PR100K (3266P-1-104)	3266	P	100000	0.25 W	10	1/4" Square	12	Side Slot	\$2.95
2194881	BI Technologies	64PR200K (3266P-1-204VP)	3266	P	200000	0.25 W	10	1/4" Square	12	Side Slot	\$2.95
2200727	BI Technologies	64WR50 (3266W-1-500VP)	3266	W	50	0.25 W	10	1/4" Square	12	Top Slot	\$2.95
254626	BI Technologies	64WR200 (3266W-1-201)	3266	W	200	0.25 W	10	1/4" Square	12	Top Slot	\$2.95
2194945	BI Technologies	64WR500 (3266W-1-501)	3266	W	500	0.25 W	10	1/4" Square	12	Top Slot	\$2.95
696351	BI Technologies	3266W-1-102LF (64WR1K)	3266	W	1000	0.25 W	10	1/4" Square	12	Top Slot	\$2.95
2194929	BI Technologies	3266W-1-202K(64WR2K)	3266	W	2000	0.25 W	10	1/4" Square	12	Top Slot	\$2.95
254669	Jameco Valuepro	3266W-1-502VP(64WR5K)	3266	W	5000	0.25 W	10	1/4" Square	12	Top Slot	\$2.95
254677	Jameco Valuepro	860W-1-103/3266W-1-103VP	3266	W	10000	0.25 W	10	1/4" Square	12	Top Slot	\$2.95
696415	BI Technologies	3266W-1-203VP(64WR20K)	3266	W	20000	0.25 W	10	1/4" Square	12	Top Slot	\$2.95
254714	BI Technologies	64WR100K (3266W-1-104VP)	3266	W	100000	0.25 W	10	1/4" Square	12	Top Slot	\$2.95
696423	BI Technologies	64WR200K (3266W-1-204)	3266	W	200000	0.25 W	10	1/4" Square	12	Top Slot	\$2.95

Jameco Part #	Manufacturer	Manufacturer Part #	Manufacturer Series	Family	Resistance (Ohms)	Power Rating	Tolerance (%)	Type	Number of Turns	Actuator Type	Price 1
254730	BI Technologies	64WR500K (3266W-1-504)	3266	W	500000	0.25 W	10	1/4" Square	12	Top Slot	\$2.95
254748	Jameco Valuepro	3266W-1-105-VP	3266	W	1 Meg	0.25 W	10	1/4" Square	12	Top Slot	\$2.95
696520	BI Technologies	64XR500 (3266X-1-501VP)	3266	X	500	0.25 W	10	1/4" Square	12	Side Slot	\$2.95
1156314	BI Technologies	3266X-1-102VP(64XR1K)	3266	X	1000	0.25 W	10	1/4" Square	12	Side Slot	\$2.95
696474	BI Technologies	64XR25K/3266X-1-253VP	3266	X	1000	0.25 W	10	1/4" Square	12	Side Slot	\$2.49
1156381	Bourns	3266X-1-502LF	3266	X	5000	0.25 W	10	1/4" Square	12	Side Slot	\$2.95
1156331	BI Technologies	3266X-1-103VP (64XR10)	3266	X	10000	0.25 W	10	1/4" Square	12	Side Slot	\$2.95
696546	BI Technologies	64XR50K (3266X-1-503)	3266	X	50000	0.25 W	10	1/4" Square	12	Side Slot	\$2.95
769223	BI Technologies	64XR200K (3266X-1-204)	3266	X	200000	0.25 W	10	1/4" Square	12	Side Slot	\$2.95
2194953	BI Technologies	64XR250K (3266X-1-254VP)	3266	X	250000	0.25 W	10	1/4" Square	12	Side Slot	\$2.95
2285575	Bourns	3266X-1-504LF	3266	X	500000	0.25 W	10	1/4" Square	12	Side Slot	\$2.95
2194988	BI Technologies	64YR20 (3266Y-1-200)	3266	Y	20	0.25 W	10	1/4" Square	12	Top Slot	\$2.95
2194961	BI Technologies	64YR100 (3266Y-1-101)	3266	Y	100	0.25 W	10	1/4" Square	12	Top Slot	\$2.95
2199156	BI Technologies	64YR200 (3266Y-1-201VP)	3266	Y	200	0.25 W	10	1/4" Square	12	Top Slot	\$2.95
2199148	BI Technologies	64YR500 (3266P-1-501VP)	3266	Y	500	0.25 W	10	1/4" Square	12	Top Slot	\$2.95
2194970	BI Technologies	64YR25K (3266Y-1-253VP)	3266	Y	25000	0.25 W	10	1/4" Square	12	Top Slot	\$2.95
1156411	Bourns	64ZR1K (3266Z-1-102)	3266	Z	1000	0.25 W	10	1/4" Square	12	Side Slot	\$2.95