

**JAMECO ReliaPro**


## Battery Holders

\* Web Code: UAB

Eliminate battery mounting problems in portable DC power applications and products. These holders are made from special materials that maintain retention properties longer than conventional holders. They can come with leads, or attached to battery holders. \* Order in multiples of 10

Part No.	Cross Ref. No.	*Mfr. Fig.	No. of Cells	Connector	Sides	Features	1	10	100	500
216283	BH-421-1A	JRP	3	2-AAA	Wires	Single	\$.59	\$.55	\$.49	\$.39
216303	BH-431-1A	JRP	5	3-AAA	Wires	Single	.89	.79	.72	.59
216312	SBH-431-1AS	JRP	5	3-AAA	Wires	Single w/ cover & switch	.95	.85	.75	—
216339	SBH-441-AS	JRP	10	4-AAA	Wires	Single w/ cover & switch	1.45	1.29	1.19	.89
216072	BH-311-2A	JRP	1	1-AA	Wires	Single aluminum	1.05	.95	.85	.75
643954	139	KEY	2	1-AA	Tabs	Single	.75	.69	.59	.55
216081	BH-321-2A	JRP	3	2-AA	Wires	Single	.75	.69	.59	.55
216099	BH-321-4A	JRP	3	2-AA	Wires	Single w/ mounting tabs	.99	.89	.79	.65
216102	SBH-321-2A	JRP	4	2-AA	Wires	Single w/ cover, no switch	.75	.69	.59	.55
216120	SBH-321-1AS	JRP	4	2-AA	Wires	Single w/ cover & switch	.89	.79	.72	.65
216136	BH-331-A	JRP	5	3-AA	Wires	Single	.85	.77	.69	.62
216144	SBH-331-AS	JRP	6	3-AA	Wires	Single w/ cover & switch	.79	.69	.65	.59
216152	BH-341-2A	JRP	7	4-AA	Wires	Single	1.15	1.05	.95	.85
105858	BH-PC-3	JRP	8	4-AA	Wires	Single Wires w/ connector	.95	.85	.79	.64
216179	BH-343-1A	JRP	9	4-AA	Wires	Dual	.75	.69	.59	.55
216187	SBH-341-1AS	JRP	10	4-AA	Wires	Single w/ cover & switch	1.05	.95	.85	.75
216216	BH-363-A	JRP	11	6-AA	Wires	Dual	.75	.69	.59	—
216223	BH-364-A	JRP	11	6-AA	Wires	Single	.85	.77	.69	.62
216232	BH-363-B	JRP	12	6-AA	Snaps	Dual	1.09	.99	.89	.69
216240	BH-383-A	JRP	13	8-AA	Wires	Dual	1.09	.99	.89	.69
216267	BH-383-B	JRP	13	8-AA	Snaps	Dual	1.19	1.09	.99	.79
216259	BH-382-B	JRP	14	8-AA	Snaps	Dual	1.35	1.19	1.09	.79
216292	SBH-421-AS	JRP	3	2-AAA	Wires	Single w/ cover & switch	.65	.59	.55	—
216363	BH-242-1A	JRP	15	4-C	Wires	Single	1.09	.99	.89	.69
216371	BH-111-1A	JRP	1	1-D	Wires	Single	.69	.65	.59	.49
216390	BH-121-1A	JRP	3	2-D	Wires	Single	1.19	1.09	.95	.79
216401	BH-142-A	JRP	15	4-D	Wires	Single	1.35	1.19	1.09	.89
216427	BH-9V-A	JRP	16	1-9V	Wires	Single	.75	.69	.59	.55
11280	A104-R	JRP	19	1-9V	Wires	Single 3"L, 26AWG, snaps	.39	.35	.29	.25
105794	GBH-1009-R	JRP	20	1-9V	Wires	Single Metal holder	.35	.32	.29	.25
1949488	BAT-SNAP-4	♦	21	1-9V	Wires	Single 4"L, 26AWG, snaps	* .17	.14	.10	—
109154	BC6-R	JRP	21	1-9V	Wires	Single 6"L, 26AWG, snaps	.29	.26	.23	.19
216452	SBS-IR-1-R	JRP	22	1-9V	Wires	Single 6"L, 26AWG, snaps	.35	.32	.29	.25
101470	A102-R	JRP	21	1-9V	Wires	Single 10"L, 26AWG, snaps	.35	.32	.29	.25
236996	103	KEY	17	1-CR2032	PC mount	Coin cell	1.65	1.49	1.35	1.19
356434	17002-00603	JRP	18	1-CR2032	PC mount	Coin cell	.79	.69	.65	.59
38543	2S2325	JRP	17	1-CR2354 or 2-CR2325	PC mount	Coin cell	.89	.79	.72	.59

Ⓜ Battery holder used in many personal computers Ⓜ Blue Part No. = Limited Quantity Available




**JAMECO ReliaPro**

## Rechargeable Battery Packs

\* Web Code: LAA

Part No.	Fig.	Volt	Cell	Size (L x Dia.)	Type	mAh	Connection	1	10	25
299090	1	3.6	AA Single	1.92" x 0.56" (48.8mm x 14.2mm)	NiCd	700	Lead wire	\$8.45	\$7.49	\$6.75
298821	2	3.6	D Single	2.36" x 1.26" (59.9mm x 32.0mm)	NiCd	5000	Solder tab	19.95	17.95	—
299621	3	4.8	D Single	2.36" x 1.26" (59.9mm x 32.0mm)	NiCd	5000	Lead wire	39.95	—	—
298724	3	4.8	SC Single	1.65" x 0.86" (41.1mm x 21.8mm)	NiCd	2200	Solder tab	13.65	12.29	11.39
299680	4	6.0	D Single	2.36" x 1.26" (59.9mm x 32.0mm)	NiCd	5000	Lead wire	46.95	42.25	37.95
299461	5	9.6	SC Single	1.65" x 0.86" (41.1mm x 21.8mm)	NiCd	2200	Lead wire	29.95	26.95	24.25
299495	6	9.6	SC Single	1.65" x 0.86" (41.1mm x 21.8mm)	NiCd	2200	Lead wire	24.95	22.45	—



Ⓜ Blue Part No. = Limited Quantity Available

**MW**  
MELAN WELLS

## 300, 360 & 1000-Watt Single Output Lead Acid Battery Charger

\* Web Code: ABC

- Input: 115VAC/230VAC @ 47-64Hz (switch-selectable)
- **1952409/1952417/1954332/1954341/1954359:** with built-in passive PFC function
- Overload, short-circuit, reverse polarity, over voltage, over temperature protection
- **1952409/1954893:** Cooling by free-air convection;
- **1952417/1954308/1954316/1954324:** Fan on/off control (depending on charging current) • Charger for lead acid batteries
- **1954316/1954324:** Size: 10.0"L x 5.3"W x 1.9"H, Weight: 3.3 lbs.
- **1952409/1954893/1952417/1954308:** Size: 9.3"L x 5.3"W x 1.9"H • Weight: 3.3 lbs.
- **1954332/1954341/1954359:** Size: 11.8"L x 7.2"W x 2.8"H, Weight: 7.7 lbs.



1952409

Part No.	Mfr. Part No.	Watts	Boost Charge Voltage	Float Charge Voltage	Recommended Battery Capacity (AMP Hours)	Pricing	
						1	10
1952409	PB-300P-12	300	14.4	13.6	80-200	\$104.95	\$99.95
1954893	PB-300N-24	300	28.8	27.2	40-125	104.95	99.95
1952417	PB-360P-12	360	14.4	16.6	80-200	109.95	104.45
1954308	PB-360N-12	360	14.4	13.6	80-200	109.95	104.45
1954316	PB-360N-24	360	28.8	27.2	40-125	129.95	116.95
1954324	PB-360N-48	360	57.6	54.4	20-65	129.95	116.95
1954332	PB-1000-12	1000	14.4	13.8	200-600	399.95	359.95
1954341	PB-1000-24	1000	28.8	27.6	120-350	399.95	359.95
1954359	PB-1000-48	1000	57.6	55.2	60-175	399.95	359.95

\* JRP = Jameco ReliaPro | KEY = Keystone | ♦ Manufacturer Varies

\* For Complete Specs & Additional Product Listings Search [www.Jameco.com/More](http://www.Jameco.com/More) and Enter Web Code Listed Above

3 LEVELS OF SAVINGS  
NAME BRANDS HOUSE BRANDS FACTORY OVERRUN

Order by Phone 24/7 at 1-800-831-4242 or Online at [www.Jameco.com](http://www.Jameco.com)

# Batteries & Battery Chargers

3 LEVELS OF SAVINGS  
NAME BRANDS HOUSE BRANDS FACTORY OVERRUN

## Lithium, NiCd & NiMH Batteries

Save 10% or more on most batteries!

Applications: personal computers, workstations, test equipment, feature telephones, copiers, fax machines, video scramblers/descramblers and remotes.



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6



Fig. 7



Fig. 8

### Lithium

\* Web Code: GCF

Part No.	Product No.	Manufacturer	Fig.	Size	Volts	mAh	Terminals/Connection	Dimensions	1	10	25
673627	NB4414/F9D	Panasonic	5	Coin cell	2.0	1.0	4.8mm body w/ tabs (2)	0.18" Dia. x 0.06" Thick	\$0.59	\$0.49	\$0.45
673601	NBL621/F9DE	Various	—	Coin cell	2.0	4.0	Vertical PC mount	0.27" Dia. x 0.10" Thick	1.49	1.25	.99
1950665	CR2016	Various	5	Coin cell	3	90	20mm body w/ tabs (2)	0.80" Dia. x 0.07" Thick	.79	.65	.49
11789	CR2325	Various	5	Coin cell	3	165	Clock/memory/watch	0.91" Dia. x 0.13" Thick	1.79	1.59	1.45
14162	CR2032	Various	5	Coin cell	3	180	Clock/memory/watch	0.79" Dia. x 0.13" Thick	1.25	1.09	.99
1585451	DL2032	Duracell	5	Coin cell	3	180	Clock/memory/watch	0.79" Dia. x 0.13" Thick	1.49	1.35	1.19
1954631	BR2330	Various	5	Coin cell	3	255	Clock/memory/watch (w/ legs)	0.90" Dia. x 0.14" Thick	1.75	1.59	1.39
689071	DL2450	Various	5	Coin cell	3	600	Clock/memory/watch	0.95" Dia. x 0.18" Thick	2.79	2.25	1.95
126754	TL5101S	Tadiron	6	Sub-AA	3.6	850	Macintosh®	0.95" L x 0.56" Dia.	4.95	4.45	3.95
240266	ER14250	ReliaPro	7	Sub-AA	3.6	1000	Consumer tip	1.00" L x 0.55" Dia.	4.25	3.95	3.55
263898	ER14250	ReliaPro	8	Sub-AA	3.6	1000	With axial leads	1.00" L x 0.55" Dia.	4.75	4.25	3.85
33371	TL5101P	Tadiron	2	1/2AA	3.6	850	Barrel w/ leads (clock/mem.)	0.93" L x 0.56" Dia.	6.25	5.65	4.95
673635	CA1/2AA	Various	8	1/2 AA	3	950	Barrel w/ leads (2)	1.0" L x 0.58" Dia.	1.95	1.75	1.49
33398	TL5104P	Tadiron	3	AA	3.6	1900	Barrel w/ leads (clock/mem.)	1.88" L x 0.56" Dia.	6.95	6.25	5.65
146114	TL2100S	Various	4	AA	3.6	1900	Barrel pressure (clock/mem.)	1.91" L x 0.56" Dia.	6.95	6.25	5.65
240303	ER14505	ReliaPro	9	AA	3.6	2400	Consumer tip	2.00" L x 0.55" Dia.	5.95	5.35	4.95
240160	ER26500	ReliaPro	10	C	3.6	8500	Consumer tip	2.00" L x 1.02" Dia.	9.95	8.95	7.95
240151	ER34615	ReliaPro	11	D	3.6	16,500	Consumer tip	2.40" L x 1.34" Dia.	14.95	14.49	13.95
240258	CR123A	ReliaPro	1	—	3	1300	Photo/computer	1.36" L x 0.65" Dia.	2.75	2.49	2.25
263935	ER14505	ReliaPro	12	AA	3.6	2100	With solder tabs	2.00" L x 0.55" Dia.	5.95	5.35	4.95



Fig. 9



Fig. 10



Fig. 11



Fig. 12



Fig. 13



Fig. 14



Fig. 15



Fig. 16



Fig. 17



Fig. 18

### NiCd - Rechargeable

Part No.	Product No.	Manufacturer	Fig.	Size	Volts	mAh	Terminals/Connection	Dimensions	1	10	25
261657	AA-700-CT	ReliaPro	13	AA	1.2	700	Consumer tip	1.90" L x 0.55" Dia.	\$1.69	\$1.49	\$1.35
244515	AA-1000-CT	ReliaPro	13	AA	1.2	1000	Consumer tip	1.90" L x 0.55" Dia.	2.75	2.49	2.25
126720	351FT	Various	14	N/A	3.6	60	2-lead (pin), barrel	0.72" L x 0.61" Dia.	4.49	3.95	3.55
119116	3/V60R	Dantona	14	N/A	3.6	60	3-lead (pin), barrel	0.72" L x 0.61" Dia.	3.35	2.95	2.65
101653	NA101-1	Various	15	N/A	3.6	60	2-lead (eyelet), barrel	0.72" L x 0.61" Dia.	3.95	3.55	3.19

### NiMH - Rechargeable

Part No.	Product No.	Manufacturer	Fig.	Size	Volts	mAh	Terminals/Connection	Dimensions	1	10	25
231095	AAA-750NM	Dantona	18	AAA	1.2	600	Consumer tip	1.70" L x 0.40" Dia.	\$3.45	\$3.09	\$2.79
244822	AA-1800-CT	ReliaPro	16	AA	1.2	1800	Consumer tip	1.90" L x 0.55" Dia.	3.55	3.19	2.89
231087	AA-1800NM	Dantona	19	AA	1.2	1600	Consumer tip	1.90" L x 1.30" Dia.	3.95	3.55	3.19
244620	9V-200	Bao Tong USA	17	9V	9	200	Snaps	1.94" L x 0.65" Dia.	9.75	8.75	7.95
231108	9V-8.4NM	Dantona	21	9V	9	150	Snaps	1.04" L x 0.61" Dia. x 1.80" H	10.95	9.95	8.95
231124	D-900NM	Dantona	20	D	1.2	9000	Consumer tip	2.30" L x 1.30" Dia.	15.95	14.35	12.95

## Lead Acid Batteries

- Use with UPS Backup Systems, Security Fire Alarms, Wheel Chairs, Scooters
- Sealed • UL approved • Rechargeable
- Two-year warranty



Lead Acid Chargers on page 195

\* Web Code: LBR



264014



264031



318924



264057



264065



264073

Part No.	Mfr. Part No.	Nominal Voltage	Amp-Hrs.	Cross Reference				Terminal Size	Size (L" x W" x H")	Wt. (lbs.)	Pricing	
				Panasonic	YUASA	Eagle Picher	Tempest				1	10
138692	K9120-REVC	6	1.3	Honeywell	—	—	—	Quick connect 0.187"	2.1 x 1.0 x 3.8	0.7	\$3.95	\$3.55
264014	TY-6-4.5	6	4.5	LCR6VP	NP4-6	CF16V4	TR-4-6	Quick connect 0.187"	2.8 x 1.9 x 4.0	1.9	11.95	10.75
317024	LA-TY-6-12	6	12.0	—	—	—	—	Quick connect 0.187"	5.9 x 1.9 x 3.7	4.6	19.95	17.95
318844	LA-TY-12-1.2	12	1.2	—	—	—	—	Quick connect 0.187"	3.8 x 1.7 x 2.1	1.3	14.95	13.45
264031	TY-12-2.3	12	2.3	LCR12V2.2P	NP2.3-12	CF12V1.5	TR2.3-12	Quick connect 0.187"	7.0 x 1.3 x 2.4	2.1	19.95	17.95
318924	LA-TY-12-3.2	12	3.2	—	—	—	—	Quick connect 0.187"	5.3 x 2.7 x 2.4	3.1	22.95	20.65
264057	TY-12-7.5	12	7.5	LCR12V7.2BP	NP712	CFM12V65	TR7.5-12	Quick connect 0.187"	5.9 x 2.6 x 3.7	5.6	22.95	20.65
264065	TY-12-12	12	12.0	PS12120	—	CFM12V12	TR12-12	Quick connect 0.187"	5.9 x 3.9 x 3.9	9.0	39.95	35.95
264073	TY-12-18	12	18.0	LCR12V17BP	NPG18-12	CF12V18	TR18-12	Quick connect 0.472"	7.1 x 3.0 x 6.6	13.3	47.95	42.95
318852	LA-TY-12-35	12	35.0	—	—	—	—	Nut & bolt	7.6 x 5.1 x 6.3	27.6	74.95	67.45

## Compact Charger with Two 9V NiMH Batteries

- 120VAC 2-watt wall mount • LED charge indicator per battery
- Includes two 160mAh 9V batteries
- Trickle charges overnight at 16mA per battery



Part No.	Mfr. Part No.	1	10	25
2081684	1000-077	\$9.95	\$8.95	\$7.95



## Universal NiCd/NiMH Charger

- Recharge batteries individually or as a group
- Fast charging in the specified period with an automatic switch for trickle charge

\* Web Code: PBF

Part No.	Mfr. Part No.	Compatible Battery	1	10	25
231132	CHG-6P	AAA, AA, C, D, 9V	\$19.95	\$17.95	\$16.15



RoHS compliant product + This product is available in both RoHS and non-RoHS versions. Add an "R" before part number for RoHS version. Details on page 189.

## Energizer®, Duracell® & Rayovac® Alkaline Batteries



Alkaline			1	10
Part No.	Size			
198731	9-volt Energizer®	.....	\$2.05	\$1.85
198791	9-volt Duracell®	.....	2.95	2.65
150965	4.5V @ 600mAH Rayovac®	.....	9.95	8.95
215845	3.6V D-cell Energizer®	.....	1.15	1.05

Part No.	Size	Min	1	40	100
198707	AA Energizer®†	4	\$.79	\$.69	\$.65
115432	AAA Duracell®††	2	.....	.69	.59
198715	AAA Energizer®†	4	.....	.69	.59

†Sold in multiples of 4 ††Sold in multiples of 2

\* Web Code: NBF

Energizer® and the Energizer Bunny® are registered trademarks of the Eveready Battery Company, Inc.

## Silver Oxide and Zinc Chloride Batteries

Applications: personal computers, workstations, test equipment, feature telephones, copiers, fax machines, video scramblers/descramblers and remotes.



Part No.	Cross Ref.	Description	1	10
140783	357	Silver oxide, button	\$1.55	\$1.39
151095	GF6F22	Zinc chloride, 9V	1.35	1.19

## Compact Battery Tester

Simply lift the swivel arm of this battery between the contacts and it will provide you a voltage measurement of your batteries. Tests AAA, AA, C, D, 9V and button cell batteries.



Part No.	Description	1	10
239556	Compact battery tester.....	\$3.75	\$3.39

## velleman

## Analog Panel Meters

• Includes mounting hardware • 316507: Includes current shunt

Part No.	Mfr. P/N	Range	Size (W"xH"xD")	1	10
316603	AVM6015	0 - 15VDC	2.4 x 1.8 x 1.3	\$9.95	\$8.95
316671	AVM7015	0 - 15VDC	2.8 x 2.4 x 1.4	9.95	8.95
316638	AVM6030	0 - 30VDC	2.4 x 1.8 x 1.3	9.95	8.95
316654	AVM7030	0 - 30VDC	2.8 x 2.4 x 1.4	9.95	8.95
316718	AVM60150	0 - 150VAC	2.4 x 1.8 x 1.3	9.95	8.95
316785	AVM60300	0 - 300VAC	2.4 x 1.8 x 1.3	9.95	8.95
315301	AIM60005	0 - 50µA	2.4 x 1.8 x 1.3	9.95	8.95
316523	AIM6050	0 - 50mA	2.4 x 1.8 x 1.3	9.95	8.95
316486	AIM60100	0 - 100mA	2.4 x 1.8 x 1.3	9.95	8.95
316558	AIM60500	0 - 500mA	2.4 x 1.8 x 1.3	9.95	8.95
316566	AIM60500	0 - 5A	2.4 x 1.8 x 1.3	9.95	8.95
316582	AIM705000	0 - 5A	2.8 x 2.4 x 1.4	9.95	8.95
316494	AIM6010A	0 - 10A	2.4 x 1.8 x 1.3	9.95	8.95
316507	AIM6030A	0 - 30A	2.4 x 1.8 x 1.3	12.95	11.65

\* Web Code: YBQ



316603



316523

## 0.6" High 3½ & 4½-Digit LCD Digital Panel Meters



108388      175951      146835      123140

- Input ranges: 200mV, 20V, 200V, 500V
- Accuracy: ±0.5%
- Supply voltage: 8-12VDC (recommend 9V battery P/N 151095, above right)
- Automatic polarity indication
- Input impedance: >100MΩ
- Size: 2.7"W x 1.7"H

\* Web Code: WBU

Part No.	Cross Ref. No.	Description	1	10	25
108388	PM-428	3½ digit (no bezel, snap mount) .....	\$10.95	\$9.95	\$8.95
175951	PM-128	3½ digit (bezel, screw mount) .....	12.95	11.65	10.49
146835	PM-188BL	3½ digit (with backlight display) .....	14.95	13.45	11.95
123140	PM-328	4½ digit (bezel, screw mount) .....	29.95	26.95	24.25


## 60mm Solar Panel

Photovoltaic Mini Module

- Clear coat plastic
- Voltage output: 4.7VDC to 5VDC
- Power output: 0.25W max.
- Size: 2.36" L x 2.36" W x 0.1" Thick
- Material: Copper Indium Diselenide

Part No.	Description	1	10	100
1928142	Solar panel .....	\$7.95	\$6.95	\$6.25

\* Web Code: AEK




## PowerFilm. Flexible Thin Film Solar Modules

\* Web Code: QEM

### Wireless Electronics Series

The Wireless Electronics Series offers a new opportunity to solve the old problem of limited power for wireless electronics in portable and remote applications. This module is lightweight, paper thin and durable.

Part No.	Mfr. Part No.	Operating Voltage	Operating Current (mA)	Size (L x W x T)		Pricing		
				Inches	mm	1	10	100
227985	SP3-37	3.0	22	2.5 x 1.5 x .01	64 x 37 x 0.2	\$3.95	\$3.49	\$3.15
227993	TX3-25	3.0	25	4.5 x 1.0 x .01	114 x 25 x 0.2	3.95	3.49	3.15
171061	MP3-37	3.0	50	4.5 x 1.5 x .01	114 x 37 x 0.2	5.95	5.35	4.79
228013	MPT3.6-75	3.6	50	2.9 x 3.0 x .01	74 x 75 x 0.2	7.95	6.95	6.45
228030	SP4.2-37	4.2	22	3.3 x 1.5 x .01	84 x 37 x 0.2	5.95	5.35	4.79
228056	MPT4.8-150	4.8	100	3.7 x 5.9 x .01	94 x 150 x 0.2	17.95	16.95	15.25
228072	MPT6-150	6.0	100	4.5 x 5.9 x .01	114 x 150 x 0.2	19.95	17.95	15.95
228099	MP7.2-150	7.2	200	10 x 5.9 x .02	253 x 150 x 0.6	39.95	35.95	31.95
228101	MPT15-75	15.4	50	10 x 3.0 x .02	253 x 75 x 0.6	19.95	17.95	15.95
228110	MPT15-150	15.4	100	10 x 5.9 x .02	253 x 150 x 0.6	39.95	35.95	31.95



228013

### WeatherPro Series

The right choice for permanent outdoor applications that are directly exposed to the elements. These modules features rugged construction, a UV-stabilized surface, an extra edge seal for weather protection, and tin-coated copper leads that extend from the module.


Part No.	Mfr. Part No.	Operating Voltage	Operating Current (mA)	Size (L x W x T)		Pricing		
				Inches	mm	1	10	100
228161	P7.2-75	7.2	100	10.3 x 3.9 x .04	270 x 100 x 1.1	\$34.95	\$31.49	\$28.25
228179	P7.2-150	7.2	200	10.3 x 6.9 x .04	270 x 175 x 1.1	49.95	44.95	39.95
228195	PT15-150	15.4	100	10.3 x 6.9 x .04	270 x 175 x 1.1	54.95	49.45	44.49
228208	PT15-300	15.4	200	10.3 x 12.8 x .04	270 x 325 x 1.1	99.95	89.95	79.95

228161

## Mini-Panel Solar Cells

Ready to Use! No Soldering

Encapsulated mini-panels utilize solar cells similar to those that power our satellites in space, yet they are safe and simple to use. Mini-panels allow for handling without the normal breakage and cell damage associated with fragile solar cells. 6" red/black lead wires attached. Modules may be connected to create different outputs.



200221



215327

- Connection: lead

\* Web Code: MPS

Part No.	Ref. No.	VDC @ mA	Size (L x W)	1	10
200221	SOL4	2.0 @ 200	3.0" x 3.7" ...	\$10.95	\$9.95
215319	4-3.0-100	3.0 @ 100	3.8" x 2.5" .....	11.95	10.95
215327	4-6.0-50	6.0 @ 50	3.8" x 2.5" .....	15.95	14.49

## Quick and Easy Search

Our enhanced website offers thousands of datasheets and photos to assist you in finding the products you need.

\* For Complete Specs & Additional Product Listings Search [www.Jameco.com/More](http://www.Jameco.com/More) and Enter Web Code Listed Above