

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 177949



BRIDGE RECTIFIERS & DIODES

General Purpose Diodes

Series	I _{AV}	Voltage									Outline
		50	100	200	300	400	500	600	800	1000	
1N4000	1	1N4001	1N4002	1N4003		1N4004		1N4005	1N4006	1N4007	DO-41
1N5391	1.5	1N5391	1N5392	1N5393	1N5394	1N5395	1N5396	1N5397	1N5398	1N5399	DO-15
1N5400	3	1N5400	1N5401	1N5402	1N5403	1N5404	1N5405	1N5406	1N5407	1N5408	DO-201AD
S1	1	S1A	S1B	S1D		S1G		S1J	S1K	S1M	SMA
S2	1.5	S2A	S2B	S2D		S2G		S2J	S2K	S2M	SMB
S3	3	S3A	S3B	S3D		S3G		S3J	S3K	S3M	SMC
PX6A	6	PX6A01	PX6A02	PX6A03		PX6A04		PX6A05	PX6A06	PX6A07	R-6

Fast Recovery Diodes

Series	I _{AV}	Voltage								Outline
		50	100	150	200	400	600	800	1000	
ES1*	1	ES1A	ES1B	ES1C	ES1D	ES1G				SMA
UF1**	1	UF1001	UF1002		UF1003	UF1004	UF1005	UF1006	UF1007	DO-41
US1**	1	US1A	US1B		US1D	US1G	US1J			SMA
RS1	1	RS1A	RS1B		RS1D	RS1G	RS1J	RS1K	RS1M	SMA
1N4933***	1	1N4933	1N4934		1N4935	1N4936	1N4937			DO-41
PR1000***	1	PR1001	PR1002		PR1003	PR1004	PR1005	PR1006	PR1007	DO-41
RS2***	1.5	RS2A	RS2B		RS2D	RS2G	RS2J	RS2K	RS2M	SMB
ES2*	2	ES2A	ES2B	ES2C	ES2D					SMB
ES3*	3	ES3A	ES3B		ES3D					SMC
UF3**	3	UF3001	UF3002		UF3003	UF3004	UF3005	UF3006	UF3007	DO-201AD
PR3000***	3	PR3001	PR3002		PR3003	PR3004	PR3005	PR3006	PR3007	DO-201AD
RS3***	3	RS3A	RS3B		RS3D	RS3G	RS3J	RS3K	RS3M	SMC
PR6000***	6	PR6001	PR6002		PR6003	PR6004	PR6005	PR6006	PR6007	R-6

* = trr(nS) 20-25nS

** = trr(nS) 50-75nS

*** = trr(nS) 150-500nS

Schottky Diodes

Series	I _{AV}	Voltage					Outline
		20	30	40	50	60	
B1	1	B120	B130	B140	B150	B160	SMA
B2	2	B220	B230	B240	B250	B260	SMB
B3	3	B320	B330	B340	B350	B360	SMC
1N5817 - 19	1	1N5817	1N5818	1N5819			DO-41
1N5820 - 22	3	1N5820	1N5821	1N5822			DO-201AD