




JAMECO ValuePro

Miniature Toggle Switches

* Web Code: PAJ

• Mounting hole diameter: 1/4"
Includes: Mounting hardware



Part No.	Mfr.	Product No.	Fig.	Pins	Contact Form () Momentary	Contact Rating (A @ VAC)	Dimensions (L" x W" x D")	Lead Spacing			Terminal Type	Lever Type	Pricing		
								A"	B"	C"			1	10	100
317228	JVP	1MS9T1B1M1QE	1	2	SPST on-off	5 @ 120 & 2 @ 250	.50 x .27 x .35	—	0.190	—	Solder lugs	Round	\$1.95	\$1.75	\$1.59
76523	JVP	JMT113	1	2	SPST on-off	6 @ 125 & 3 @ 250	.52 x .32 x .38	—	0.185	—	Solder lugs	Round	1.39	1.25	1.09
317287	JVP	1MS9T6B11M1QE	2	3	SPST on-off	5 @ 120 & 2 @ 250	.50 x .27 x .35	—	0.185	—	Solder lugs	Flat	1.49	1.35	1.19
777768	C&K	T101MHZQE	1	3	SPDT on-on	3 @ 120	.32 x .20 x .34	—	0.100	—	Solder lugs	Round	5.95	5.49	4.95
26332	JVP	MPC123R	1	3	SPDT on-on	6 @ 125 & 3 @ 250	.52 x .32 x .37	—	0.185	—	PC straight	Round	1.89	1.75	1.49
21936	JVP	JMT123	1	3	SPDT on-on	6 @ 125 & 3 @ 250	.52 x .32 x .38	—	0.185	—	Solder lugs	Round	1.55	1.25	1.09
75854	JVP	SWM132	1	3	SPDT on-on	6 @ 125 & 3 @ 250	.52 x .32 x .38	—	0.185	—	Solder lugs	Round	1.55	1.25	1.09
317236	JVP	1MS1T1B1M1QE	2	3	SPDT on-on	5 @ 120 & 2 @ 250	.50 x .27 x .35	—	0.185	—	Solder lugs	Round	1.39	1.25	1.09
317295	JVP	1MS1T6B11M1QE	2	3	SPDT on-on	5 @ 120 & 2 @ 250	.50 x .27 x .35	—	0.185	—	Solder lugs	Flat	1.49	1.35	1.09
317279	JVP	1MS2T1B1M1QE	2	3	SPDT on-(on)	5 @ 120 & 2 @ 250	.50 x .27 x .35	—	0.185	—	Solder lugs	Round	1.75	1.59	1.39
317332	JVP	1MS2T6B11M1QE	2	3	SPDT on-(on)	5 @ 120 & 2 @ 250	.50 x .27 x .35	—	0.185	—	Solder lugs	Flat	1.75	1.59	1.39
22833	JVP	MS102F1-R	2	3	SPDT on-on	6 @ 125 & 3 @ 250	.52 x .28 x .36	—	0.185	—	Solder lugs	Flat	1.49	1.35	1.09
71597	JVP	SWM148	3	3	SPDT on-on	6 @ 125 & 3 @ 250	.52 x .32 x .38	—	0.185	0.20	PC right angle	Round	.99	.89	.79
75871	JVP	SWM145	4	3	SPDT on-on	6 @ 125 & 3 @ 250	.52 x .32 x .38	—	0.185	0.20	PC right angle	Round	1.49	1.35	1.09
567744	C&K	7105	2	3	SPDT (on)-off-(on)	5 @ 125	.50 x .27 x .35	—	0.185	—	PC straight	Round	1.25	1.09	.79
75889	JVP	SWM129	1	3	SPDT (on)-off-(on)	6 @ 125 & 3 @ 250	.52 x .32 x .38	—	0.185	—	Solder lugs	Round	1.49	1.25	1.09
21910	JVP	JMT121	1	3	SPDT on-off-on	6 @ 125 & 3 @ 250	.52 x .32 x .38	—	0.185	—	Solder lugs	Round	1.35	1.25	1.09
26315	JVP	MPC121	1	3	SPDT on-off-on	6 @ 125 & 3 @ 250	.52 x .32 x .37	—	0.185	—	PC straight	Round	1.29	1.15	1.05
317244	JVP	1MS3T1B1M1QE	2	3	SPDT on-off-on	5 @ 120 & 2 @ 250	.50 x .27 x .35	—	0.185	—	Solder lugs	Round	1.75	1.59	1.39
317308	JVP	1MS3T6B11M1QE	2	3	SPDT on-off-on	5 @ 120 & 2 @ 250	.50 x .27 x .35	—	0.185	—	Solder lugs	Flat	1.75	1.59	1.39
317252	JVP	1MS4T1B1M1QE	2	3	SPDT (on)-off-(on)	5 @ 120 & 2 @ 250	.50 x .27 x .35	—	0.185	—	Solder lugs	Round	1.75	1.59	1.39
317316	JVP	1MS4T6B11M1QE	2	3	SPDT (on)-off-(on)	5 @ 120 & 2 @ 250	.50 x .27 x .35	—	0.185	—	Solder lugs	Flat	1.49	1.25	1.09
317261	JVP	1MS5T1B1M1QE	2	3	SPDT on-off-(on)	5 @ 120 & 2 @ 250	.50 x .27 x .35	—	0.185	—	Solder lugs	Round	1.75	1.59	1.39
317324	JVP	1MS5T6B11M1QE	2	3	SPDT on-off-(on)	5 @ 120 & 2 @ 250	.50 x .27 x .35	—	0.185	—	Solder lugs	Flat	1.75	1.59	1.39
2077044	JVP	MTS-103AA	3	3	SPDT on-off-on	6 @ 125 & 3 @ 250	.52 x .32 x .39	—	0.149	0.51	PC right angle	Round	.99	.89	.79
317404	JVP	1MD9T1B1M1QE	5	6	DPST on-off	5 @ 120 & 2 @ 250	.50 x .45 x .35	0.19	0.185	—	Solder lugs	Round	2.29	1.95	1.75
317463	JVP	1MD9T6B11M1QE	5	6	DPST on-off	5 @ 120 & 2 @ 250	.50 x .45 x .50	0.19	0.185	—	Solder lugs	Flat	1.59	1.39	1.19
75900	JVP	SWM133	6	6	DPDT on-on	6 @ 125 & 3 @ 250	.52 x .52 x .38	0.20	0.185	—	Solder lugs	Round	1.79	1.59	1.35
21979	JVP	JMT223	6	6	DPDT on-on	6 @ 125 & 3 @ 250	.52 x .52 x .38	0.20	0.185	—	Solder lugs	Round	1.49	1.25	1.09
26367	JVP	GTS112-P	6	6	DPDT on-on	6 @ 125 & 3 @ 250	.52 x .50 x .41	0.20	0.157	—	PCB	Round	1.49	1.25	1.09
317412	JVP	1MD1T1B1M1QE	5	6	DPDT on-on	5 @ 120 & 2 @ 250	.50 x .45 x .35	0.19	0.185	—	Solder lugs	Round	2.29	1.95	1.75
317472	JVP	1MD1T6B11M1QE	5	6	DPDT on-on	5 @ 120 & 2 @ 250	.50 x .45 x .35	0.19	0.185	—	Solder lugs	Flat	2.29	1.95	1.75
317455	JVP	1MD2T1B1M1QE	5	6	DPDT on-(on)	5 @ 120 & 2 @ 250	.50 x .45 x .35	0.19	0.185	—	Solder lugs	Round	11.49	1.29	1.09
317519	JVP	1MD2T6B11M1QE	5	6	DPDT on-(on)	5 @ 120 & 2 @ 250	.50 x .45 x .36	0.19	0.185	—	Solder lugs	Flat	2.29	1.95	1.75
22859	JVP	GTS172BLK	5	6	DPDT on-on	6 @ 125 & 3 @ 250	.52 x .52 x .38	0.20	0.185	—	Solder lugs	Flat	1.55	1.25	1.09
202964	◆	WI24	3	6	DPDT on-off-(on)	6 @ 125 & 3 @ 250	.50 x .50 x .46	0.15	0.150	0.20	PC right angle	Round	.99	.89	.79
75951	JVP	SWM130	6	6	DPDT (on)-off-(on)	6 @ 125 & 3 @ 250	.52 x .52 x .38	0.20	0.185	—	Solder lugs	Round	1.49	1.25	1.09
26358	JVP	MPC221	6	6	DPDT on-off-on	6 @ 125 & 3 @ 250	.52 x .52 x .38	0.20	0.185	—	PC straight	Round	1.49	1.25	1.09
21952	JVP	GTS114	6	6	DPDT on-off-on	6 @ 125 & 3 @ 250	.52 x .52 x .38	0.20	0.185	—	Solder lugs	Round	1.55	1.25	1.09
317439	JVP	1MD4T1B1M1QE	5	6	DPDT (on)-off-(on)	5 @ 120 & 2 @ 250	.50 x .45 x .35	0.19	0.185	—	Solder lugs	Round	2.29	1.95	1.75
317498	JVP	1MD4T6B11M1QE	5	6	DPDT (on)-off-(on)	5 @ 120 & 2 @ 250	.50 x .45 x .35	0.19	0.185	—	Solder lugs	Flat	1.95	1.75	1.59
317447	JVP	1MD5T1B1M1QE	5	6	DPDT on-off (on)	5 @ 120 & 2 @ 250	.50 x .45 x .35	0.19	0.185	—	Solder lugs	Round	2.29	1.95	1.75
317501	JVP	1MD5T6B11M1QE	5	6	DPDT on-off-(on)	5 @ 120 & 2 @ 250	.50 x .45 x .35	0.19	0.185	—	Solder lugs	Flat	2.29	1.95	1.75
317421	JVP	1MD3T1B1M1QE	5	6	DPDT on-off-on	5 @ 120 & 2 @ 250	.50 x .45 x .35	0.19	0.185	—	Solder lugs	Round	2.29	1.95	1.75
317490	JVP	1MD3T6B11M1QE	5	6	DPDT on-off-on	5 @ 120 & 2 @ 250	.50 x .45 x .35	0.19	0.185	—	Solder lugs	Flat	2.29	1.95	1.75
22841	JVP	GTS164BLK	5	6	DPDT on-off-on	6 @ 125 & 3 @ 250	.52 x .52 x .38	0.20	0.185	—	Solder lugs	Flat	1.49	1.25	1.09
620576	GCE	35-009	6	6	DPDT on-on-on	5 @ 125	.50 x .45 x .40	.23	.15	—	Solder	Bat brass	3.95	3.59	3.19
547436	ALC	MTA306D	6	9	3PDT on-on	6 @ 125 & 3 @ 250	.70 x .51 x .45	0.19	0.190	—	Solder lugs	Round	10.95	9.95	8.95

Electromech



Can't find what you are looking for in the catalog?
Check out the thousands of products online priced near cost.
Large Quantities Heavily Discounted
Factory Overruns - Jameco Excess Inventory - Discontinued Product Lines
www.Jameco.com/Clearance

* ALC = AlcoSwitch | C&K = C&K Switches | GCE = GC Electronics | JVP = Jameco ValuePro | ◆ Manufacturer Varies

* For Complete Specs & Additional Product Listings Search www.Jameco.com/More and Enter Web Code Listed Above

3 LEVELS OF SAVINGS
NAME BRANDS HOUSE BRANDS FACTORY OVERRUN

Order by Phone 24/7 at 1-800-831-4242 or Online at www.Jameco.com