


3.5" & 5.25" Disk Drive Power Splitters and Adapters

- IBM PC/XT and higher compatibles
- 28354/277528/72304: Splits 4-line Molex male into 2 females
- 28397: 4-line Molex male to female



* Web Code: OAE

Part No.	Drive	AWG	Length	1	10	100
28354	5.25"	18	5"	\$2.75	\$2.49	\$1.95
277528	5.25"	20	6"	1.55	1.39	1.25
72304	3.5"	22	5"	3.75	3.49	2.95
28397	3.5"	22	3.5"	4.75	4.25	3.79

CD-ROM Audio Cables

Part No.	Connection from	Sound Blaster to	Length	1	10	25
127546	Sony/MPC2	25"	\$1.95	\$1.75	\$1.49	
168613	Universal	18"	2.49	2.25	1.95	

Keyboard Adapters

- 157930/159097: Connect AT type keyboards to PS/2
- 5-pin female DIN to 6-pin male mini DIN
- 189771: Connect PS/2 keyboard to AT
- 6-pin female mini DIN to 5-pin male DIN connector



316831: • USB-A female to PS/2 male

Blue Part No. = Limited Quantity Available

Part No.	Length	Material	1	10	100
159097	1.4"	Metal	\$1.95	\$1.75	\$1.59
157930	1.7"	Plastic/metal	.39	.35	.29
189771	1.7"	Plastic	.95	.85	.75
316831	2.0"	Plastic	1.49	1.35	1.19

Macintosh® Printer and Keyboard Cables

Part No.	Mfr.	Description	1	10	100
1944994	Various	40' DIN8M w/EMI	\$2.95	\$2.49	\$2.25
10604	ValuePro	6' DIN8M	3.95	3.49	3.05
130025	ValuePro	10' DIN8M	4.95	4.45	3.95

Monitor/Mouse/Keyboard Cable

HDDDB15 male/female for monitor, 5-pin DIN male/female for keyboard and DB9 male/female for mouse.



Part No.	Product No.	Length	1	5
141284	G/S(KVM062)	6'	\$9.95	\$8.95

PS/2 & AT Cables

- Non-coiled cable

* Web Code: HAE

Part No.	Length	Color	1	10	100
177261	2'	Gray	\$1.75	\$1.49	\$1.25
174772	6'	Black	3.95	2.95	2.49
174908	6'	Beige	3.49	2.95	2.49
112628	10'	Beige	7.95	7.25	5.95
205655	25'	Beige	7.95	6.95	6.25

PS/2 6-Pin Mini DIN, Male to Male

- For use with switch box

Part No.	Length	Color	1	10	100
28549	6'	Beige	\$4.75	\$4.25	\$3.95
111053	10"	Beige	4.95	4.45	3.95

PS/2 6-Pin Mini DIN, Male to Female

- For cable extension

Part No.	Length	Color	1	10	100
114981	6'	Beige	\$1.95	\$1.75	\$1.49

PC/XT/AT 5-Pin Mini DIN, Male to Female

Part No.	Length	Color	1	10	100
114981	6'	Beige	\$1.95	\$1.75	\$1.49

SATA Data Cables

- 0.5m, 7-pin cable
- SATA-I & SATA-II compatible



* Web Code: SAC

2114407: eSATA (external)

Part No.	Connector A/B	Cable Color	1	10	100
2114327	Right angle/right angle	Transparent red	\$2.49	\$2.25	\$1.95
2114386	Right angle/straight	Red	2.65	2.39	2.15
2114301	Straight/straight	Transparent red	2.49	2.25	1.95
2114407	Straight latching/straight latching	Red	2.65	2.39	2.15

SATA Disk Drive Power Adapters

- 4-pin Molex to 15-pin SATA



* Web Code: SAD

Part No.	Molex	SATA	Length	1	10	100
2114343	5.25 (M)	Straight (F)	6"	\$2.29	\$1.95	\$1.79
2114351	5.25 (M)	Dual straight (F)	6"	2.49	2.29	2.09
2114360	5.25 (F)	Straight (M)	7"	4.95	4.49	3.95
2114378	5.25 (M)	Right angle (M)	6"	2.29	1.95	1.79

ADAM TECH

SATA Connectors

These SATA connectors combine hot plug capability with a combination of power and signal contacts in a blindmate design. They are ideal for connecting disk drives to backplanes in servers or networking equipment.

- -55°C to 125°C
- UL94V-0 approved
- Black insulator
- Gold flash over nickel plating

* Web Code: SAT



Part No.	Description	1	10	100
2113973	7-pin right angle, SMT	\$0.65	\$0.55	\$0.45
2113990	7 & 15 pin dual vertical, SMT	1.49	1.29	1.09



We Offer Data Sheets for Most of the Products We Carry. Find Them Easily on the Product Specification Page.

www.Jameco.com

* For Complete Specs & Additional Product Listings Search www.Jameco.com/More and Enter Web Code Listed Above