



[Click Here to Request a Large Quantity Quote](#)

[15 to 24 Volt Open Frame Switching Power Supplies](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Number of Outputs	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Size (L" x W" x H")	PFC Function	Agency Approvals	Price 1
2210731	Phihong	PSA-25-115	1	15	1.6		100 to 240	47 to 63		4 x 3 x 1.3	No	UL/CUL/CSA/CE	\$3.49
2164527	MEAN WELL	EPS-45-15	1	15	3.3	13.5 to 16.5	90 to 264	47 to 63	JST B4P-VH	4 x 2 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	\$12.40
2164682	MEAN WELL	EPS-65-15	1	15	4.8	13.5 to 16.5	90 to 264	47 to 63	JST B4P-VH	4 x 2 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	\$13.10
216751	MEAN WELL	PS-65-15	1	15	4.8		90 to 264	47 to 440	Molex 5273-06	5 x 3 x 1.7	No	UL/CUL/TUV/CB/CE/EN	\$15.95
216670	MEAN WELL	LPP-100-15	1	15	6.7		85 to 264	47 to 63	JST B8P-VH	8.7 x 2.4 x 1.3	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$31.20
2239728	MEAN WELL	EPS-120-15	1	15	8		80 to 264	47 to 63	JST B4P-VH	4 x 2 x 1.14	No	UL/CUL/TUV/CB/CE/EN/EAC	\$20.30
375065	MEAN WELL	LPP-150-15	1	15	10		85 to 264	47 to 63	JST B6P-VH (x2)	8.7 x 3 x 1.6	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$33.30
2249272	MEAN WELL	EPP-200-15	1	15	13.4		80 to 264	47 to 63	JST B6P-VH	4 x 2 x 1.14	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$40.90
2253861	MEAN WELL	EPP-400-15	1	15	16.7		80 to 264	47 to 63	Screw Terminals	5 x 3 x 1.38	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$68.80
2105560	MEAN WELL	PS-05-24	1	24	0.25		85 to 264	47 to 63	Molex 5273-02	3 x 1.6 x 0.8	No	CB/CE/EN/EAC	\$5.70
2174119	MEAN WELL	EPS-15-24	1	24	0.69	21.6 to 27	85 to 264	47 to 63	JST B2P-VH	2.5 x 1.8 x 0.9	No	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$7.20
2227575	Bel Power Solutions	BLP40-1024G	1	24	1.1		100 to 250	50 to 60	See datasheet	4.5 x 2.5 x 0.16	No	UL/CULTUV/CE	\$4.95

Jameco Part #	Manufacturer	Manufacturer Part #	Number of Outputs	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Size (L" x W" x H")	PFC Function	Agency Approvals	Price 1
2164359	MEAN WELL	EPS-25-24	1	24	1.17	21.6 to 27	85 to 264	47 to 63	JST B2P-VH	3 x 2 x 0.9	No	UL/CUL/TUV/CB/CE/EN/EAC	\$11.20
2164447	MEAN WELL	EPS-35-24	1	24	1.65	21.6 to 27	85 to 264	47 to 63	JST B2P-VH	3 x 2 x 0.9	No	UL/CUL/TUV/CB/CE/EN/EAC	\$11.60
2164535	MEAN WELL	EPS-45-24	1	24	2.1	21.6 to 27	90 to 264	47 to 63	JST B4P-VH	4 x 2 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	\$12.40
2164691	MEAN WELL	EPS-65-24	1	24	3	21.6 to 27	90 to 264	47 to 63	JST B4P-VH	4 x 2 x 1.1	No	UL/CUL/TUV/CB/CE/EN/EAC	\$13.10
148647	MEAN WELL	PS-65-24	1	24	3		90 to 264	47 to 440	Molex 5273-06	5 x 3 x 1.7	No	UL/CUL/TUV/CB/CE/EN	\$15.95
1773591	Artesyn Embedded Power	LPS65	1	24	3.3		85 to 264	47 to 440	Pin Terminal Block	5 x 3 x 1.7	No	CB/CE/CSA/EN/IEC/LVD/NEMKO/UL/VDE	\$111.09
244727	MEAN WELL	LPS-75-24	1	24	3.5	22 to 27	90 to 264	47 to 63	JST B6P-VH	8.7 x 2.2 x 1.2	No	UL/CUL/TUV/CB/CE/EN/EAC	\$17.50
173463	MEAN WELL	LPS-100-24	1	24	4.2		88 to 132, 176 to 264	47 to 63	JST B8P-VH	8.7 x 2.4 x 1.3	No	UL/CUL/TUV/CB/CE/EN/EAC	\$27.60
2172412	MEAN WELL	EPP-100-24	1	24	4.2		90 to 264	47 to 63	JST B4P-VH	4 x 2 x 1.1	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$35.70
2239437	MEAN WELL	EPS-120-24	1	24	5		80 to 264	47 to 63	JST B4P-VH	4 x 2 x 1.14	No	UL/CUL/TUV/CB/CE/EN/EAC	\$20.30
2172463	MEAN WELL	EPP-150-24	1	24	6.25		90 to 264	47 to 63	JST B4P-VH	4 x 2 x 1.1	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$39.00
213672	MEAN WELL	LPP-150-24	1	24	6.3		85 to 264	47 to 63	JST B6P-VH (x2)	8.7 x 3 x 1.6	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$33.30
668730	MEAN WELL	PPS-200-24	1	24	8.3	21.6 to 26.4	90 to 264	47 to 63	JST B8P-VH	5 x 3 x 1.4	Yes	UL/CUL/TUV/CB/CE/EN	\$61.95
2249281	MEAN WELL	EPP-200-24	1	24	8.4		80 to 264	47 to 63	JST B6P-VH	4 x 2 x 1.14	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$40.90
2253888	MEAN WELL	EPP-400-24	1	24	10.5		80 to 264	47 to 63	Screw Terminals	5 x 3 x 1.38	Yes	UL/CUL/TUV/CB/CE/EN/EAC/CCC	\$68.80

Jameco Part #	Manufacturer	Manufacturer Part #	Number of Outputs	Primary Output Voltage (VDC)	Output Current (A)	Additional Output Voltages (VDC)	Input Voltage (VAC)	Input Frequency	Output Connector Type	Size (L" x W" x H")	PFC Function	Agency Approvals	Price 1
2164279	MEAN WELL	EPP-300-24	1	24	12.5		90 to 264	47 to 63	Screw Terminals	5 x 3 x 1.4	Yes	UL/CUL/TUV/CB/CE/EN/EAC	\$57.00