



[Click Here to Request a Large Quantity Quote](#)

48 Volt DC Brushless Fan

Jameco Part #	Manufacturer	Manufacturer Part #	Voltage (VDC)	Height - mm	Width - mm	Depth - mm	Air Flow (CFM)	Bearing	Current (mA)	Agency Approvals	Noise (dBA)	Connection (Leads)	Price 1
2306647	Sunon	EEC0381B1-000U-A99	12	120	120	38	138	Ball	880	UL/CUL/TUV/CE	46	12"	\$13.95
2306775	AVC America	DATA0625B8H S023	48	60	60	25	33.9	Ball	160	UL/CUL/TUV/CE	47	(3) 6" w/ conn., speed sensor	\$8.95
2315767	ADDA Corporation	AD0848XB-F71DS	48	80	80	38	65.3	Ball	180	UL/CUL/TUV/CE	47.2	12"	\$19.95
2306639	Orion Fans	OD9238-48HBVXC	48	92	92	38	135	Ball	400	UL/CUL/TUV	58	12"	\$14.95
2203400	ADDA Corporation	AD1248HB-A71GL	48	120	120	25	104	Ball	100	UL/CUL/TUV/CE	39.1	12"	\$16.95
2233342	ADDA Corporation	AD1248MB-F91GP	48	120	120	38	94	Ball	280	UL/CUL/TUV/CE	57.5	12"	\$11.95
2289031	Delta Electronics	EFB1248VHE	48	120	120	38	102	Ball	100	UL/CSA/CE	45.5	(3) 12", speed sensor	\$11.95
2231646	ADDA Corporation	AD1248HB-F5B(N)	48	120	120	38	105	Ball	180	UL/CUL/TUV/CE	46.7	(4) 11", PWM + FG	\$12.95
2302887	ADDA Corporation	AD1248HB-F51	48	120	120	38	105.5	Ball	180	UL/CUL/CSA/CE	41	12"	\$19.95
2313295	NMB Technologies	4715KL-07W-B30-E00	48	120	120	38	108	Ball	160	UL/CUL/VDE/CE	42.5	12"	\$12.95
2289023	Mechatronics	A1238H48B	48	120	120	38	124	Ball	150	UL/CSA/CE	41	13"	\$19.95
2289039	Delta Electronics	AFB1248VHE-R00	48	120	120	38	130	Ball	180	UL/TUV/CE/CSA	48	(3) 12", speed sensor	\$19.95
2315423	ADDA Corporation	AS12048HB389BOOOCL	48	120	120	38	228.4	Ball	1150	UL/CUL/TUV/CE	67.7	(4) 12", speed & PWM	\$19.95
2306583	Sanyo Denki	9SG1212G102	48	120	120	38	260	Ball	4000	UL/CUL/TUV	64	(3) 12", locked rotor	\$34.95
2233465	ADDA Corporation	AD1348HB-F51	48	127	127	38	161	Ball	210	UL/CUL/TUV/CE	53	12"	\$29.95
2302847	Sanyo Denki	9SG5748P5G01	48	172	150	51	543	Ball	2910	UL/CUL/TUV	78	(4) 12" (PWM + Pulse)	\$59.95