



*Web Code: SAV

Small PC Mount Relays

Designed for the appliance and temperature control markets, these relays are also well suited for automotive load management.

- Mechanical life: 10 million operations
- Electrical life: 100,000 operations
- Dielectric strength: 1500V_{RMS} (between contact and coil)



Part No.	Manufacturer	Mfr. Part No.	Potter & Brumfield Cross Reference	Fig.	Contact Form	Coil Voltage	Coil (Ohms)	Contact Current	Contact Voltage	Pins	Dimensions (L" x W" x H")	Pricing		
												1	10	50
2077394	Fujitsu	JV-3S-KT	—	1A	SPST-NO	3VDC	45	5A	250VAC/30VDC	4	.69 x .39 x .49	\$2.29	\$2.09	\$1.89
2077271	Fujitsu	FTR-F2AL006T	—	1B	SPST-NO	6VDC	145	5A	250VAC/30VDC	4	.95 x .43 x .98	1.49	1.29	1.09
2077378	Fujitsu	FBR161NED006-WB	—	2C	SPST	6VDC	100	10A	120VAC/30VDC	5	.85 x .63 x .63	1.49	1.29	1.09
2120217	Bestar	BS-114	—	3D	SPST	12VDC	320	10A	120VAC/30VDC	5	.85 x .63 x .63	2.95	2.75	2.49
145753	Rayex*	L90A-12W	T90S1D12-12	4E	SPST	12VDC	155	30A/20A	240VAC/28VDC	5	1.2 x 1.0 x .77	2.95	2.75	2.49
134949	Rayex	L90-5W	T90S5D12-5	4E	SPDT	5VDC	27	20A	240VAC/28VDC	6	1.3 x 1.1 x .80	2.29	2.09	1.89
187151	Omron	G5LE-1DC5	—	2F	SPDT	5VDC	63	10A/8A	120VAC/30VDC	5	.90 x .65 x .75	1.49	1.29	1.09
843155	Panasonic	JS1-5V	T7C55D-05	5C	SPDT	5VDC	69.4	10A/5A	250VAC/100VDC	5	.87 x .63 x .63	1.19	1.09	.95
174450	Rayex	LU-5	T81H5D215	6G	SPDT	5VDC	125	1A/2A	120VAC/24VDC	6	.60 x .40 x .45	1.95	1.69	1.49
187418	Omron	G6E-134P-ST-US-DC5	—	7H	SPDT	5VDC	125	.4A/2A	125VAC/30VDC	5	.63 x .39 x .33	2.95	2.75	2.49
760616	Panasonic	DS1E-S-DC5V	—	8I	SPDT	5VDC	125	2.0A	125VAC/30VDC	5	.59 x .39 x .39	3.95	3.49	2.95
187240	Omron	G5V-1-DC5	T5C-105L3H	7J	SPDT	5VDC	166.7	.5A/1A	125VAC/24VDC	6	.50 x .30 x .40	2.29	2.09	1.89
454563	Hasco	KLTC12DC9	—	6K	SPDT	9VDC	225	12A	120VAC/28VDC	5	.73 x .59 x .61	1.75	1.49	1.25
664309	Nais (Aromat)	JW1FSN-DC12V	RTB14012F	9L	SPDT	12VDC	270	10A	250VAC/30VDC	5	1.13 x .51 x .79	2.49	2.25	1.95
144186	Velleman	JZC-22F	VR15M121C	6K	SPDT	12VDC	337	15A	120VAC/28VDC	5	.80 x .64 x .80	2.95	2.75	2.49
174432	Rayex	LEG-12F	T7C55D12	6K	SPDT	12VDC	400	15A	120VAC/24VDC	5	.76 x .62 x .60	1.89	1.59	1.49
184461	Omron	G5V-1-DC12	—	7J	SPDT	12VDC	960	.5A/1A	125VAC/24VDC	6	.50 x .30 x .40	2.29	2.09	1.89
172937	Nais (Aromat)	JS1-12V	T72M5D121-12	5C	SPDT	12VDC	400	10A/5A	125VAC/24VDC	5	.85 x .62 x .63	1.19	1.09	.95
2078186	Fujitsu	FBR161NED012	T7C55D-12	6C	SPDT	12VDC	400	10A	125VAC/30VAC	5	.80 x .60 x .60	1.95	1.69	1.49
843201	Nais (Aromat)	JW1FSN-DC24V	RTB14024F	9C	SPDT	24VDC	1100	10A/10A	250VAC/30VDC	5	1.11x .49 x .78	1.95	1.69	1.49
187400	Omron	G6E-134P-ST-US-DC48	—	7H	SPDT	48VDC	5760	.4A/2A	125VAC/30VDC	5	.63 x .39 x .33	3.95	3.59	3.29
998190	Panasonic	JW2ASN-DC5V	RTE44005F	9M	DPST	5VDC	47	5A/5A	250VAC/30VDC	6	1.13 x .50 x .79	1.49	1.29	1.09
215909	Potter & Brumfield	RKA-7DZ-12	—	7N	DPST-NO	12VDC	270	5A/5A	250VAC/24VDC	6	1.16 x .57 x 1.05	1.95	1.69	1.49
15051	Panasonic	AGQ200A4HZ	SMD-PKG	10N	DPDT	4.5VDC	145	.3A/1A	125VAC/30VDC	8	.417 x .283 x .213	1.49	1.35	1.19
2077255	NEC	EE2-4.5NUX-L	SMD-PKG	10N	DPDT	4.5VDC	145	.5/2A	125VAC/30VDC	8	.59 x .30 x .35	1.49	1.29	1.09
2095390	Axicom	V23079A1011B301	—	11O	DPDT	4.5VDC	145	2A	250VAC/220VDC	10	.57 x .28 x .39	1.95	1.75	1.49
2077415	Fujitsu	BA-5W-K	—	12N	DPDT	5VDC	100	.5A/1A	125VAC/30VDC	8	.59 x .29 x .38	2.19	1.89	1.49
187282	Omron	G6A-234PSTUSDC5	C93416	12P	DPDT	5VDC	125	.3A/1A	125VAC/30VDC	8	.80 x .33 x .40	3.95	3.59	3.29
842953	Panasonic	DS2E-S-DC5V	—	13Q	DPDT	5VDC	125	2A	125VAC/30VDC	8	.79 x .39 x .39	3.95	3.59	3.29
843649	Panasonic	TXA2SA-5V	—	10N	DPDT	5VDC	178	2A	30VDC	8	.59 x .29 x .22	1.95	1.69	1.49
2081650	NEC	EC2-5NJ	—	11N	DPDT	5VDC	178	2A	220VAC/220VDC	8	.59 x .30 x .37	2.49	2.25	1.95
15034	Panasonic	TN2-5VDC	—	14R	DPDT	5VDC	178	.5A/1A	125VAC/30VDC	10	.55 x .22 x .39	2.49	2.25	1.95
2077263	Siemens	V23079-F1101-B301	SMD-PKG	10N	DPDT	5VDC	357	5A	250VAC/220VDC	10	.57 x .28 x .41	1.95	1.69	1.49
2077386	Fujitsu	AL-D9W-K	—	12S	DPDT	9VDC	45	.5A/1A	125VAC/30VDC	10	.55 x .35 x .20	1.69	1.49	1.29
174378	Rayex	LM2-12D	RKA5DZ12	1N	DPDT	12VDC	270	5A	250VAC/30VDC	8	1.2 x .48 x 1.0	2.49	2.25	1.95
187258	Omron	G5V-2-DC12	—	11U	DPDT	12VDC	288	.5A/2A	125VAC/30VDC	8	.81 x .40 x .45	2.85	2.49	2.19
842793	Panasonic	DS2E-M-DC12V	—	13O	DPDT	12VDC	360	2A	125VAC/30VDC	8	.79 x .39 x .39	2.95	2.75	2.49
842873	Panasonic	DS2E-ML2-DC12V	—	8U	DPDT	12VDC	400	2A	250VAC/220VDC	10	.79 x .39 x .39	3.95	3.75	3.35
2078215	Omron	G2VN-234P-US	—	12P	DPDT	24VDC	1600	.5A/1.5A	120VAC/30VDC	8	.77 x .39 x .401	2.19	1.89	1.49
200740	Omron	G5V-2-HI	—	11T	DPDT	24VDC	2800	.5A/1A	125VAC/24VDC	8	.81 x .40 x .45	2.29	2.09	1.89
2078274	Fujitsu	FBR46D024	—	12P	DPDT	24VDC	2880	.5A/1A	120VAC/30VDC	8	.63 x .39 x .33	1.49	1.29	1.09
842937	Panasonic	DS2E-S-DC24V	—	8I	DPDT	24VDC	2880	2A	250VAC/220VDC	8	.79 x .39 x .37	3.95	3.59	3.29
2077360	Fujitsu	RA4-12W-K	—	15V	4PDT	12VDC	720	.5A/1A	120VAC/24VDC	14	1.39 x .39 x .39	3.95	3.49	2.95

*Manufacturer may vary † SMD package ⊕ Blue Part No. = Limited Quantity Available

*For Complete Specs & Additional Product Listings Search www.Jameco.com/More and Enter Web Code Listed Above



Order by Phone 24/7 at 1-800-831-4242 or Online at www.Jameco.com