



[Click Here to Request a Large Quantity Quote](#)

AUDIO COMPONENTS - SPEAKERS

Jameco Part#	Manufacturer	Manufacturer Part #	Impedance (ohms)	Dimensions (Dia" x Depth")	Input Power (Nom)W	Input Power (Max) (W)	Ouput SPL (dB)	Frequency Range (Hz)	Magnet Size (Dia" x H")	Price 1
673766	Jameco Valuepro	AZ-50S	4	1.9 x 0.2	0.4	0.8	70	500 - 6000	1.9 x 0.1	\$ 1.09
99996	Jameco Valuepro	TQ-066F-R	4	2.6 x 0.9	3.0	4	95	300 - 14000	1.8 x 0.5	\$ 3.59
2224041	Jameco Valuepro	110153-01	4	2.4 x 1.4	10.0	10	85	1000 - 12000	2.2 x 0.5	\$ 1.95
2229618	Jameco Valuepro	SP99023A	4	2.06 x 1.25	10.0	20	90	400 - 8000	2.1 x 1.25	\$ 1.75
2099606	Jameco Valuepro	SP801W	8	1.05 x 0.35	0.1	0.2	78	320 - 7500	0.67 x 0.17	\$ 1.59
2205561	Panasonic	45P30S	8	1.8 x 0.7	0.1	0.1	93	530 - 3000	0.69 x 0.45	\$ 0.75
135722	Jameco Valuepro	36MS30008-PN	8	1.2 x 0.52	0.2	0.2	83	700 - 5000	.50 x 1.17	\$ 1.25
2095234	MG Electronics	38MS30008	8	0.57 x 1.24	0.2	0.2	83	700 - 4000	.57 x 1.24	\$ 0.99
135694	Jameco Valuepro	TQ-050F-R	8	2.0 x 0.7	0.2	0.3	82	500 - 6000	1.3 x 0.5	\$ 2.29
88411	Jameco Valuepro	A0200-R	8	2.0 x 0.8	0.2	0.4	82	430 - 4500	0.5 x 0.4	\$ 2.25
2228851	CUI	GC0361MA	8	1.42 x 0.18	0.2	0.5	84	380 - 680	.64 x .65	\$ 1.49
320362	Jameco Valuepro	TR-050F	8	2.0 x 0.7	0.3	0.5	86	320 - 4000	1.3 x 0.25	\$ 2.55
2146388	Jameco Valuepro	TR-057A-R	8	2.25 x 0.77	0.3	0.5	84	300 - 14000	0.5 x 0.4	\$ 2.75
2231161	Shogyo International	GF0506X	8	2L x 2W x 0.68D	0.3	0.5	82	430 - 7200	1.8 x 0.5	\$ 1.95
2286327	Jameco Valuepro	DMSP-0913AJ-20-TG	8	0.47 x 0.32 x 0.1	0.3	0.5	63	100 - 10000	.47 x .31	\$ 0.99
76030	Jameco Valuepro	AZ-40S	8	1.6 x 0.2	0.4	0.8	70	600 - 6000	1.6 x 0.1	\$ 1.49
2227508	Jameco Valuepro	AZ30R	8	1.2 x 0.2	0.4	0.8	70	1300 - 8000	.5 x 0.2	\$ 1.49
2227516	Jameco Valuepro	AZ40R	8	1.6 x 0.2	0.4	0.8	70	600 - 6000	1.6 x 0.1	\$ 1.25
2270943	Jameco Valuepro	A0202C	8	2.5 x 0.7	0.5	1	88	320 - 5000	0.8 x 0.4	\$ 1.29
2208825	Jameco Valuepro	EAS-6P60SD	8	2.2 x 1.3	0.4	0.8	85	100 - 5000	2.2 x 1.3	\$ 0.99
2272639	Jameco Valuepro	SPU3520	8	1.4L x 0.8W x 0.32D	1.0	1	80	500-2000	.55 x .10	\$ 1.49
2234134	Jameco Valuepro	40R	8	1.5 x 0.2	1.0	1.5	93	100 - 15000	0.63 x 0.05	\$ 2.49
1950972	Sony Corporation	1-826-219-11	8	8.2L x 2.2W x 2.0H	1.0	4.5	85	20 - 20000	1.5 x 2.8	\$ 1.95
135812	Jameco Valuepro	TV-4171A-R	8	1.6L x 2.8W x 1.2H	2.0	3	88	450 - 20000	0.5 x 0.5	\$ 2.59
2234759	Jameco Valuepro	TQ-023CP-8	8	0.9L x 0.9W x 0.4H	2.0	4	76	300 - 20000	0.5 x 0.12	\$ 3.59
2115442	Jameco Valuepro	K7048022	8	1.6L x 2.8W x 0.9H	3.0	3	82	310 - 12000	0.87 x 0.29	\$ 2.09
2167285	Jameco Valuepro	1-529-483-11	8	3.0 x 2.25	4.0	5	85	180 - 10000	2.5 x 1.0	\$ 3.59
1954818	Jameco Valuepro	TQ-100F-R	8	4.0 x 1.4	5.0	8	97	800 - 10000	1.8 x 0.5	\$ 3.59
2265895	Jameco Valuepro	BLS86-2-08H30.5-05LF	8	3.4 x 3.4 x 1.21	6.0	12	87	800 - 10000	2.3 x 0.4	\$ 2.95
2224032	Zenith Electronics	49-1334-02	8	6.3L x 3.1W x 2.2D	7.0	7	85	100 - 18000	2.1 x 1.0	\$ 2.75
2258806	Samsung Electronics	15294900	8	7 x 5	10.0	10	82	100 - 10000	2.5 x 1.1	\$ 2.95
2258793	Jameco Valuepro	S03O7F390	8	2.9L x 1.2W x 1.0H	1.0	0.5	80	100 - 1000	1.2 x 0.8	\$ 1.95
2239146	MG Electronics	MSC299SWC	8	2.0 x 0.7	2.0	0.7	83	500 - 8000	1.3 x 0.4	\$ 1.95
31959	Jameco Valuepro	GSP01-R	16	2.6 x 0.8	0.2	0.4	85	330 - 8000	1.3 x 0.5	\$ 2.75
2205202	Jameco Valuepro	HKS-16-5	16	3 x 0.86	0.5	2	92	200 - 3000	1.25 x 0.24	\$ 0.55
2217828	Jameco Valuepro	HKS-16-0.5	16	3 x 0.9	0.5	1	89	500-5000	1.25 x 0.24	\$ 0.59
2179681	Jameco Valuepro	27JRG-1624	16	4.0 x 4.0	2.0	2	85	800 - 11000	1.8 x 0.5	\$ 0.99
2188916	Sharp Electronics	80P-G3YB	32	3.0 x 0.7	0.5	2	92	200 - 3000	0.8 x 0.5	\$ 0.89
2230782	Jameco Valuepro	A0102-45	45	1.58 x 0.41	0.1	0.2	80	650 - 5000	0.7 x 0.42	\$ 1.25



[Click Here to Request a Large Quantity Quote](#)

AUDIO COMPONENTS - SPEAKERS

Jameco Part#	Manufacturer	Manufacturer Part #	Impedance (ohms)	Dimensions (Dia" x Depth")	Input Power (Nom)W	Input Power (Max) (W)	Ouput SPL (dB)	Frequency Range (Hz)	Magnet Size (Dia" x H")	Price 1
2236674	Jameco Valuepro	FEB30045	45	3L x 3W x 1H	0.5	1	90	260 - 5000	3 x 3 x 1	\$ 1.35