


[Click Here to Request a Large Quantity Quote](#)

BATTERY HOLDERS

Jameco Part#	Manufacturer	Manufacturer Part #	Cell Size	Number of		Connector	Product Type	Features	Product Length	Product Width	Product	
				Cells	Sides						Height	Price
2146231	Jameco Reliapro	BH-18650-2S-WG	18650	2	Single	Wires, 6"	Battery Holders (open)	No internal PCB, for flat top cells	75.7 mm	41.5 mm	20.0 mm	\$ 1.95
2203899	Jameco Reliapro	9VSNAPOB6	9V	1	Single	Snaps	Battery Contact Clip	PC mount	10.2 mm	7.0 mm	17.0 mm	\$ 0.39
11280	Jameco Reliapro	A104-R	9V	1	Single	Wires, 3"	Battery Holders (open)	T-Type	14.2 mm	25.4 mm	6.5 mm	\$ 0.49
105794	Jameco Reliapro	GBH-1009-R	9V	1	Single	None	Battery Holder Clip	Side mount	17.0 mm	16.0 mm	30.0 mm	\$ 0.49
101470	Jameco Reliapro	G/S(A-102)-R	9V	1	Single	Wires, 10"	Battery Holders (open)	I-Type	25.4 mm	12.7 mm	6.4 mm	\$ 0.49
1949488	Jameco Reliapro	BAT-SNAP-4	9V	1	Single	Wires, 4"	Battery Holders (open)	I-Type	25.4 mm	12.7 mm	6.5 mm	\$ 0.49
109154	Jameco Reliapro	BC6-R	9V	1	Single	Wires, 6"	Battery Holders (open)	I-Type	25.4 mm	13.8 mm	6.1 mm	\$ 0.49
216452	Jameco Reliapro	SBS-IR-1-R	9V	1	Single	Wires, 6"	Battery Holders (open)	I-Type, protected terminals	26.0 mm	13.0 mm	8.0 mm	\$ 0.55
2191891	Jameco Reliapro	12BH079-GR-VP	9V	1	Single	None	Battery Holder Clip	Flat mount	26.4 mm	16.0 mm	19.3 mm	\$ 0.69
216427	Jameco Reliapro	BH-9V-A-R	9V	1	Single	Wires, 6"	Battery Holders (open)	Flat mount	55.0 mm	31.0 mm	20.0 mm	\$ 0.89
2234118	Memory Protection Devices	BH-9VPC	9V	1	Single	PC Mount	Battery Holders (open)	Pins 0.50" apart	54.4 mm	30.0 mm	20.6 mm	\$ 1.25
2191904	Eagle Plastics	660279	9V	1	Single	Wires, 4", 2P connector	Battery Holders (open)	I-Type, JP2411-2P connector	25.4 mm	12.7 mm	6.5 mm	\$ 1.49
2228447	Memory Protection Devices	BC9VPC	9V	1	Single	PC Mount	Battery Holders (open)	Pins 0.51" apart	54.9 mm	30.0 mm	21.4 mm	\$ 1.49
2128067	Jameco Reliapro	SBH-9VAS	9V	1	Single	Wires, 6"	Battery Holders (closed)	Cover and switch	68.6 mm	33.0 mm	21.6 mm	\$ 1.49
2207056	Jameco Reliapro	1X9V-2.1 SNAP	9V	1	Single	Wires, 6", 2.1mm Plug	Battery Holders (open)	I-Type, 2.1mm x 5.5mm barrel plug, center positive	25.4 mm	12.7 mm	6.5 mm	\$ 1.95
2207030	Jameco Reliapro	1X9V-2.1	9V	1	Single	Wires, 6", 2.1mm Plug	Battery Holders (open)	2.1mm x 5.5mm barrel plug, center positive	54.5 mm	30.5 mm	20.9 mm	\$ 2.49
2207048	Jameco Reliapro	1X9V-2.1 CS	9V	1	Single	Wires, 6", 2.1mm Plug	Battery Holders (closed)	Cover and switch, 2.1mm x 5.5mm barrel plug, center positive	53.6 mm	30.0 mm	16.0 mm	\$ 3.59
2222133	Keystone Electronics	209	A, AA, CR2, CR123A	1	Single	Spring Contact, Snap-In	Battery Contact Clip	A/AA/CR2/CR123A	7.9 mm	9.1 mm	11.7 mm	\$ 0.35
2222230	Keystone Electronics	590	A, AA, CR2, CR123A, N, 9V	1	Single	Spring Contact, THM	Battery Contact Clip	A/AA/CR2/CR123A/N/9V	9.2 mm	10.3 mm	14.4 mm	\$ 0.25
216072	Jameco Reliapro	BH-311-2A-R	AA	1	Single	Wires, 6"	Battery Holders (open)	Holder is in-line with wires	57.0 mm	17.0 mm	17.0 mm	\$ 0.75
216099	Jameco Reliapro	BH-321-4A-R	AA	2	Single	Wires, 6"	Battery Holders (open)	Mounting tabs	71.0 mm	32.0 mm	16.0 mm	\$ 0.69
2270007	Eagle Plastics	128BH321PR	AA	2	Single	PC Mount	Battery Holders (open)	Pins 0.478" apart, release strap	57.1 mm	32.0 mm	15.7 mm	\$ 0.85
216081	Jameco Reliapro	BH-321-2A-R	AA	2	Single	Wires, 6"	Battery Holders (open)		59.0 mm	33.0 mm	15.0 mm	\$ 0.89
2278463	Jameco Reliapro	BAT. HOLDER-R WHT	AA	2	Single	Wires, 6", 2P connector	Battery Holders (open)	Molex 0050375023 connector	57.0 mm	62.0 mm	15.0 mm	\$ 0.99
216102	Jameco Reliapro	SBH-321-2A-R	AA	2	Single	Wires, 6"	Battery Holders (closed)	Cover, no switch	68.4 mm	35.4 mm	18.6 mm	\$ 1.49
216120	Jameco Reliapro	SBH-321-1AS-S10	AA	2	Single	Wires, 6"	Battery Holders (closed)	Cover and switch	68.5 mm	34.0 mm	18.2 mm	\$ 1.95
216136	Jameco Reliapro	BH-331-A-R	AA	3	Single	Wires, 6"	Battery Holders (open)		58.0 mm	48.0 mm	17.0 mm	\$ 0.95
216144	Jameco Reliapro	SBH-331-AS-R	AA	3	Single	Wires, 6"	Battery Holders (closed)	Cover and switch	68.5 mm	48.0 mm	18.7 mm	\$ 1.65
105858	Jameco Reliapro	BAT. HOLDER-R	AA	4	Single	Wires, 6", 4P Connector	Battery Holders (open)	4P connector with 0.1" pitch	58.4 mm	63.5 mm	16.3 mm	\$ 0.99
216179	Jameco Reliapro	BH-343-1A-R	AA	4	Dual	Wires, 6"	Battery Holders (open)		57.0 mm	30.0 mm	27.0 mm	\$ 1.09
2191883	Eagle Plastics	12BH341-GR	AA	4	Dual	Snaps	Battery Holders (open)	2x2, long	57.0 mm	30.0 mm	27.0 mm	\$ 1.19
216152	Jameco Reliapro	BH-341-2A-R	AA	4	Single	Wires, 6"	Battery Holders (open)		57.0 mm	62.0 mm	15.0 mm	\$ 1.19
2095453	Jameco Reliapro	SBH-341-1A	AA	4	Single	Wires, 6"	Battery Holders (closed)	Cover, no switch	65.0 mm	68.0 mm	19.0 mm	\$ 1.49
2207013	Jameco Reliapro	4XAA-2.1	AA	4	Single	Wires, 6", 2.1mm Plug	Battery Holders (open)	2.1mm x 5.5mm barrel plug, center positive	63.2 mm	57.7 mm	15.6 mm	\$ 2.49
216187	Jameco Reliapro	SBH-341-1AS-R	AA	4	Single	Wires, 6"	Battery Holders (closed)	Cover and switch	68.0 mm	64.4 mm	19.3 mm	\$ 2.49
216223	Jameco Reliapro	BH-364-A	AA	6	Single	Wires, 6"	Battery Holders (open)	Holder is in-line with wires	57.0 mm	91.0 mm	16.0 mm	\$ 1.69
2207021	Jameco Reliapro	6XAA-2.1	AA	6	Single	Wires, 6", 2.1mm Plug	Battery Holders (open)	2.1mm x 5.5mm barrel plug, center positive	91.7 mm	57.4 mm	16.0 mm	\$ 2.75
216267	Jameco Reliapro	BH-383-B-R	AA	8	Dual	Snaps	Battery Holders (open)	4x2 cells wide	58.0 mm	63.0 mm	28.0 mm	\$ 0.99
216259	Jameco Reliapro	BH-382-B-R	AA	8	Dual	Snaps	Battery Holders (open)	4x2 cells long	108.0 mm	31.0 mm	29.0 mm	\$ 1.39
216240	Jameco Reliapro	BH-383-A	AA	8	Dual	Wires, 6"	Battery Holders (open)	4x2 cells wide	57.0 mm	30.0 mm	27.0 mm	\$ 1.95
2197935	Jameco Reliapro	BC-0302	AA, AAA	1	Single	Contact	Battery Contact Clip	PC Mount, 0.3" pitch, 2 required	9.0 mm	14.0 mm	15.0 mm	\$ 0.29
216283	Jameco Reliapro	BH-421-1A-R	AAA	2	Single	Wires, 6"	Battery Holders (open)		52.0 mm	25.0 mm	13.0 mm	\$ 0.99
2236981	Jameco Reliapro	12-051	AAA	2	Single	Wires, 2.5", with crimped pins	Battery Holders (open)	Breadboard pins	53.3 mm	24.6 mm	13.0 mm	\$ 1.09
216292	Jameco Reliapro	SBH-421-AS-R	AAA	2	Single	Wires, 6"	Battery Holders (closed)	Cover and switch	63.0 mm	26.0 mm	16.0 mm	\$ 1.25
216303	Jameco Reliapro	BH-431-1A	AAA	3	Single	Wires, 6"	Battery Holders (open)		53.0 mm	38.0 mm	13.0 mm	\$ 1.15
216312	Jameco Reliapro	SBH-431-1AS-R	AAA	3	Single	Wires, 6"	Battery Holders (closed)	Cover and switch	63.2 mm	36.8 mm	16.0 mm	\$ 1.15
2232833	Jameco Reliapro	UM-4	AAA	4	Single	PC Mount	Battery Holders (open)	Pins 0.478" apart	50.3 mm	47.2 mm	12.2 mm	\$ 0.99
216339	Jameco Reliapro	SBH-441-AS-R	AAA	4	Single	Wires, 6"	Battery Holders (closed)	Cover and switch	63.0 mm	48.0 mm	15.0 mm	\$ 1.59
2245546	Jameco Reliapro	BH-482B	AAA	8	Dual	Snaps	Battery Holders (open)	4x2, long	97.0 mm	23.8 mm	24.4 mm	\$ 1.35
216363	Jameco Reliapro	BH-242-1A-R	C	4	Single	Wires, 6"	Battery Holders (open)		108.0 mm	54.0 mm	26.0 mm	\$ 1.39
2246856	Jameco Reliapro	WJ-CR1220-1	CR1216, CR1220	1	Coin Cell	PC Mount	Battery Holders (open)	Retaining clip, one side open	13.4 mm	11.7 mm	2.3 mm	\$ 0.35
2258646	Arndt	AAA-BAT-054	CR2012, CR2016, CR2020, CR2025, CR2032	1	Coin Cell	Surface Mount	Battery Holders (open)	For 20mm cells	31.9 mm	23.0 mm	4.2 mm	\$ 0.99
2280143	Jameco Reliapro	BS2032-1	CR2025, CR2032	1	Coin Cell	PC Mount	Battery Holders (open)	Pins 0.769" apart	24.3 mm	22.3 mm	9.0 mm	\$ 0.79
355434	Jameco Reliapro	17002-00603	CR2032	1	Coin Cell	PC Mount	Battery Holders (open)	For 20mm cells	23.7 mm	22.5 mm	8.0 mm	\$ 0.75
236996	Keystone Electronics	103	CR2032	1	Coin Cell	PC Mount	Battery Holders (open)	For 20mm cells	28.5 mm	22.7 mm	8.3 mm	\$ 1.69
2280527	Jameco Reliapro	1065	CR2032	1	Coin Cell	PC Mount, Vertical	Battery Holders (open)	For 20mm cells	26.4 mm	7.5 mm	23.4 mm	\$ 1.75
38543	Jameco Reliapro	GS025-021G	CR2354, CR2325 (x2)	1 or 2	Coin Cell	PC Mount	Battery Holders (open)	For 23mm cells	29.1 mm	25.4 mm	8.3 mm	\$ 0.79
216371	Jameco Reliapro	BH-111-1A	D	1	Single	Wires, 6"	Battery Holders (open)	Holder is in-line with wires	69.0 mm	37.0 mm	27.0 mm	\$ 1.15
216390	Jameco Reliapro	BH-121-1A-R	D	2	Single	Wires, 6"	Battery Holders (open)		71.0 mm	73.0 mm	31.0 mm	\$ 1.39
216401	Jameco Reliapro	BH-142-A-R	D	4	Single	Wires, 6"	Battery Holders (open)		133.5 mm	74.0 mm	31.0 mm	\$ 1.09
2265735	Eagle Plastics	12BH521PR	N	2	Single	PC Mount	Battery Holders (open)	Pins 0.478" apart, release strap	38.1 mm	27.0 mm	12.7 mm	\$ 0.85