



[Click Here to Request a Large Quantity Quote](#)

## ELECTROMECHANICAL MOTORS VIBRATING

Jameco Part#	Manufacturer	Manufacturer Part #	Voltage (VDC)	Current (mA)	Voltage Range (VDC)	Rated RPM@VDC	Lead Length (")	Motor Size (Dia x Depth ")	Shaft Size (Dia x Length ")	Price 1
<a href="#">256306</a>	Jameco Reliapro	6ZK003-R	1.3	80	0.85 - 1.60	8500 @ 1.3	1	0.23 x 0.39	0.10 x 0.10	\$ 2.65
<a href="#">2236762</a>	Jinlong Machinery	Z6SCAA0061141	1.3	90	.90 - 1.6	8500 @ 1.3	PC Terminal	.27 x .40	.11 x .16	\$ 1.75
<a href="#">2230838</a>	Jinlong Machinery	C1226A001F	1.3	100	1.1 - 1.6	9000 @ 1.3	1	.47 x .11	No Shaft	\$ 1.95
<a href="#">2209035</a>	Jinlong Machinery	Z4SL2A0280131	1.3	85	1.1 - 1.6	10000 @ 3.0	1	.18 x .40	.20 x .15	\$ 1.95
<a href="#">256365</a>	Jameco Reliapro	7ZK692-R	3	60	2.40 - 3.00	6500 @ 3.0	4.7	0.28 x 0.66	0.18 x 0.22	\$ 3.49
<a href="#">256382</a>	Jameco Reliapro	7ZK681-R	3	60	2.4 - 3.6	7500 @ 3.0	1.1	0.28 x 0.66	0.12 x 0.16	\$ 3.49
<a href="#">2236771</a>	Jinlong Machinery	Z6SC0B0170081	3	75	2.2 - 3.6	8000 @3.0	PC Terminal	.27 x .40	.06 x .16	\$ 1.95
<a href="#">2237781</a>	Jameco Reliapro	6ZK053-R-PINS	3	75	1.6 - 3.6	8500 @ 3.0	1	.15 x .10	.15 x .10	\$ 3.75
<a href="#">256331</a>	Jameco Reliapro	6ZK261-R	3	75	2.4 - 3.0	8500 @ 3.0	PC Terminal	0.27 x 0.48	0.11 x 0.11	\$ 2.95
<a href="#">256314</a>	Jameco Reliapro	6ZK053-R	3	75	1.60 - 3.60	8500 @ 3.0	1	0.23 x 0.39	0.10 x 0.10	\$ 2.75
<a href="#">256314</a>	Jameco Reliapro	6ZK053-R	3	75	1.60 - 3.60	8500 @ 3.0	1	0.23 x 0.39	0.10 x 0.10	\$ 2.75
<a href="#">2189476</a>	Jameco Reliapro	C1034B850F	3	80	2.50 x 4.00	9000 @ 3.0	1	.39 x .13	No Shaft	\$ 2.95
<a href="#">2271503</a>	Jinlong Machinery	C1234B016F	3	80	2.7 - 3.3	9000 @ 3.0	2	.50 x .13	No Shaft	\$ 2.95
<a href="#">2234353</a>	Jinlong Machinery	C1020B283F	3	90	2.3 - 4.0	9000 @ 3.0	1	.39 x .09	No Shaft	\$ 1.75
<a href="#">2230846</a>	Jinlong Machinery	C1026B200F	3	80	2.5 - 4.0	10000 @ 3.0	Coin Type	.42 x .20	No Shaft	\$ 1.59
<a href="#">2230184</a>	Jinlong Machinery	Z6D12B0055211	3	70	2.40 - 3.60	11000 @ 3.0	0.87	.27 x 1.00	No Shaft	\$ 1.95
<a href="#">2218169</a>	Jameco Reliapro	JL1027-001021-30-01	3	85	1.20- 3.00	12000 @ 3.0	1	.39 x .10	No Shaft	\$ 2.95
<a href="#">2278807</a>	Jinlong Machinery	Z7AL2B1692082	3	250	2.2 - 3.6	12000 @ 3.0	1.8	.34 x 1.0	No Shaft	\$ 3.59