



[Click Here to Request a Large Quantity Quote](#)

## ELECTROMECHANICAL AUDIO COMPONENTS PIEZO BUZZERS

Jameco Part#	Manufacturer	Manufacturer Part #	Tone Mode	Operating Supply		Sound (dB)	Frequency (Hz)	Dimensions (H" x Dia")	Price 1
				(V/mA)	Voltage Range				
<a href="#">336989</a>	Jameco Valuepro	11S3120LF-TA	Single	1-16/30	6-16	100	2900	1.35 x 1.71	\$ 3.25
<a href="#">2207081</a>	Jameco Valuepro	AZ-3040E-W-LF	Speaker	3/5	3-30	85	4000	.22 x 1.18	\$ 1.09
<a href="#">2232817</a>	Mallory Products	PK-12N40P	Continuous	3/10	3-15	83	4100	.29 x .55	\$ 1.95
<a href="#">2234804</a>	Jameco Valuepro	DB-E208	Single	3/20	1-3	70	400	.91 x .61	\$ 1.49
<a href="#">2244076</a>	Jameco Valuepro	GKWT1470J05B	Single	5/3	5-25	80	4000	.27 x .55	\$ 1.25
<a href="#">2236092</a>	Kobitone Audio	254-353	Continuous	6/6	3-30	90	2800	.63 x 1.63	\$ 1.25
<a href="#">2173861</a>	Jameco Valuepro	20S1060LF - LA	Single	6/25	4-8	75	400	.91 x .61	\$ 1.75
<a href="#">2236105</a>	Kobitone Audio	254-PB517	Continuous	9/7	3-15	90	3400	.46 x .96	\$ 1.25
<a href="#">138713</a>	Jameco Valuepro	32S4120-LFPN	Single	12/7	3-16	80	4000	30 x 54	\$ 1.99
<a href="#">2271031</a>	Jameco Valuepro	32S4120	Single	12/7	3-16	80	4000	.55 x .30	\$ 1.59
<a href="#">673900</a>	Jameco Valuepro	SEP-1172	Transducer	12/7	3-28	81	3300	0.63 x 1.25	\$ 0.35
<a href="#">2202925</a>	Jameco Valuepro	PKM33EP-1001	Continuous	12/7	3-30	70	4000	.29 x 1.25	\$ 0.59
<a href="#">2120452</a>	Jameco Valuepro	LF16G	Single	12/8	3-20	85	2900	.63 x .93	\$ 1.75
<a href="#">2117430</a>	Jameco Valuepro	7P3120LF-LA	Pulse	12/10	3-15	90	3200	.98 x 1.1	\$ 2.75
<a href="#">2234337</a>	Jameco Valuepro	SL12ADF3120LF-EA	Single	12/20	6-28	90	2900	1.3 x 1.7	\$ 2.75
<a href="#">249498</a>	Jameco Valuepro	11D3120-LF-TA	Dual/Continuous	12/25	4-16	95	2900	1.35 x 1.72	\$ 3.59
<a href="#">2261298</a>	Velleman	SVM12N	Single	12/25	8-15	85	500	.92 x .58	\$ 2.49
<a href="#">2203063</a>	Jameco Valuepro	BPS8432L-12-C	Siren	12/85	6-15	105	2800	3.3 x 1.3	\$ 4.49
<a href="#">2231849</a>	Jameco Valuepro	LD-72	Continuous	12/110	6-15	108	N/A	1.87 x .90	\$ 5.95
<a href="#">2131223</a>	Velleman	SV/PS1	Siren	12/200	6-15	107	3500	2.2 x 1.7	\$ 4.29
<a href="#">207993</a>	Jameco Valuepro	SL15R3120LA-R	Siren	12/250	6-16	105	3500	2.3 x 1.6	\$ 4.75
<a href="#">32602</a>	Jameco Valuepro	11S3240LF-TA	Single	24/15	1-27	95	2900	1.4 x 1.7	\$ 2.75
<a href="#">123538</a>	Jameco Valuepro	11D3240-R	Dual/Continuous	24/20	4-28	80	2900	1.4 x 1.7	\$ 3.55
<a href="#">76021</a>	Jameco Valuepro	7S3240LFLA	Single	24/20	1.5-28	95	3200	1.0 x 1.1	\$ 3.95
<a href="#">2192499</a>	Multicorp	MBUZ-24VDC	Single	24/30	15-27	75	400	.90 x .57	\$ 0.95
<a href="#">2287511</a>	Murata	PKLCS1212E4001-R1	Transducer	25/1.5	25	84	4000	.48 x .11	\$ 1.59
<a href="#">335557</a>	Jameco Valuepro	116S3120XLF-PN	Single	3-20/3-16	3-20	90	3400	.39 x .91	\$ 2.19
<a href="#">2172906</a>	Mallory Products	SCM616N-1	Continuous	6/16 / 6-22	6-16	90	2900	1.06 x 1.7	\$ 1.75
<a href="#">2233297</a>	Mallory Products	SCM616N-W/O	Continuous	6-16 / 6-22	6-16	90	2900	1.06 x 1.7	\$ 0.89