



[Click Here to Request a Large Quantity Quote](#)

SOLAR PANELS

Jameco Part#	Manufacturer	Manufacturer Part #	Description	Dimensions (in.)	Output Voltage	Output Current	Price 1
2113666	Solar Made	GB213	40 Piece Solar Cell Grab Bag All Different Shapes and Sizes	Miscellaneous	-	-	\$ 9.95
2278879	Velleman	SOL3N	Small Polycrystalline Solar Cell 1V 200mA with Connected Wires	1.8 x 1.6 x 0.08	1 V	200 mA	\$ 2.95
2210079	Jameco Valuepro	FAD-1	1.2V Solar Cell with 5" Leads	1.2 x 0.7 x 0.1	1.2 V	75 mA	\$ 3.95
2260949	Jameco Valuepro	FAD-1-W/PINS	1.2V 75mA Solar Cell with Wires and Pins	1.2 x 0.73 x 0.1	1.2 V	75 mA	\$ 4.49
215319	Solar Made	4-3.0-100	Solar Miniature Panel 3.0 Volt 100ma with 6 Inch Red-Black Wire Leads	3.8 x 2.5 x 0.23	3 V	100 mA	\$ 10.95
1928142	Jameco Valuepro	STO.4-XI	Solar Panel 0.25W 60 x 60 x 2 mm 80mA @3.2VDC	2.36 x 2.36 x 0.1	3.2 V	80 mA	\$ 3.95
215327	Solar Made	4-6.0-50	Solar Miniature Panel 6.0 Volt 50mA with 6 Inch Red-Black Wire Leads	3.8 x 2.5 x 0.25	6 V	50 mA	\$ 11.95
2260041	Jameco Valuepro	G/S SOLAR PANEL	6 Volts 150mA 0.9 Watt Solar Panel with Alligator Clips	3.5 x 3.0 x 0.1	6 V	150 mA	\$ 9.95
2245298	Jameco Valuepro	130x85mm	6 Volts 270 mA 1.6 Watt Solar Panel with Alligator Clips	5.1 x 3.3 x 0.1	6 V	270 mA	\$ 8.95
2282559	Jameco Valuepro	ALI-MVPWR	Mini Solar Panel Module for Cell Phone Battery Chargers 110x60mm	4.3 x 2.3 x 0.12	6 V	600 mA	\$ 7.95
2162572	RU Solar	RU6715	12 Cell Monocrystal Sealed Solar Panel 103.5mW	1.46 x 1.30 x 0.07	6.9 V	15 mA	\$ 1.95
2245280	Jameco Valuepro	140x90mm	7 Volts 250 mA 1.7 Watt Solar Panel with Alligator Clips	5.5 x 3.2 x 0.1	7 V	250 mA	\$ 9.95
2221456	Picoturbine International	PEP20	7.2 Volts 200mA Solar Panel with 20" Alligator Clip Leads	4.75 x 3.5 x 0.1	7.2 V	200 mA	\$ 14.95