



[Click Here to Request a Large Quantity Quote](#)

**ELECTROMECHANICAL RELAYS - SOLID STATE**

Jameco Part#	Manufacturer	Manufacturer Part #	Type	Contact Form	Contact Voltage	Contact Current(A)	Control Voltage	Pins	Terminal Type	Dimensions (L' x W"xH")	Price 1
<a href="#">176648</a>	Kyotto	KG1005D-R	DC/DC	SPST	120 VDC	5	3-32VDC	4	SCREW TERMINAL	2.3 x 1.7 x 0.9	\$ 17.95
<a href="#">176655</a>	Kyotto	KG1010D	DC/DC	SPST	120 VDC	10	3-32VDC	4	SCREW TERMINAL	2.3 x 1.7 x 0.9	\$ 19.95
<a href="#">162342</a>	Excel Cell Electronics	ESR5102401000Z	DC/AC	SPST	240 VAC	10	3-32VDC	4	SCREW TERMINAL	1.7 x 1.1 x 2.3	\$ 16.95
<a href="#">2179462</a>	Crouzet Corporation	M-0AC5AH	DC/AC	SPST	240 VAC	20	2.75 - 8 VDC	4	SOLDER LEADS	1.7 x 1.0 x 0.4	\$ 3.49
<a href="#">162369</a>	Excel Cell Electronics	ESR5102402500Z	DC/AC	SPST	240 VAC	25	3-32VDC	4	SCREW TERMINAL	1.7 x 1.1 x 2.3	\$ 17.95
<a href="#">175214</a>	Kyotto	KB20C02A	DC/AC	SPST	280 VAC	2	3-32VDC	4	SOLDER LEADS	1.4 x 0.3 x 1.5	\$ 7.95
<a href="#">176698</a>	Kyotto	KB20C06A	DC/AC	SPST	280 VAC	6	3-32VDC	4	SOLDER LEADS	1.4 x 0.3 x 0.9	\$ 8.95
<a href="#">2273167</a>	Crydom	D4825	DC/AC	SPST	530 VAC	25	3-32VDC	4	SCREW TERMINAL	2.25 x 1.75 x .89	\$ 39.95
<a href="#">172591</a>	Kyotto	KF0602D	DC/DC	SPST	60 VDC	2	3-32VDC	4	SOLDER LEADS	1.5 x 0.3 x 0.9	\$ 8.25
<a href="#">175222</a>	Kyotto	KF0604D	DC/DC	SPST	60 VDC	4	3-32VDC	4	SOLDER LEADS	1.5 x 0.3 x 0.9	\$ 9.95
<a href="#">2218126</a>	Crydom	CMX60D10-6454	DC/DC	SPST	60 VDC	10	3-10VDC	4	SOLDER LEADS	1.60 x 0.3 x 0.9	\$ 9.95
<a href="#">1583041</a>	Clare/LXYS Corporation	LCA710	DIP-6	OPTOMOS	60 V Load	1	0.5 ohms	6	PC MOUNT	.33 x .25 x .13	\$ 4.49
<a href="#">1582997</a>	Clare/LXYS Corporation	LCA110	DIP-6	OPTOMOS	350 V Load	0.12	35 ohms	6	PC MOUNT	.33 x .25 x .13	\$ 2.19
<a href="#">1582903</a>	Clare/LXYS Corporation	LAA110	DIP-8	OPTOMOS	350 V Load	0.05	35 ohms	8	PC MOUNT	.36 x .25 x .15	\$ 3.95