



[Click Here to Request a Large Quantity Quote](#)

ELECTROMECHANICAL ROTARY SWITCHES

Jameco Part#	Manufacturer	Manufacturer Part #	Poles	Positions	Max Current (mA)	Voltage (VAC)	Index Angle(Deg)	Dimensions (L"xDia")	Shaft (Dia")	Shaft (L")	Type	Terminal	Contact Style	Price 1
2184464	Jameco Valuepro	RSL25-1-1-7-19R	1	7	300.0	125	30	1.46 x 1.22	0.285	0.5	Round	Solder	Shorting Make/Break	\$ 3.49
2236181	Taiwan Alpha Electronic	SR2513-110NS	1	10	300.0	125	30	1.36 x 1.22	0.235	0.437	D Flat Side	PCB	Non-Shorting Break/Make	\$ 1.75
2236201	Taiwan Alpha Electronic	SR2513-112NS	1	12	300.0	125	30	1.36 x 1.22	0.235	0.437	D Flat Side	PCB	Non-Shorting Break/Make	\$ 1.75
576501	C&K	A11215RNZQ	1	12	2.5/350	125/250	30	2.63 x 1.12	0.245	1.5	D Flat Side	Solder	Non-Shorting Break/Make	\$ 5.95
101532	Jameco Valuepro	G3SR026-R	1	12	300/300	125/30VDC	30	1.57 x 1.19	0.235	0.5	Slotted Knurl	Solder	Shorting Make/Break	\$ 1.95
2167322	Jameco Valuepro	KC52A13.00NPS	1	12	350/150	125/250	30	1.53 x 1.10	0.235	0.45	D Flat Side	PCB	Non-Shorting Break/Make	\$ 1.95
2276455	NKK Switches	MRB24H	2	3	400.0	28	45	.62 x .64	0.09	0.393	D Flat Side	PCB/Right Angle	Non-Shorting Break/Make	\$ 7.95
2236199	Taiwan Alpha Electronic	SR2513-24NS	2	4	300.0	125	30	1.36 x 1.22	0.235	0.437	D Flat Side	PCB	Non-Shorting Break/Make	\$ 1.75
2170353	Taiwan Alpha Electronic	SR2511F-25FN	2	5	0.3A@125VAC	300	30	1.56 x 1.22	0.245	0.312	D Flat Side	Solder	Non-Shorting Break/Make	\$ 2.75
2236236	Lorlin Electronics	CK2407	2	6	1/150	24VDC/250	30	1.54 x 1.08	0.245	0.375	D Flat Side	Solder	Non-Shorting Break/Make	\$ 1.95
576421	C&K	A20615RNZQ	2	6	2500/125	350/125VDC	30	1.50 x .874	0.3	1.5	D Flat Side	Solder	Non-Shorting Break/Make	\$ 6.95
101574	Jameco Valuepro	G3SR022-R	2	6	300/300	125/30VDC	45	1.57 x 1.19	0.235	0.5	Slotted Knurl	Solder	Shorting Make/Break	\$ 1.95
2267695	Mountain Switch	105SR251334NS	3	4	300.0	125	30	1.36 x 1.22	0.235	0.437	D Flat Side	PCB	Non-Shorting Break/Make	\$ 1.75
2236228	Lorlin Electronics	CK1026	3	4	1/150	24VDC/250	30	2.30 x 1.08	0.245	1.15	D Flat Side	Solder	Non-Shorting Break/Make	\$ 2.95
101566	Jameco Valuepro	G3SR023-R	3	4	300/300	125/30VDC	45	1.57 x 1.19	0.235	0.5	Slotted Knurl	Solder	Shorting Make/Break	\$ 1.95
2236244	Taiwan Alpha Electronic	SR2513-43NS	4	3	300.0	125	30	1.36 x 1.22	0.235	0.437	D Flat Side	PCB	Non-Shorting Break/Make	\$ 1.59
101558	Jameco Valuepro	G3SR024-R	4	3	300/300	125/30VDC	30	1.51 x 1.19	0.235	0.5	Slotted Knurl	Solder	Shorting Make/Break	\$ 1.95