



[Click Here to Request a Large Quantity Quote](#)

ELECTROMECHANICAL SWITCHES- TACTILE

Jameco Part#	Manufacturer	Mfg PN	Pins	Current Rating (mA @VDC)	Length (")	Width (")	Depth (")	Actuator Height (")	Lead Spacing W x L (")	Contact Form	Switch Function	Actuator Type	Color - Actuator/Cap	Price 1
2095120	Panasonic	EVQ11L07K	2	20 @ 15	0.2	0.24	0.14	0.11	0.20 x 0.17	SPST-NO	OFF-(ON)	Round Button	Black	\$ 0.39
199726	Panasonic	EVQ-11A04M	2	20 @ 15	0.2	0.24	0.14	0.03	0.20 x 0.17	SPST-NO	OFF-(ON)	Round Button	White	\$ 0.39
2162791	Alps Electric	SKHLAAA010	2	50 @ 12	0.2	0.14	0.14	0.06	0.26	SPST-NO	OFF-(ON)	Rectangular Button	Black	\$ 0.25
155249	Jameco Valuepro	KRS-3550-BK-R	2	50 @ 12	0.2	0.14	0.15	0.25	0.27	SPST-NO	OFF-(ON)	Rectangular Button	Brown	\$ 0.35
2280495	Alps Electric	SKHHLNA010	2	50 @ 12	0.2	0.23	0.15	0.15	0.1	SPST-NO	OFF-(ON)	Round Button	Black	\$ 0.29
2279527	Jameco Valuepro	BTS-S1104A5-3-DYL	2	50 @ 12	0.4	0.23	0.15	0.25	0.2	SPST-NO	OFF-(ON)	Round Button	Black	\$ 0.35
2282687	Jameco Valuepro	BTS-S1104A5-3-RP-DYL	2	50 @ 12	0.4	0.23	0.15	0.25	0.2	SPST-NO	OFF-(ON)	Square Button	Black	\$ 0.35
2286071	Omron	B3W-9000-G2G	3	50 @ 24	0.4	0.39	0.43	0.23	0.2	SPST-NO	OFF-(ON)	Square Button	Green	\$ 3.95
1586074	Apem Components	JTP1230A	4	20 @ 12	0.2	0.24	0.14	0.05	0.17 x 0.26	SPST-NO	OFF-(ON)	Round Button	Black	\$ 0.25
149948	Jameco Valuepro	BTS-1102B-2	4	20 @ 15	0.2	0.24	0.15	0.13	0.17 x 0.25	SPST-NO	OFF-(ON)	Round Button	Black	\$ 0.35
119011	Jameco Valuepro	01-805-R	4	20 @ 15	0.2	0.24	0.15	0.03	0.17 x 0.25	SPST-NO	OFF-(ON)	Round Button	Black	\$ 0.35
122973	Jameco Valuepro	DTS1212-R	4	20 @ 15	0.5	0.47	0.18	0.02	0.20 x 0.50	SPST-NO	OFF-(ON)	Round Button	Black	\$ 0.69
2228842	Omron	B3F-1026	4	50 @ 12	0.2	0.236	0.134	0.035	0.17 x 0.25	SPST-NO	OFF-(ON)	Flat Button	Blue	\$ 0.29
153252	Jameco Valuepro	G/S(PT-6601)-R	4	50 @ 12	0.2	0.24	0.15	0.06	0.17 x 0.25	SPST-NO	OFF-(ON)	Round Button	Black	\$ 0.35
155380	Jameco Valuepro	KRS-1273B-R	4	50 @ 12	0.5	0.47	0.14	0.14	0.17 x 0.53	SPST-NO	OFF-(ON)	Square Button	Brown	\$ 0.45
2231603	Omron	B3F-1001	4	50 @ 24	0.2	0.236	0.134	0.035	0.17 x 0.25	SPST-NO	OFF-(ON)	Flat Button	Black	\$ 0.25
162886	Omron	B3F-1000	4	50 @ 24	0.2	0.24	0.13	0.03	0.17 x 0.25	SPST-NO	OFF-(ON)	Flat Plunger	White	\$ 0.25
2076261	Omron	B3E-1100-RED	4	50 @ 24	0.2	0.24	0.19	0.07	0.17	SPST-NO	OFF-(ON)	Illuminated Button	Red	\$ 0.04
2076287	Omron	B3E-1100-GREEN	4	50 @ 24	0.2	0.24	0.19	0.07	0.17 x 0.25	SPST-NO	OFF-(ON)	Illuminated Button	Green	\$ 0.25
2286063	Omron	B3W-9000-Y2Y	4	50 @ 24	0.4	0.39	0.4	0.3	0.2	SPST-NO	OFF-(ON)	Square Button	Yellow Illum	\$ 2.75
2287919	Omron	B3W-9010G1N	4	50 @ 24	0.5	0.47	0.4	0.3	0.3	SPST-NO	OFF-(ON)	Square Button	White	\$ 2.95
2287087	Omron	B3W-9000-HG1C	4	50 @ 24	0.4	0.39	0.4	0.3	0.3	SPST-NO	OFF-(ON)	Square Button	Green Illum.	\$ 2.95
2287903	Omron	B3W-9002G2C	4	50 @ 24	0.4	0.39	0.4	0.3	0.3	SPST-NO	OFF-(ON)	Square Button	Trans Green Illum.	\$ 2.95
2287911	Omron	B3W-9002Y2C	4	50 @ 24	0.4	0.39	0.4	0.3	0.3	SPST-NO	OFF-(ON)	Square Button	Yellow Illum	\$ 2.95
2076252	C&K	KSC121JB	4	50 @ 32	0.2	0.24	0.1	0	0.15	SPST-NO	OFF-(ON)	Round Button	Gray	\$ 0.19
2280327	CIT Relay and Switch	CT1102V5-85F100	4	50 @ 50	0.2	0.24	0.26	0.23	0.17 x 0.27	SPST-NO	OFF-(ON)	Round Button	Black	\$ 0.25
2268143	Mountain Switch	101-TS4122R3201-EV	SMD	50 @ 12	0.3	0.354	0.177	0.028	0.2	SPST-NO	OFF-(ON)	Rectangular Button	Salmon	\$ 0.35
2280687	Omron	B3FS-1050	SMD	50 @ 24	0.2	0.23	0.1	0.4	0.28	SPST-NO	OFF-(ON)	Square Button	Black	\$ 0.29