



[Click Here to Request a Large Quantity Quote](#)

## SEMICONDUCTORS: MEMORY EPROM

Jameco Part#	Manufacturer	Manufacturer Part #	Description	Package Type	Configuration	Price 1
40002	Major Brands	2716	IC 2716 EPROM 16K-Bit 450ns NMOS UV Erasable and Electrically Programmable EPROM	DIP-24	2Kx8	\$ 3.95
40096	Major Brands	2732	IC 2732 EPROM 32K-Bit 450ns NMOS UV Erasable and Electrically Programmable EPROM	DIP-24	4Kx8	\$ 5.95
39950	Major Brands	27128A-15	IC 27128A-15 EPROM 128K-Bit 150ns NMOS UV Erasable Electrically Programmable Memory	DIP-28	16Kx8	\$ 3.95
40011	Major Brands	2716-1	IC 2716-1 EPROM 16K-Bit 350ns NMOS UV Erasable and Electrically Programmable EPROM	DIP-24	2Kx8	\$ 4.49
308662	Major Brands	2716A-2	IC 2716A-2 EPROM 16K-Bit 200ns NMOS UV Erasable PROM	DIP-24	2Kx8	\$ 4.95
40125	Major Brands	2732A-25	IC 2732A-25 EPROM 32K-Bit 250ns NMOS UV Erasable and Electrically Programmable EPROM	DIP-24	4Kx8	\$ 4.95
40192	Major Brands	2764-20	IC 2764-20 EPROM 64K-Bit 200ns NMOS UV Erasable and Electrically Programmed EPROM	DIP-28	8Kx8	\$ 4.95
40248	Major Brands	2764A-25	IC 2764A-25 EPROM 64K-Bit 250ns CMOS Express ROM Device	DIP-28	8Kx8	\$ 4.25
74624	Major Brands	27C010-12	IC 27C010-12 EPROM 1MEG-Bit 120ns CMOS UV Erasable Programmable ROM	DIP-32	128Kx8	\$ 3.95
146149	Major Brands	27C010-70	IC 27C010-70 EPROM 1MEG-Bit 70ns CMOS Ultraviolet Erasable Programmable Rom	DIP-32	128Kx8	\$ 4.95
65699	Major Brands	27C020-15	IC 27C020-15 EPROM 2M-Bit 150ns CMOS UV Erasable EPROM and OTP EPROM	DIP-32	256Kx8	\$ 3.95
102293	Major Brands	27C040-12	IC 27C040-12 EPROM 4M-Bit 120ns CMOS Ultraviolet Erasable Programmable Rom	DIP-32	512x8	\$ 5.95
85462	Major Brands	27C040-15	IC 27C040-15 EPROM 4096K-Bit 150ns CMOS UV Erasable Programmed ROM	DIP-32	512Kx8	\$ 4.95
266124	Major Brands	27C040-70	IC 27C040-70 EPROM 4M-Bit 70ns CMOS UV Erasable Programmable ROM	DIP-32	512Kx8	\$ 5.95
203641	Advanced Micro Devices	27C1024-120DC	1 27C1024-120 EPROM 1M-Bit 120ns CMOS Ultraviolet Erasable PROM (Ceramic Pkg)	DIP-40	65Kx16	\$ 3.95
87935	Major Brands	27C128-12	IC 27C128-12 EPROM 128K-Bit 120ns CMOS UV Erasable Programmable ROM	DIP-28	16Kx8	\$ 4.95
101101	Major Brands	27C128-20	IC 27C128-20 EPROM 128K-Bit 200ns CMOS UV Erasable Programmable ROM	DIP-28	16Kx8	\$ 4.49
39685	Major Brands	27C128-25	IC 27C128-25 EPROM 128K-Bit 250ns CMOS Ultraviolet Erasable Programmable Rom	DIP-28	16Kx8	\$ 3.95
112740	Major Brands	27C256-10	IC 27C256-10 EPROM 256K-Bit 100ns CMOS UV Erasable Programmable ROM	DIP-28	32Kx8	\$ 4.95
39714	Major Brands	27C256-15	IC 27C256-15 EPROM 256K-Bit 150ns CMOS UV Erasable Prommable ROM	DIP-28	32Kx8	\$ 4.49
39722	Major Brands	27C256-20	IC 27C256-20 EPROM 256K-Bit 200ns CMOS UV EPROM AND OTP EPROM	DIP-28	32Kx8	\$ 3.95
39731	Major Brands	27C256-25	IC 27C256-25 EPROM 256K-Bit 250ns CMOS Electrically Programmable ROM	DIP-28	32Kx8	\$ 3.49
140476	Major Brands	27C256-70	IC 27C256-70 EPROM 256K-Bit 70ns CMOS Ultraviolet Erasable Programmable ROM	DIP-28	32Kx8	\$ 5.95
131959	Major Brands	27C512-10	IC 27C512-10 EPROM 512K-Bit 100ns CMOS Ultraviolet Erasable ROM	DIP-28	64Kx8	\$ 4.49
39781	Major Brands	27C512-15	IC 27C512-15 EPROM 512K-Bit 150ns UV EPROM and OTP EPROM	DIP-28	64Kx8	\$ 3.25
203625	Major Brands	27C512-70	IC 27C512-70 EPROM 512K-Bit 70ns UV EPROM and OTP EPROM	DIP-28	64Kx8	\$ 4.95
266036	Major Brands	27C64-10	IC 27C64-10 EPROM 64K-Bit 100ns UV Erasable and Electrically Reprogrammed CMOS PROM	DIP-28	8Kx8	\$ 5.95
105304	Major Brands	27C64-12	IC 27C64-12 EPROM 64K-Bit 120ns CMOS UV Erasable Programmable ROM	DIP-28	8Kx8	\$ 5.49
39829	Major Brands	27C64-15	IC 27C64-15 EPROM 64k-Bit 150ns CMOS UV Erasable Programmable ROM	DIP-28	8Kx8	\$ 4.95
74608	Major Brands	27C64-20	IC 27C64-20 EPROM 65,536-Bit 200ns CMOS UV Erasable Electrically Progammable OTP	DIP-28	8Kx8	\$ 3.75
2287935	Advanced Micro Devices	AM27S281APC	IC AM27S281 PROM 8,192-Bit 80ns Bipolar Schottky TTL Prom (one time programmable	PDIP-28	1Kx8	\$ 4.95
40061	Various	D27256-25	IC 27256-25 EPROM 256K-Bit 250ns Production UV Erasable PROM	DIP-28	32Kx8	\$ 3.95
40230	Major Brands	M2764A-2F1	IC 2764A-20 EPROM 64K-Bit 200ns CMOS Express ROM Device Programmed & Tested OTP	DIP-28	8Kx8	\$ 4.49
697944	STMicroelectronics	M27C1001-10F1	IC 27C1001-10 EPROM 1M-Bit 100ns UV EPROM and OTP EPROM	DIP-32	128Kx8	\$ 4.75
697987	STMicroelectronics	M27C1001-15F1	IC 27C1001 EPROM 1M-Bit 150ns Ultraviolet Erase and OTP (one time programmable)	DIP-32	128Kx8	\$ 6.95
698031	STMicroelectronics	M27C2001-12F1	IC 27C2001-12 EPROM 2M-Bit 120ns UV EPROM and OTP EPROM	DIP-32	256Kx8	\$ 5.95
698082	STMicroelectronics	M27C256B-10F1	IC 27C256B-10 EPROM 256K-Bit 100ns UV EPROM and OTP EPROM	DIP-28	32Kx8	\$ 5.49
698091	STMicroelectronics	M27C256B-12F1	IC 27C256B-12 EPROM 256K-Bit 120ns UV EPROM and OTP EPROM	DIP-28	32Kx8	\$ 4.95
698111	STMicroelectronics	M27C256B-15F1	IC 27C256B-15 EPROM 256K-Bit 150ns UV EPROM and OTP EPROM	DIP-28	32Kx8	\$ 4.49
698226	STMicroelectronics	M27C512-12F1	IC 27C512-12 EPROM 512K-Bit 120ns UV EPROM and OTP EPROM	DIP-28	64Kx8	\$ 4.95
698234	STMicroelectronics	M27C512-15F1	IC 27C512-15 EPROM 512K-Bit 150ns UV EPROM and OTP EPROM	DIP-28	64Kx8	\$ 4.49
698322	STMicroelectronics	M27C64A-15F1	IC 27C64A-15 EPROM 64K-Bit 150ns UV EPROM and OTP EPROM	DIP-28	8Kx8	\$ 5.95



[Click Here to Request a Large Quantity Quote](#)

## SEMICONDUCTORS: MEMORY EPROM

Jameco Part#	Manufacturer	Manufacturer Part #	Description	Package Type	Configuration	Price 1
<a href="#">33611</a>	National Semiconductor	TMS2716	IC 2716 EPROM 16,384-Bit 450ns Eraseable Programmable Rom	DIP-24	2Kx8	\$ 2.39
<a href="#">2288047</a>	Major Brands	WS57C45-35MB	IC 57C45-35 PROM 16K-Bit 35ns Registered CMOS High Speed Military (one time programmable)	PDIP-24	2Kx8	\$ 9.95