



[Click Here to Request a Large Quantity Quote](#)

INTERCONNECTS AC POWER RECEPTACLES

Jameco Part#	Manufacturer	Manufacturer Part #	Product Type	Connector Type	Contact Gender	Current Rating (A)	Voltage Rating (VAC)	Mounting Type	Termination Type	Filtered	Fused	Switch Function	Body Orientation	Price 1
2235874	Kobiconn	161-R3012E	AC Receptacle, Combo	C14, C13	Male, Female	10	250	Panel Mount, Snap-In	0.187" Quick Connect	No	No	Not Switched	Straight	\$ 1.25
2235891	Kobiconn	161-R3012S	AC Receptacle, Combo	C14, C13	Male, Female	10	250	Panel Mount, Snap-In	0.187" Quick Connect	No	Yes	Not Switched	Straight	\$ 1.25
2276999	Electri-Cord	0718-1-PP	AC Receptacle, Female Socket	C13	Female	10	250	Panel Mount, Snap-In	PCB, Right Angle	No	No	Not Switched	Right Angle	\$ 0.79
1954640	Jameco Valuepro	EAC405	AC Receptacle, Female Socket	C13	Female	15	250	Panel Mount, Snap-In	0.187" Faston	No	No	Not Switched	Straight	\$ 0.59
2277007	Electri-Cord	0709-PQ	AC Receptacle, Female Socket	NEMA 5-15R	Female	15	125	Panel Mount, Snap-In	0.187" Quick Connect	No	No	Not Switched	Straight	\$ 0.99
2114095	Adam Technologies	NEMA-5-2	AC Receptacle, Female Socket	NEMA 5-15R	Female	15	125	Panel Mount, Snap-In	Fork terminals	No	No	Not Switched	Straight	\$ 0.79
2289519	Jameco Valuepro	5320-SI LEVITON	AC Receptacle, Female Socket	NEMA 5-15R (2x)	Female	15	125	Panel Mount, Front, Screw Flange	Quickwire Push-in & screw terminals	No	No	Not Switched	Straight	\$ 1.95
1951529	Delta Electronics	01DEEG3V	AC Receptacle, Male Blades	C14	Male	1	250	Panel Mount, Front, Screw Flange	0.250" Faston	Yes	No	Not Switched	Right Angle	\$ 0.29
1172613	TE Connectivity	1EGG1-2	AC Receptacle, Male Blades	C14	Male	1	250	Panel Mount, Front, Screw Flange	0.250" Faston	Yes	Yes	Not Switched	Straight	\$ 14.95
1951588	Delta Electronics	06DEEG3V	AC Receptacle, Male Blades	C14	Male	6	250	Panel Mount, Front, Screw Flange	0.250" Faston	Yes	No	Not Switched	Right Angle	\$ 0.75
2114124	Adam Technologies	PLF-6DZ2KR	AC Receptacle, Male Blades	C14	Male	6	250	Panel Mount, Front, Screw Flange	0.250" Faston	Yes	Yes	Switched	Straight	\$ 8.95
2234652	Schaffner	FN282B-6-06	AC Receptacle, Male Blades	C14	Male	6	250	Panel Mount, Front, Screw Flange	0.250" Faston	Yes	Yes	Switched	Straight	\$ 9.95
2179729	Jameco Valuepro	10958	AC Receptacle, Male Blades	C14	Male	6	250	Panel Mount, Rear, Screw Flange	0.250" Solder Eyelet	No	No	Not Switched	Straight	\$ 0.25
2181095	Schaffner	FN379B-6	AC Receptacle, Male Blades	C14	Male	6	250	Panel Mount, Snap-In	0.14" Solder Lug	Yes	Yes	Not Switched	Straight	\$ 24.95
2290631	Schurter	PF11	AC Receptacle, Male Blades	C14	Male	6	250	Panel Mount, Snap-In	0.187" Quick Connect	No	Yes	Not Switched	Straight	\$ 1.95
2235920	Kobiconn	161-R331	AC Receptacle, Male Blades	C14	Male	10	250	Cable Mount	Quick Connect	No	No	Not Switched	Straight	\$ 1.25
265528	Jameco Valuepro	JR-101-F	AC Receptacle, Male Blades	C14	Male	10	250	Panel Mount, Front, Screw Flange	0.185" Faston	No	Yes	Not Switched	Straight	\$ 1.49
2232868	Schurter	DC11.0001.001	AC Receptacle, Male Blades	C14	Male	10	250	Panel Mount, Front, Screw Flange	0.187" Quick Connect	No	No	Switched	Straight	\$ 4.95
2189599	Adam Technologies	PLF-1DZ2KR	AC Receptacle, Male Blades	C14	Male	10	250	Panel Mount, Front, Screw Flange	0.250" Faston	Yes	Yes	Switched	Straight	\$ 4.95
2277119	Schurter	5220.0623.1	AC Receptacle, Male Blades	C14	Male	10	250	Panel Mount, Front, Screw Flange	0.250" Quick Connect	Yes	Yes	Not Switched	Straight	\$ 17.95
2235989	Kobiconn	161-R301B07	AC Receptacle, Male Blades	C14	Male	10	250	Panel Mount, Front, Screw Flange	PCB, Right Angle	No	No	Not Switched	Right Angle	\$ 0.75
2178507	Arndt	6100-4115	AC Receptacle, Male Blades	C14	Male	10	250	Panel Mount, Snap-In	0.14" Solder Lug	No	No	Not Switched	Straight	\$ 0.29
2157546	Adam Technologies	IEC-GS-1-200	AC Receptacle, Male Blades	C14	Male	10	250	Panel Mount, Snap-In	0.187" Quick Connect	No	Yes	Switched	Straight	\$ 3.25
117445	Jameco Valuepro	JR-101-1FS-R	AC Receptacle, Male Blades	C14	Male	10	250	Panel Mount, Snap-In	0.187" Quick Connect	No	Yes	Not Switched	Straight	\$ 1.95
2280551	Radius Power	RP183SN-10-0	AC Receptacle, Male Blades	C14	Male	10	250	Panel Mount, Snap-In	0.187" Quick Connect	Yes	No	Switched	Straight	\$ 3.95
2277111	Schurter	6200-4115	AC Receptacle, Male Blades	C14	Male	10	250	Panel Mount, Snap-In	Solder terminal	No	Yes	Not Switched	Straight	\$ 2.25
147901	Jameco Valuepro	0701-1-CN-R	AC Receptacle, Male Blades	C14	Male	15	250	Panel Mount, Front, Screw Flange	0.187" Faston	No	No	Not Switched	Straight	\$ 1.09
2236033	Kobiconn	161-R301SN01	AC Receptacle, Male Blades	C14	Male	15	250	Panel Mount, Front, Screw Flange	0.187" Quick Connect	No	No	Not Switched	Straight	\$ 0.75
16652	Jameco Valuepro	G1W106-R	AC Receptacle, Male Blades	C14	Male	15	250	Panel Mount, Front, Screw Flange	0.250" Faston	No	No	Not Switched	Straight	\$ 0.79
2287615	Major Brands	R301	AC Receptacle, Male Blades	C14	Male	15	250	Panel Mount, Front, Screw Flange	0.250" Faston	No	No	Not Switched	Straight	\$ 0.99
2280431	Jameco Valuepro	8301213	AC Receptacle, Male Blades	C14	Male	15	250	Panel Mount, Front, Screw Flange	0.250" Faston	No	No	Not Switched	Straight	\$ 0.99
2178494	Arndt	EAC-324	AC Receptacle, Male Blades	C14	Male	15	250	Panel Mount, Rear, Screw Flange	0.16" Solder Lug	No	No	Not Switched	Straight	\$ 0.29
2280439	Jameco Valuepro	703W	AC Receptacle, Male Blades	C14	Male	15	250	Panel Mount, Rear, Screw Flange	PCB, Right Angle	No	No	Not Switched	Right Angle	\$ 0.95
2178515	Switchcraft	EAC-409	AC Receptacle, Male Blades	C14	Male	15	250	Panel Mount, Snap-In	0.16" Solder Lug	No	No	Not Switched	Straight	\$ 4.95
2095525	Adam Technologies	IEC-GS-1-100	AC Receptacle, Male Blades	C14	Male	15	250	Panel Mount, Snap-In	0.187" Faston	No	Yes	Switched	Straight	\$ 2.95
2189521	Adam Technologies	IEC-GS-1-150-SPR	AC Receptacle, Male Blades	C14	Male	15	250	Panel Mount, Snap-In	0.187" Quick Connect	No	Yes	Switched	Straight	\$ 2.95
2229298	Schurter	6100-43	AC Receptacle, Male Blades	C14	Male	15	250	Panel Mount, Snap-In	0.250" Faston	No	No	Not Switched	Straight	\$ 0.39
147109	Jameco Valuepro	0711-PW	AC Receptacle, Male Blades	C14	Male	15	250	Panel Mount, Snap-In	0.250" Quick Connect	No	No	Not Switched	Straight	\$ 0.99