



[Click Here to Request a Large Quantity Quote](#)

INTERCONNECTS RECTANGULAR CONNECTORS 3.96MM SERIES

Jameco Part#	Manufacturer	Manufacturer Part #	Gender	Number of Contacts	Number of Rows	Mximum Current Rating (Amp)	Maximum Voltage Rating	Maximum Contact Resistance	Contact Plating	Contact Material	Housing Color	Housing Material	Body Orientation	Price 1
104433	Jameco Valuepro	7900F-3-R	Female	3	1	5	250VAC/250VDC				Natural/White	Nylon 66	Straight	\$ 0.25
463435	Molex	09-50-3031	Female	3	1	7	250VAC/250VDC				Natural/White	Nylon	Straight	\$ 0.25
463443	Molex	09-50-3041	Female	4	1	5	250VAC				Natural/White	Polyester	Straight	\$ 0.25
236161	TE Connectivity	640250-4	Female	4	1	10	250VAC				Natural/White	Nylon	Straight	\$ 0.25
463451	Molex	09-50-3051	Female	5	1	7	250VAC/250VDC				Natural/White	Polyester	Straight	\$ 0.25
104732	Jameco Valuepro	7900F-6-R	Female	6	1	5	250VAC/250VDC				Natural/White	Nylon 66	Straight	\$ 0.29
463486	Molex	09-50-3081	Female	8	1	7	250VAC				Natural/White	Nylon	Straight	\$ 0.39
879861	Molex	26-60-4020	Male	2	1	7	250VAC/250VDC	6mOhm	Tin Over Copper	Brass	Natural/White	Polyester	Straight	\$ 0.25
797179	Molex	26-64-5020	Male	2	1	7	250VAC/250VDC	6mOhm	Tin Over Copper	Brass	Natural/White	Thermoplastic	Right Angle	\$ 0.29
879887	Molex	26-60-4030	Male	3	1	7	250VAC/250VDC	6mOhm	Gold	Brass	Natural/White	Polyester	Right Angle	\$ 0.35
104792	Jameco Valuepro	7900-4-R	Male	4	1	5	250VAC/250VDC	6mOhm	Tin	Brass	Natural/White	Nylon 66	Straight	\$ 0.43
879924	Molex	26-60-4050	Male	5	1	7	250VAC/250VDC	6mOhm	Tin	Brass	Natural/White	Polyester	Straight	\$ 0.47
879941	Molex	26-60-4060	Male	6	1	7	250VAC/250VDC	6mOhm	Tin Over Copper	Brass	Natural/White	Polyester	Straight	\$ 0.53
879983	Molex	26-60-4080	Male	8	1	7	250VAC/250VDC	6mOhm	Tin Over Copper	Brass	Natural/White	Polyester	Straight	\$ 0.95
880001	Molex	26-60-4090	Male	9	1	7	250VAC/250VDC	6mOhm	Tin Over Copper	Brass	Natural/White	Polyester	Straight	\$ 0.79