



[Click Here to Request a Large Quantity Quote](#)

INTERCONNECTS CIRCULAR DIN CONNECTORS

Jameco Part#	Manufacturer	Manufacturer Part #	Gender	Total Number of Contacts	Connector Style	Maximum Current Rating	Maximum Voltage Rating	Termination	Mounting Type	Price 1
2235971	CUI	SD-30SN	Socket	3	DIN(180 Degree)	1A,2A	100VAC,12VDC	Solder Lug	Panel Mount	\$ 1.95
2288455	CUI	SD-30J	Socket	3	DIN(180 Degree)	2A	100VAC	Solder	Free Hanging (In-Line)	\$ 1.75
2272767	CUI	SDS-30J	Socket	3	DIN(180 Degree)	2A	100VAC	Solder	Through Hole, Right Angle	\$ 1.29
2272791	CUI	MD-30SN	Socket	3	Mini DIN	1A,2A	100VAC,12VDC	Solder	Panel Mount	\$ 1.59
2288487	CUI	MD-30J	Socket	3	Mini DIN	1A,2A	100VAC,12VDC	Solder	Free Hanging (In-Line)	\$ 1.75
2272687	CUI	MD-30CV	Socket	3	Mini DIN	1A,2A	100VAC,12VDC	Solder	Panel Mount, Through Hole	\$ 1.95
2272743	CUI	SD-40SN	Socket	4	DIN(210 Degree)	1A,2A	100VAC,12VDC	Solder Lug	Panel Mount	\$ 2.25
2288463	CUI	SD-40J	Socket	4	DIN(210 Degree)	2A	100VAC	Solder	Free Hanging (In-Line)	\$ 1.95
2178531	CUI	SDS-40J	Socket	4	DIN(210 Degree)	2A	100VAC	Solder	Through Hole, Right Angle	\$ 1.35
140791	CUI	MD-40SM	Socket	4	Mini DIN	1A,2A	100VAC,12VDC	Solder	Through Hole, Right Angle	\$ 1.49
2288495	CUI	MD-40J	Socket	4	Mini DIN	1A,2A	100VAC,12VDC	Solder	Free Hanging (In-Line)	\$ 1.95
2272711	CUI	MD-40CV	Socket	4	Mini DIN	1A,2A	100VAC,12VDC	Solder	Panel Mount, Through Hole	\$ 2.09
2205510	CUI	MD-40SN	Socket	4	Mini DIN	1A,2A	100VAC,12VDC	Solder	Panel Mount	\$ 1.95
2192667	Arndt	SOCK-RA-5	Socket	5	DIN(180 Degree)	1A	100VAC	Solder	Free Hanging (In-Line)	\$ 1.09
15844	CUI	SD-50SN	Socket	5	DIN(180 Degree)	1A,2A	100VAC,12VDC	Solder Lug	Panel Mount	\$ 2.49
2289207	CUI	SD-50J	Socket	5	DIN(180 Degree)	2A	100VAC	Solder	Free Hanging (In-Line)	\$ 1.49
29399	Jameco Valuepro	B-1001-R	Socket	5	DIN(180 Degree)	2A	100VAC	Solder	Free Hanging (In-Line)	\$ 1.09
2205501	Switchcraft	57HB5F	Socket	5	DIN(180 Degree)	2A	34VDC	Solder Lug	Panel Mount	\$ 1.49
2288503	CUI	MD-50J	Socket	5	Mini DIN	1A,2A	100VAC,12VDC	Solder	Free Hanging (In-Line)	\$ 2.25
2272695	CUI	MD-50CV	Socket	5	Mini DIN	1A,2A	100VAC,12VDC	Solder	Panel Mount, Through Hole	\$ 1.95
15852	CUI	SD-60SN	Socket	6	DIN(240 Degree)	1A,2A	100VAC,12VDC	Solder Lug	Panel Mount	\$ 2.59
2288471	CUI	SD-60J	Socket	6	DIN(240 Degree)	2A	100VAC	Solder	Free Hanging (In-Line)	\$ 1.95
2272783	CUI	SDS-60J	Socket	6	DIN(240 Degree)	2A	100VAC	Solder	Through Hole, Right Angle	\$ 1.49
2272807	CUI	MD-60SN	Socket	6	Mini DIN	1A,2A	100VAC,12VDC	Solder	Panel Mount	\$ 1.95
2288511	CUI	MD-60J	Socket	6	Mini DIN	1A,2A	100VAC,12VDC	Solder	Free Hanging (In-Line)	\$ 2.25
119475	CUI	MD-60SM	Socket	6	Mini DIN	1A,2A	100VAC,12VDC	Solder	Through Hole, Right Angle	\$ 1.09
2076762	CUI	MD-60CV	Socket	6	Mini DIN	1A,2A	100VAC,12VDC	Solder	Panel Mount, Through Hole	\$ 2.09
2246531	Jameco Valuepro	A170718LH	Socket	6	Mini DIN	1A,2A	100VAC,12VDC	Solder	Panel Mount, Through Hole	\$ 1.25
2272799	CUI	MD-50SN	Socket	6	Mini DIN	1A,2A	100VAC,12VDC	Solder Lug	Free Hanging (In-Line)	\$ 1.95
2235997	Kobiconn	161-2007	Socket	7	DIN(180 Degree)	1A	100VAC	Solder	Through Hole, Right Angle	\$ 0.59
2281055	CUI	MD-70SM	Socket	7	Mini DIN	1A,2A	100VAC,12VDC	Solder	Through Hole, Right Angle	\$ 1.25
15861	CUI	SD-80SN	Socket	8	DIN(270 Degree)	1A,2A	100VAC,12VDC	Solder Lug	Panel Mount	\$ 2.75
29410	CUI	SDS-80J	Socket	8	DIN(270 Degree)	2A	100VAC	Solder	Through Hole, Right Angle	\$ 1.95
2288479	CUI	SD-80J	Socket	8	DIN(270 Degree)	2A	100VAC	Solder	Free Hanging (In-Line)	\$ 2.09
207722	CUI	MD-80SM	Socket	8	Mini DIN	1A,2A	100VAC,12VDC	Solder	Through Hole, Right Angle	\$ 1.95
2272815	CUI	MD-80SN	Socket	8	Mini DIN	1A,2A	100VAC,12VDC	Solder	Panel Mount	\$ 2.09
2272703	CUI	MD-80CV	Socket	8	Mini DIN	1A,2A	100VAC,12VDC	Solder	Panel Mount, Through Hole	\$ 2.09
2272759	CUI	SD-30	Plug	3	DIN(180 Degree)	1A,2A	100VAC,12VDC	Solder Lug	Free Hanging (In-Line)	\$ 0.95
2272719	CUI	MD-30	Plug	3	Mini DIN	1A,2A	100VAC,12VDC	Solder	Free Hanging (In-Line)	\$ 1.25



[Click Here to Request a Large Quantity Quote](#)

INTERCONNECTS CIRCULAR DIN CONNECTORS

Jameco Part#	Manufacturer	Manufacturer Part #	Gender	Total Number of Contacts	Connector Style	Maximum Current Rating	Maximum Voltage Rating	Termination	Mounting Type	Price 1
2272751	CUI	SD-40	Plug	4	DIN(210 Degree)	1A,2A	100VAC,12VDC	Solder Lug	Free Hanging (In-Line)	\$ 1.29
2272727	CUI	MD-40	Plug	4	Mini DIN	1A,2A	100VAC,12VDC	Solder	Free Hanging (In-Line)	\$ 1.39
142280	Jameco Valuepro	171-2504	Plug	4	Mini DIN	1A,2A	100VAC,12VDC	Solder	Free Hanging (In-Line)	\$ 0.65
15879	CUI	SD-50	Plug	5	DIN(180 Degree)	1A,2A	100VAC,12VDC	Solder Lug	Free Hanging (In-Line)	\$ 1.39
2288447	CUI	SD-50J	Plug	5	DIN(180 Degree)	2A	100VAC	Solder	Free Hanging (In-Line)	\$ 2.19
2272735	CUI	MD-50	Plug	5	Mini DIN	1A,2A	100VAC,12VDC	Solder Lug	Free Hanging (In-Line)	\$ 1.49
2178620	Switchcraft	09CL4M	Plug	6	DIN	3A	34VDC	Solder	Free Hanging (In-Line)	\$ 5.95
2178638	Arndt	12BL6M	Plug	6	DIN	3A	34VDC	Solder Lug	Free Hanging (In-Line)	\$ 5.95
142262	CUI	MD60	Plug	6	DIN(180 Degree)	1A,2A	100VAC,12VDC	Solder Lug	Free Hanging (In-Line)	\$ 1.25
15887	CUI	SD-60	Plug	6	DIN(240 Degree)	1A,2A	100VAC,12VDC	Solder	Free Hanging (In-Line)	\$ 1.39
15895	CUI	SD-80	Plug	8	DIN(270 Degree)	1A,2A	100VAC,12VDC	Solder	Free Hanging (In-Line)	\$ 1.49
2288519	CUI	MD-80J	Plug	8	Mini DIN	1A,2A	100VAC,12VDC	Solder Lug	Free Hanging (In-Line)	\$ 2.25
111878	CUI	MD-80	Plug	8	Mini DIN	1A,2A	100VAC,12VDC	Solder Lug	Free Hanging (In-Line)	\$ 1.59