



[Click Here to Request a Large Quantity Quote](#)

**LCD MODULES CHARACTER DISPLAYS**

Jameco SKU	Mfr Name	Mfr P/N	Characters x Lines	Interface	Display Mode	Character / Background Color	Backlight (Y/N)	Character Format	Display Size		Input Current mA	Input Voltage Max (V)	Module Size (WxHxD) Inches	Price 1
									(WxH) Inches	Inches				
2270959	Arndt	CCM0820	8x2	Parallel 4/8 Bit	—	Black / None	N	5x8	1.5 x 0.62	2	3.3	2.3 X 1.2 X 0.4	\$ 3.95	
2265927	Vikay America	2316STLDYGTN	16x1	Parallel 4/8 Bit	Dot Matrix LCD	Black / Yellow-Green	Y	5x8	1.7 x 0.5	1	5	2.36 X 1.30 X.46	\$ 1.49	
2265751	Samsung Electronics	UC16130	16x1	Parallel 4/8 Bit	—	Black / Green	Y	5x8	2.54 x 0.54	2	5	3.15 X 1.41 X 0.44	\$ 2.75	
2265919	Samsung Electronics	UC16116	16x1	Parallel 8 Bit	—	Black / None	N	5x8	2.54 x 0.51	2	5	3.15 X 1.42 X 0.39	\$ 1.95	
2160374	DFRobot	FIT0127	16x2	Parallel	—	White / Blue	Y	5x8	2.6 x 0.63	3	5	3.15 X 1.42 X 0.47	\$ 10.95	
2211071	Microtips Technology	MTC-S16204XFYHSAY-08	16x2	Parallel 4 Bit	STN Transflective	Black / Yellow-Green	Y	5x7	2.45 x 0.70	3	4.5	3.31 X 1.73 X 0.56	\$ 6.95	
2265935	Arndt	DENS-16-2	16x2	Parallel 4/8 Bit	—	Black / None	N	5x8	2.5 x 0.624	2	5	3.35 X 1.42 X 0.37	\$ 1.19	
2265943	Solomon Goldentek Display	LM1181	16x2	Parallel 4/8 Bit	—	Black / Green	Y	5x8	2.5 x 0.624	2	5	3.32 X 1.75 X 0.48	\$ 2.75	
2265951	Samsung Electronics	UC16231	16x2	Parallel 4/8 Bit	—	Black / None	N	5x8	2.5 x 0.62	2	5	3.35 X 1.42 X 0.44	\$ 3.59	
2231030	Lumex Optoelectronics	LCM-SO1602DTR/M	16x2	Parallel 4/8 Bit	TN Reflective	Grey / None	N	5x8	1.84 x 0.45	3	5	2.6 X 1.0 X 0.27	\$ 6.95	
2160358	DFRobot	DFR0063	16x2	Parallel I2C/TWI	—	White / Blue	Y	5x8	2.5 x 0.58	n/a	5	3.23 X 1.38 X 0.71	\$ 11.95	
2135638	Jameco Valuepro	LK162-12-WB-C166	16x2	Serial I2C	—	White / Blue	Y	5x8	2.5x.7	9	5	3.2 x 1.5 x 0.8	\$ 13.95	
210761	Jameco Valuepro	HC16401(HYUNDAI)	16x4	Parallel 4/8 Bit	TN Reflective	Black / None	N	5x8	2.4 x 1.0	2.2	6.5	3.4 X 2.4 X 0.3	\$ 7.95	
2265767	Samsung Electronics	UC20102	20x1	Parallel 8 Bit	—	Black / None	N	5x8	6.09 x 0.63	2	5	7.187 X 1.32 X 0.36	\$ 2.75	
2265775	Samsung Electronics	SAM-20-2-EL	20x2	Parallel 4/8 Bit	—	Black / Yellow	Y	5x8	3.27 x 0.73	1	5	4.57 X 1.46 X 0.39	\$ 2.75	
2155372	Arndt	HC20216NYU-LYVO	20x2	Parallel 8 Bit	STN Transflective	Black / Yellow-Green	Y	5x8	4.86 x 0.923	—	5	5.75 x 1.69 x 0.52	\$ 3.29	
2109309	Parallax	27979	20x4	Serial	STN Pos. Transflective	Black / Yel,Grn	Y	5x8	—	50	5	2.37 x 3.86	\$ 40.79	
2265743	Samsung Electronics	UC2410	24x1	Parallel 8 Bit	—	Black / None	N	5x8	3.93 x 0.54	2	5	4.97 X 1.42 X 0.38	\$ 1.19	
2265783	Epson	EPS-24-2-RIB-CBL	24x2	Parallel	—	Black / None	N	5x8	3.68 x 0.63	2	5	4.28 X 1.38 X 0.42	\$ 1.49	
2265799	Samsung Electronics	UC40401	40x4	Parallel 4/8 Bit	—	Black / None	N	5x8	5.75 x 1.16	2.5	5	7.5 X 2.16 X 0.375	\$ 3.95	