



[Click Here to Request a Large Quantity Quote](#)

**DISCRETE LEDS - STANDARD 5MM LEDS**

Jameco Part#	Manufacturer	Manufacturer Part #	Type	Color	Lens Type	Package	Wavelength	Luminous Intensity - Iv (mcd)	Viewing Angle (deg)	Forward Voltage - Vf (Typ.)	Forward Current - If (Typ.)	Height (mm)	Mounting	Pin Count	Price 1
333851	Jameco Valuepro	UT6371-41-M1-R	Standard	Red	Diffused	3mm, T-1	643 nm	65	60	2.2	30 mA	5.25	0.1"	2	\$ 0.12
2186515	Lite-On Electronics	LTL-4202	Standard	Red	Non Diffused	3mm, T-1	655 nm	5.6	45	1.7	40 mA	5.2	0.1"	2	\$ 0.25
2006705	Lite-On Electronics	LTL-1CHYE	Standard	Yellow	Non Diffused	3mm, T-1	588 nm	40	45	2.6	20 mA	5.2	0.1"	2	\$ 0.25
138691	Jameco Valuepro	LVB3330	Standard	Blue	Diffused	5mm, T-1 3/4	430 nm	10	36	5.5	30 mA	8.6	0.1"	2	\$ 0.99
333227	Jameco Valuepro	LG13530	Standard	Green	Diffused	5mm, T-1 3/4	565 nm	25	36	2.6	30 mA	8.6	0.1"	2	\$ 0.09
693901	MCD Electronics	MCDL-5013GD	Standard	Green	Diffused	5mm, T-1 3/4	565 nm	12.5	60	2.1	10 mA	0.1"	2	\$ 0.10	
334086	Jameco Valuepro	LG13740	Standard	Green	Diffused	5mm, T-1 3/4	565 nm	20	68	2.6	30 mA	0.1"	2	\$ 0.10	
2230547	Sunled Corporation	XLUG53C	Standard	Green	Non Diffused	5mm, T-1 3/4	565 nm	79	20	2	30 mA	8.6	0.1"	2	\$ 0.12
34761	Jameco Valuepro	LG3330	Standard	Green	Diffused	5mm, T-1 3/4	565 nm	30	36	2.6	30 mA	0.1"	2	\$ 0.15	
790217	Lite-On Electronics	LTL-307GE	Standard	Green	Non Diffused	5mm, T-1 3/4	565 nm	29	40	2	30 mA	8.6	0.2"	2	\$ 0.25
104256	Everlight Electronics	MV64539.MP7	Standard	Green	Diffused	5mm, T-1 3/4	565 nm	30	46	2.6	30 mA	0.1"	2	\$ 0.45	
697653	Lite-On Electronics	LTL-4233	Standard	Green	Diffused	5mm, T-1 3/4	569 nm	19	36	2.6	30 mA	0.1"	2	\$ 0.12	
697531	Lite-On Electronics	LTL-307G	Standard	Green	Diffused	5mm, T-1 3/4	569 nm	19	50	2.6	30 mA	8.6	0.1"	2	\$ 0.12
2193897	Huey Jann Electronics	HB5-133	Standard	Green	Diffused	5mm, T-1 3/4	570 nm	80	30	2.15	25 mA	8.7	0.1"	2	\$ 0.25
2155268	Jameco Valuepro	BVL-501E1D	Standard	Orange	Diffused	5mm, T-1 3/4	622 nm	750	25	2.1	30 mA	8.6	0.1"	2	\$ 0.25
152857	Jameco Valuepro	LT1841R81-R	Standard	Orange	Diffused	5mm, T-1 3/4	630 nm	23.1	45	2.4	20 mA	8.7	0.1"	2	\$ 0.25
107393	Jameco Valuepro	LE3330	Standard	Orange	Diffused	5mm, T-1 3/4	635 nm	24	36	2.6	30 mA	0.1"	2	\$ 0.12	
302033	Jameco Valuepro	LT1814-81	Standard	Orange	Non Diffused	5mm, T-1 3/4	650 nm	10	10	2.1	30 mA	8.7	0.1"	2	\$ 0.25
210825	BV Optotech	BVU-5M1QN1	Standard	Orange Red	Diffused	5mm, T-1 3/4	615 nm	600	30	2.1	20 mA	8.6	0.1"	2	\$ 0.25
2193900	Lite-On Electronics	LTL-307UR-002	Standard	Red	Diffused	5mm, T-1 3/4	470 nm	12.6	50	1.8	40 mA	8.3	0.1"	2	\$ 0.15
697522	Lite-On Electronics	LTL-307E-002A	Standard	Red	Diffused	5mm, T-1 3/4	623 nm	19	50	2.6	30 mA	0.1"	2	\$ 0.12	
790081	Lite-On Electronics	LTL-10223W	Standard	Red	Diffused	5mm, T-1 3/4	623 nm	60	60	2.6	30 mA	0.1"	2	\$ 0.12	
697602	Lite-On Electronics	LTL-4223	Standard	Red	Diffused	5mm, T-1 3/4	623 nm	19	36	2.6	30 mA	0.1"	2	\$ 0.25	
2006730	Lite-On Electronics	LTL-307E-3	Standard	Red	Diffused	5mm, T-1 3/4	623 nm	12.6	40	2.6	30 mA	8.7	0.1"	2	\$ 0.25
253753	Major Brands	HLMP-3301	Standard	Red	Diffused	5mm, T-1 3/4	635 nm	7	65	3	30 mA	8.89	0.1"	2	\$ 0.25
333973	Jameco Valuepro	UT1871-81-M1-R	Standard	Red	Diffused	5mm, T-1 3/4	643 nm	75	36	2.2	30 mA	0.1"	2	\$ 0.12	
2186321	Lite-On Electronics	LTL-4204	Standard	Red	Non Diffused	5mm, T-1 3/4	655 nm	19	16	2	40 mA	8.6	0.1"	2	\$ 0.05
94511	Jameco Valuepro	LH3330	Standard	Red	Diffused	5mm, T-1 3/4	697 nm	4.5	36	2.6	15 mA	8.6	0.1"	2	\$ 0.15
2276831	Major Brands	HLMP-3850	Standard	Yellow	Water Clear	5mm, T-1 3/4	583 nm	140	24	2.1	30 mA	9.19	0.1"	2	\$ 0.45
34825	Jameco Valuepro	LY3330	Standard	Yellow	Diffused	5mm, T-1 3/4	585 nm	12	36	2.8	20 mA	0.1"	2	\$ 0.15	
1995927	Lite-On Electronics	LTL-10253	Standard	Yellow	Diffused	5mm, T-1 3/4	585 nm	12.6	60	2.1	20 mA	7.2	0.1"	2	\$ 0.19
2193985	Arndt	MYB51D	Standard	Yellow	Diffused	5mm, T-1 3/4	585 nm	55	50	2.6	20 mA	0.87	0.1"	2	\$ 0.25
697549	Lite-On Electronics	LTL-307Y	Standard	Yellow	Diffused	5mm, T-1 3/4	588 nm	29	50	2.6	20 mA	0.1"	2	\$ 0.09	
2121666	Lite-On Electronics	LTL-307YE-081	Standard	Yellow	Non Diffused	5mm, T-1 3/4	588 nm	40	40	2.1	20 mA	8.6	0.1"	2	\$ 0.15
697696	Lite-On Electronics	LTL-4253	Standard	Yellow	Diffused	5mm, T-1 3/4	588 nm	19	36	2.6	20 mA	8.6	0.1"	2	\$ 0.25
334108	Jameco Valuepro	UT1831-81-R	Standard	Yellow	Non Diffused	5mm, T-1 3/4	590 nm	90	10	2.6	30 mA	8.6	0.1"	2	\$ 0.12
2152104	Jameco Valuepro	MCDL-10003SGD	Standard	Green	Diffused	10mm, T-3 1/4	570 nm	50	60	2.2	30 mA	0.1"	2	\$ 0.59	
2152139	Jameco Valuepro	MCDL-10003ED-E	Standard	Orange	Diffused	10mm, T-3 1/4	610 nm	25	60	2	30 mA	13.2	0.1"	2	\$ 0.45
2152112	Jameco Valuepro	MCDL-10003SED	Standard	Red	Diffused	10mm, T-3 1/4	635 nm	35	60	2	30 mA	13.2	0.1"	2	\$ 0.55