



[Click Here to Request a Large Quantity Quote](#)

OPTO COMPONENTS - IR LED EMITTERS

Jameco Part#	Manufacturer	Manufacturer Part #	Color	Lens Type	Package	Wavelength	Viewing Angle (deg)	Forward Voltage - Vf (Typ.)	Forward Current - If (Typ.)	Height (mm)	Mounting	Price 1
2125261	Vishay	TSHA4400	InfraRed	Water Clear	3mm, T-1	875 nm	20	1.5	100 mA	4.5	0.1"	\$ 0.17
2276407	Everlight Electronics	SIR204	InfraRed	Water Clear	3mm, T-1	875 nm	30	1.3	20 mA	5.2	0.1"	\$ 0.25
112150	Ligitek	LIR2043	Infrared	Water Clear	3mm, T-1	940 nm	30	1.2	20 mA	5.2	0.1"	\$ 0.19
2291223	Fairchild Semiconductor	QEC113	InfraRed	Water Clear	3mm, T-1	940 nm	18	1.5	100 mA	4.9	0.1"	\$ 0.35
1950825	Jameco Valuepro	L-34F3CS	InfraRed	Water Clear	3mm, T-1	940 nm	50	1.2	20 mA	5.25	0.1"	\$ 0.39
372737	Jameco Valuepro	UT1883-81-880-R	InfraRed	Water Clear	5mm, T-1 3/4	880 nm	10	1.5	20 mA	8.7	0.1"	\$ 0.39
2276663	Optek Technology	OP296B	Infrared	IR Transmissive	5mm, T-1 3/4	890 nm	20	2	150 mA	7.6	0.1"	\$ 0.59
372762	Jameco Valuepro	UT1883-81-940-R	InfraRed	Non Diffused	5mm, T-1 3/4	940 nm	10	1.3	50 mA	8.7	0.1"	\$ 0.15
2279287	Jameco Valuepro	LED-5mmIR	InfraRed	Clear Blue	5mm, T-1 3/4	940 nm	18	1.2	20 mA	8.7	0.1"	\$ 0.15
106526	Ligitek	LVIR3333	InfraRed	White Non Diffused	5mm, T-1 3/4	940 nm	20	1.2	20 mA	8.6	0.1"	\$ 0.19
1110914	Vishay	TSAL6100	InfraRed	Blue Grey	5mm, T-1 3/4	940 nm	20	1.35	100 mA	8.7	0.1"	\$ 0.49
2275839	Jameco Valuepro	LED-5mmIR	InfraRed	Clear	5mm, T-1 3/4	940 nm	30	1.4	20 mA	8.6	0.1"	\$ 0.69
2285031	Major Brands	1N6265	InfraRed	Clear	TO-46	940 nm	40	1.7	100 mA	3.94	0.1"	\$ 2.95