



[Click Here to Request a Large Quantity Quote](#)

PW24 SERIES LINEAR TAPER WIREWOUND POTENTIOMETERS 24mm 5W (20%)

Jameco SKU	Mfr Name	Manufacturer Series	Mfr P/N	Resistance (Ohms)	Power Rating (W)	Tolerance (%)	Shaft Type	Shaft Length	Bushing Thread	Termination Style	Taper	Body Diameter	Price
2291143	Jameco Valuepro	PW24	PW24-B5,L-22E/N=4.5/M8	5	5	20	Round	0.866"	M8 x 0.75	Solder, Panel Mount	Linear	24 mm	\$5.29
2291151	Jameco Valuepro	PW24	PW24-B10,L-22RE/N=4.5/M8/LAL	10	5	20	Round	0.866"	M8 x 0.75	Solder, Panel Mount	Linear	24 mm	\$5.29
2291159	Jameco Valuepro	PW24	PW-24H-20S-B50	25	5	20	Round	0.866"	M8 x 0.75	Solder, Panel Mount	Linear	24 mm	\$5.29
2272279	Jameco Valuepro	PW24	PW-24H-20S-B100	50	5	20	Round Slotted	0.787"	M8 x 0.75	Solder, Panel Mount	Linear	24 mm	\$4.95
140514	Jameco Valuepro	PW24	PW24-B100-R	100	5	20	Round Slotted	0.787"	M8 x 0.75	Solder, Panel Mount	Linear	24 mm	\$4.95
2291167	Jameco Valuepro	PW24	PW24-B100,L-22RE/N=4.5/M8/LAL	100	5	20	Round	0.866"	M8 x 0.75	Solder, Panel Mount	Linear	24 mm	\$5.29
2291175	Jameco Valuepro	PW24	PW24-B250,L-22RE/N=4.5/	250	5	20	Round	0.866"	M8 x 0.75	Solder, Panel Mount	Linear	24 mm	\$5.29
2291183	Jameco Valuepro	PW24	PW24-B500,L-22RE/N=4.5/	500	5	20	Round	0.866"	M8 x 0.75	Solder, Panel Mount	Linear	24 mm	\$5.29
2291191	Jameco Valuepro	PW24	PW24-B1K,L-22RE/N=4.5/8	1,000	5	20	Round	0.866"	M8 x 0.75	Solder, Panel Mount	Linear	24 mm	\$5.95
2291199	Jameco Valuepro	PW24	PW24-B5K,L-22RE/N=4.5/8	5,000	5	20	Round	0.866"	M8 x 0.75	Solder, Panel Mount	Linear	24 mm	\$6.95
2234855	Jameco Valuepro	VW24F	VW24F-10D6-20K-B25	25	5	20	Knurled Slotted	0.590"	3/8" - 32 NEF	Solder, Panel Mount	Linear	24 mm	\$4.95