



[Click Here to Request a Large Quantity Quote](#)

PASSIVE COMPONENTS - CERAMIC DISK CAPACITORS

Jameco Part#	Manufacturer	Manufacturer Part #	Capacitance	Voltage	Tolerance (%)	Body Length or Diameter (mm)	Price 1
15333	Jameco Valuepro	DC10/50	10 pF	50	20	5	\$ 0.25
2280727	Jameco Valuepro	PC150J050NP005A5S	15 pF	500	5	5	\$ 0.25
15405	Jameco Valuepro	DC22	22 pF	50	20	5	\$ 0.25
2280735	Jameco Valuepro	PC270J050NP005A5S	27 pF	500	5	5	\$ 0.25
332217	Jameco Valuepro	CD33/50-R	33 pF	50	20	5	\$ 0.25
1947028	Jameco Valuepro	DC33ATR	33 pF	500	5	6	\$ 0.25
15512	Jameco Valuepro	DC47-VP-R	47 pF	50	20	5	\$ 0.25
1947036	Jameco Valuepro	DC47TR	47 pF	500	5	5	\$ 0.25
15552	Jameco Valuepro	DC68	68 pF	50	5	8	\$ 0.25
15341	Jameco Valuepro	DC100	100 pF	50	20	5	\$ 0.25
1947044	Jameco Valuepro	DC100TR	100 pF	100	10	7	\$ 0.25
2280783	Jameco Valuepro	6831X5R10M	100 pF	12,000	20	8	\$ 0.79
1947087	Jameco Valuepro	DC150ATR	150 pF	100	-20/+80	4	\$ 0.25
1947052	Jameco Valuepro	DC150TR	150 pF	100	10	8	\$ 0.25
1947132	Jameco Valuepro	DC220/50/10%	220 pF	50	10	4	\$ 0.25
15413	Jameco Valuepro	DC220	220 pF	50	20	5	\$ 0.25
2281031	Jameco Valuepro	DC220/10	220 pF	50	10	5	\$ 0.25
1947301	Jameco Valuepro	DC330TR	330 pF	100	-20/+80	5	\$ 0.25
15528	Jameco Valuepro	DC470	470 pF	50	20	5	\$ 0.25
1947319	Jameco Valuepro	DC470TR	470 pF	100	-20/+80	5	\$ 0.25
2162759	Jameco Valuepro	DC820	820 pF	1,000	20	7	\$ 0.25
15190	Jameco Valuepro	DC.001	0.001 μ F	50	20	5	\$ 0.25
1947343	Jameco Valuepro	DC.001TR	0.001 μ F	100	-20/+80	4	\$ 0.25
1947415	Jameco Valuepro	DC.001B	0.001 μ F	500	10	7	\$ 0.25
332436	Jameco Valuepro	CD1000/1000-R	0.001 μ F	1,000	20	5	\$ 0.25
1947327	Jameco Valuepro	DC.0022TR	0.0022 μ F	25	20	4	\$ 0.29
1947407	Jameco Valuepro	DC.0033	0.0033 μ F	500	20	9	\$ 0.25
2159883	Jameco Valuepro	DC.0033/1000	0.0033 μ F	1,000	20	7	\$ 0.25
2280775	Jameco Valuepro	C2B332K3FF9-L	0.0033 μ F	3,000	10	15	\$ 0.79
15211	Jameco Valuepro	DC.0047	0.0047 μ F	50	20	8	\$ 0.25



[Click Here to Request a Large Quantity Quote](#)

PASSIVE COMPONENTS - CERAMIC DISK CAPACITORS

Jameco Part#	Manufacturer	Manufacturer Part #	Capacitance	Voltage	Tolerance (%)	Body Length or Diameter (mm)	Price 1
1947335	Jameco Valuepro	DC.0047TR	0.0047 μ F	100	-20/+80	5	\$ 0.25
15229	Jameco Valuepro	DC.01	0.01 μ F	50	20	6	\$ 0.25
97375	Jameco Valuepro	DC.01/1K20	0.01 μ F	1,000	20	11	\$ 0.39
332487	Jameco Valuepro	CD20000/1000-R	0.02 μ F	1,000	20	14	\$ 0.29
15245	Jameco Valuepro	DC.022	0.022 μ F	50	20	4	\$ 0.29
1947351	Jameco Valuepro	DC.047B	0.047 μ F	25	-20/+80	7	\$ 0.25
15253	Jameco Valuepro	DC.047	0.047 μ F	50	20	5	\$ 0.25
2289847	Jameco Valuepro	RSB-303Y5V473Z6I6	0.047 μ F	50	20	8	\$ 0.25
332507	Jameco Valuepro	CD50000/1000	0.05 μ F	1,000	20	19	\$ 0.29
2289855	Jameco Valuepro	DC.1/16	0.1 μ F	16	-20/+80	7	\$ 0.25
151116	Jameco Valuepro	DC.1/25	0.1 μ F	25	20	5	\$ 0.25
2146302	Jameco Valuepro	SE1H104M-L515B	0.1 μ F	50	20	6	\$ 0.25
15270	Jameco Valuepro	DC.1	0.1 μ F	50	20	7	\$ 0.25
2146311	Jameco Valuepro	SC45YV1H104Z	0.1 μ F	50	20	11	\$ 0.29
2289863	Jameco Valuepro	DC.1/50-13mm	0.1 μ F	50	20	13	\$ 0.29
332516	Jameco Valuepro	CD100000/1000-R	0.1 μ F	1,000	20	22	\$ 0.65
2130642	Jameco Valuepro	K/CAP1 (224 pcs. Kit)	Assorted	50		7	\$ 19.95
130232	Jameco Valuepro	130232 (refill cabinet kit)	Assorted	50		7	\$ 29.95