



[Click Here to Request a Large Quantity Quote](#)

PASSIVE COMPONENTS - CAPACITORS ELECTROLYTIC RADIAL

Jameco Part#	Manufacturer	Manufacturer Part #	Capacitance (uF)	Voltage (V)	Tolerance (%)	Size	Construction	Maximum Operating Temperature	Mounting	Price 1
2151970	Jameco Valuepro	R0.1/50	0.1	50	20	5mm X 11x2mm	Radial	85	Through Hole	\$ 0.25
609043	Jameco Valuepro	UVR2A0R1MDD	0.1	100	20	5x11x2mm	Radial	85	Through Hole	\$ 0.21
330465	Jameco Valuepro	RA0.47/50-R	0.47	50	20	5 x 11 x 2mm	Radial	85	Through Hole	\$ 0.21
330431	Jameco Valuepro	RA1/25-R	1	25	20	5 x 11 x 2mm	Radial	85	Through Hole	\$ 0.25
94161	Jameco Valuepro	ECE-A1HKS010	1	50	20	4 X 5mm	Radial	85	Through Hole	\$ 0.21
29831	Jameco Valuepro	R1/50	1	50	20	5 x 11 x 2mm	Radial	85	Through Hole	\$ 0.25
115423	Arndt	R1/63	1	63	20	5 x 11 x 2mm	Radial	85	Through Hole	\$ 0.25
93731	Jameco Valuepro	R2.2/50-VP-R	2.2	50	20	5 x 11 x 2mm	Radial	85	Through Hole	\$ 0.21
93729	Jameco Valuepro	R2.2/50	2.2	50	20	5 x 11 x 2mm	Radial	85	Through Hole	\$ 0.25
135184	Jameco Valuepro	R3.3/50-VP	3.3	50	20	5 x 12 x 2mm	Radial	85	Through Hole	\$ 0.25
2143460	Jameco Valuepro	R4.7/25	4.7	25	20	4x7x2.5mm	Radial	85	Through Hole	\$ 0.21
2230109	Xicon	R4.7/35	4.7	35	20	5 x 11x2mm	Radial	85	Through Hole	\$ 0.21
31000	Jameco Valuepro	R4.7/50	4.7	50	20	5 x 11 x 2mm	Radial	85	Through Hole	\$ 0.21
2279983	Nippon Chemi Con	ESMG401ELL4R7MJ16S	4.7	400	20	10 x 16x5mm	Radial	85	Through Hole	\$ 0.39
198839	Jameco Valuepro	EC1016H511-R	10	16	20	5 x 11 x 2mm	Radial	85	Through Hole	\$ 0.25
94212	Jameco Valuepro	10UF/25V 4X5-R	10	25	20	4 X 5mm	Radial	85	Through Hole	\$ 0.25
1946367	Jameco Valuepro	R10/25A	10	25	20	5 x 11 x 5mm	Radial	85	Through Hole	\$ 0.25
94221	Jameco Valuepro	E00035SR0505	10	35	20	5 x 5 x 2mm	Radial	85	Through Hole	\$ 0.25
29893	Jameco Valuepro	R10/50-VP-R	10	50	20	5 x 11 x 2mm	Radial	85	Through Hole	\$ 0.21
29891	Jameco Valuepro	R10/50	10	50	20	5 x 11 x 2mm	Radial	85	Through Hole	\$ 0.25
1946295	Jameco Valuepro	R22/16	22	16	20	5x12x2mm	Radial	85	Through Hole	\$ 0.21
93739	Jameco Valuepro	R22/50-VP-R	22	50	20	5 x 11 x 2mm	Radial	85	Through Hole	\$ 0.25
2279967	Panasonic	ECA-2EM220	22	250	20	10 x 20x5mm	Radial	85	Through Hole	\$ 0.49
93747	Jameco Valuepro	R33/50-VP-R	33	50	20	6.3 x 11 x 2.5mm	Radial	85	Through Hole	\$ 0.21
1946244	Jameco Valuepro	R47/16TR	47	16	20	5 x 12 x 5mm	Radial	85	Through Hole	\$ 0.21
198952	Jameco Valuepro	EC4735H511-R	47	35	20	5 x 11 x 2mm	Radial	85	Through Hole	\$ 0.21
31114	Jameco Valuepro	R47/50	47	50	20	6 x 11 x 2.5mm	Radial	85	Through Hole	\$ 0.21
330676	Jameco Valuepro	RA47/450-R	47	450	20	18 X 30mm	Radial	85	Through Hole	\$ 1.59
1946261	Jameco Valuepro	R68/16TR	68	16	20	5 x 11 x 5mm	Radial	85	Through Hole	\$ 0.21
2230539	Jameco Valuepro	R100/10	100	10	20	6 x 11x2mm	Radial	85	Through Hole	\$ 0.21
94289	Jameco Valuepro	100UF/16V 6X5	100	16	20	6x5x2.5mm	Radial	85	Through Hole	\$ 0.21
330422	Jameco Valuepro	RA100/16-R	100	16	20	5 x 11 x 2mm	Radial	85	Through Hole	\$ 0.25
93761	Jameco Valuepro	R100/25	100	25	20	6 x 11 x 5mm	Radial	85	Through Hole	\$ 0.25
198970	Jameco Valuepro	EC10035H611-R	100	35	20	6.3 x 11 x 2.5mm	Radial	85	Through Hole	\$ 0.23
29962	Jameco Valuepro	R100/50	100	50	20	8 x 11 x 3.5mm	Radial	85	Through Hole	\$ 0.25
330529	Jameco Valuepro	RA100/100-R	100	100.0	20	10 X 17mm	Radial	85	Through Hole	\$ 0.49
330580	Jameco Valuepro	RA100/160S-R	100	160.0	20	16 x 25 x 7.5mm	Radial	85	Through Hole	\$ 0.79
330684	Jameco Valuepro	RA100/450-R	100	450.0	20	22x 47x10mm	Radial	85	Through Hole	\$ 2.75
198872	Jameco Valuepro	EC22016H611-R	220	16.0	20	6.3 x 11 x 2.5mm	Radial	85	Through Hole	\$ 0.22
30496	Jameco Valuepro	R220/25	220	25.0	20	8 x 11 x 3.5mm	Radial	85	Through Hole	\$ 0.25
93772	Jameco Valuepro	R220/35-R	220	35.0	20	8 X 12mm	Radial	85	Through Hole	\$ 0.29
93778	Jameco Valuepro	R220/50	220	50.0	20	10 x 17 x 5mm	Radial	85	Through Hole	\$ 0.39
93796	Jameco Valuepro	R330/25	330	25.0	20	10 x 12 x 5mm	Radial	85	Through Hole	\$ 0.29
198978	Jameco Valuepro	EC33035H1017-R	330	35.0	20	8 x 12 x 3.5mm	Radial	85	Through Hole	\$ 0.35
330473	Jameco Valuepro	RA330/50-R	330	50.0	20	10 x 16 x 5mm	Radial	85	Through Hole	\$ 0.39
93809	Jameco Valuepro	R470/16	470	16.0	20	8 x 11 x 3.5mm	Radial	85	Through Hole	\$ 0.25
31181	Jameco Valuepro	R470/25	470	25.0	20	10 x 12 x 5mm	Radial	85	Through Hole	\$ 0.29
93817	Jameco Valuepro	R470/35	470	35.0	20	10 x 16 x 5mm	Radial	85	Through Hole	\$ 0.39
93827	Jameco Valuepro	R470/50-VP-R	470	50.0	20	10 X 20mm	Radial	85	Through Hole	\$ 0.59



[Click Here to Request a Large Quantity Quote](#)

PASSIVE COMPONENTS - CAPACITORS ELECTROLYTIC RADIAL

Jameco Part#	Manufacturer	Manufacturer Part #	Capacitance (uF)	Voltage (V)	Tolerance (%)	Size	Construction	Maximum Operating Temperature	Mounting	Price 1
158465	Jameco Valuepro	R470B63	470	63.0	20	13 x 20 x 5mm	Radial	85	Through Hole	\$ 0.65
330456	Jameco Valuepro	RA680/25S	680	25.0	20	8x16x3.5mm	Radial	85	Through Hole	\$ 0.49
2229554	Nichicon	R680UF-25V	680	25.0	20	16 x 25x7mm	Radial	85	Through Hole	\$ 0.49
30015	Jameco Valuepro	R1000/16	1000	16.0	20	10 x 16 x 5mm	Radial	85	Through Hole	\$ 0.39
2234302	Arndt	RB1000/16-12	1000	16.0	20	12 x 14x5mm	Radial	85	Through Hole	\$ 0.45
93833	Jameco Valuepro	R1000/25	1000	25.0	20	10 x 20 x 5mm	Radial	85	Through Hole	\$ 0.45
93841	Jameco Valuepro	R1000/50	1000	50.0	20	13mm X 26mm	Radial	85	Through Hole	\$ 0.75
199111	Jameco Valuepro	EC1000100H1840-R	1000	100.0	20	18 x 41 x 7.5mm	Radial	85	Through Hole	\$ 1.75
133148	Nichicon	R2200/16-R	2200	16.0	20	18 x 16x8mm	Radial	85	Through Hole	\$ 0.49
30535	Jameco Valuepro	R2200/25-VP-R	2200	25.0	20	13 x 21 x 5mm	Radial	85	Through Hole	\$ 0.65
30533	Jameco Valuepro	R2200/25	2200	25.0	20	12 x 25 x 5mm	Radial	85	Through Hole	\$ 0.79
2229546	Arndt	R2200UF-25V	2200	25.0	20	22 x 40x12mm	Radial	85	Through Hole	\$ 0.79
198986	Jameco Valuepro	EC220035H1626-R	2200	35.0	20	16 x 25 x 7.5mm	Radial	85	Through Hole	\$ 0.89
2286359	Jameco Valuepro	UFW1H222MHD	2200	50.0	20	16x36x8mm	Radial	85	Through Hole	\$ 1.59
2234978	Vishay	67D102	2900	40.0	20	26 x 74x11mm	Radial	85	Through Hole	\$ 1.95
198898	Jameco Valuepro	EC330016H1321-R	3300	16.0	20	13 x 21 x 5mm	Radial	85	Through Hole	\$ 0.99
30893	Jameco Valuepro	R3300/25-VP-R	3300	25.0	20	13 x 29 x 5mm	Radial	85	Through Hole	\$ 0.89
2033551	Nichicon	UVR1V332MHD	3300	35.0	20	16 x 36x7mm	Radial	85	Through Hole	\$ 1.25
198901	Jameco Valuepro	EC470016H1626-R	4700	16.0	20	16 x 25 x 7.5mm	Radial	85	Through Hole	\$ 0.99
93850	Jameco Valuepro	R4700/25	4700	25.0	20	18 x 26 x 7mm	Radial	85	Through Hole	\$ 1.25
199006	Jameco Valuepro	EC470035H1836-R	4700	35.0	20	18 x34x8mm	Radial	85	Through Hole	\$ 1.59
198935	Jameco Valuepro	EC680025H1836-R	6800	25.0	20	18 x 36x8mm	Radial	85	Through Hole	\$ 1.75
609545	Jameco Valuepro	UVZ1HOR1MDD	0.1	50.0	20	5x11x2mm	Radial	105	Through Hole	\$ 0.25
330772	Jameco Valuepro	RB1/50-R	1	50.0	20	5 x 11 x 2mm	Radial	105	Through Hole	\$ 0.25
158491	Jameco Valuepro	R1B100-R	1	100.0	20	5 x 11 x 2mm	Radial	105	Through Hole	\$ 0.25
609561	Jameco Valuepro	UVZ1H2R2MDD	2.2	50.0	20	5x11x2mm	Radial	105	Through Hole	\$ 0.21
330781	Jameco Valuepro	RB4.7/50-R	4.7	50.0	20	6 x11x2mm	Radial	105	Through Hole	\$ 0.21
2290623	Jameco Valuepro	RB4.7/50-4X8	4.7	50.0	20	4x8x1.5mm	Radial	105	Through Hole	\$ 0.25
330692	Jameco Valuepro	RB10/16-R	10	16.0	20	5 x 11 x 2mm	Radial	105	Through Hole	\$ 0.21
330799	Jameco Valuepro	RB10/50-R	10	50.0	20	5 x 11 x 2mm	Radial	105	Through Hole	\$ 0.25
609641	Jameco Valuepro	UVZ1J100MDD	10	63.0	20	5x11x2mm	Radial	105	Through Hole	\$ 0.19
610036	Jameco Valuepro	UVZ2W100MHD	10	450.0	20	13x21x6mm	Radial	105	Through Hole	\$ 0.59
2286335	Panasonic	EEVFCOJ22OR	22	6.3	20	4x6.3mm	SMD	105	SMD	\$ 0.19
158327	Jameco Valuepro	LHK220M35V511	22	35.0	20	5 x 11 x 2mm	Radial	105	Through Hole	\$ 0.19
2286135	Panasonic	EEVFK1K220P	22	80.0	20	8x10mm	SMD	105	SMD	\$ 0.25
2230281	Arndt	RB22/350	22	350.0	20	13x25x6mm	Radial	105	Through Hole	\$ 0.69
609721	Jameco Valuepro	UVZ1V331MPD	33	35.0	20	10x16x5mm	Radial	105	Through Hole	\$ 0.39
2279975	Nichicon	UHE1V102MHT6	35	35.0	20	18x16x8mm	Radial	105	Through Hole	\$ 0.59
2290799	Nichicon	PCF1A470MCL1GS	47	10.0	20	6.3x6mm	SMD	105	SMD	\$ 0.99
609502	Jameco Valuepro	UVZ1C470MDD	47	16.0	20	5x11x2mm	Radial	105	Through Hole	\$ 0.25
330820	Jameco Valuepro	RB47/50-R	47	50.0	20	6.3 x 11 x 2.5mm	Radial	105	Through Hole	\$ 0.25
2280543	Nichicon	UFWA470MPD	47	100.0	20	10x12.5x2mm	Radial	105	Through Hole	\$ 0.35
610010	Jameco Valuepro	UVZ2E470MHD	47	250.0	20	13x25x6mm	Radial	105	Through Hole	\$ 0.89
2286127	NIC Components	NACZ102M6.3V8X10.5TR13	100	6.3	20	8x10.5mm	SMD	105	SMD	\$ 0.29
1946228	Jameco Valuepro	RB100/10	100	10.0	20	5x11x3.5mm	Radial	105	Through Hole	\$ 0.23
330740	Jameco Valuepro	RB100/25-R	100	25.0	20	6.3 x 11 x 2.5mm	Radial	105	Through Hole	\$ 0.25
158394	Jameco Valuepro	R100B50-R	100	50.0	20	13 x 21 x 5mm	Radial	105	Through Hole	\$ 0.29
608032	Jameco Valuepro	UPL1J101MHH6	100	63.0	20	12.5 X 15mm	Radial	105	Through Hole	\$ 0.25
2279959	Nippon Chemi Con	EKXG201ELL101ML20S	100	200.0	20	16x21x8mm	Radial	105	Through Hole	\$ 1.09
2279951	Panasonic	EEUED2D101	100	200.0	20	16x26x8mm	Radial	105	Through Hole	\$ 1.19



[Click Here to Request a Large Quantity Quote](#)

PASSIVE COMPONENTS - CAPACITORS ELECTROLYTIC RADIAL

Jameco Part#	Manufacturer	Manufacturer Part #	Capacitance (uF)	Voltage (V)	Tolerance (%)	Size	Construction	Maximum Operating Temperature	Mounting	Price 1
609967	Jameco Valuepro	UVZ2E101MHD	100	250.0	20	16x32x8mm	Radial	105	Through Hole	\$ 1.49
2286383	NIC Components	NSP121M63D3TRF	120	6.3	20	7.3x4.3x2.8	SMD	105	SMD	\$ 0.99
2158426	Jameco Valuepro	RC120/400	120	400.0	20	16X35mm	Radial	105	Through Hole	\$ 1.09
608340	Jameco Valuepro	ECA1JFQ151L	150	63.0	20	10 X 20mm	Radial	105	Through Hole	\$ 0.25
606934	Jameco Valuepro	UHE1J181MPD	180	63.0	20	10x21x5mm	Radial	105	Through Hole	\$ 0.25
158263	Jameco Valuepro	R220B25-R	220	25.0	20	8 X 11mm	Radial	105	Through Hole	\$ 0.29
93770	Jameco Valuepro	R220/35	220	35.0	20	10 x 12 x 5mm	Radial	105	Through Hole	\$ 0.35
606820	Jameco Valuepro	UHE1H221MPD	220	50.0	20	10x16x5mm	Radial	105	Through Hole	\$ 0.21
2279943	Nichicon	UVZ2D221MDH	220	200.0	20	18x36x7mm	Radial	105	Through Hole	\$ 1.75
2285951	NIC Components	NACZ331M35V10X10.5TR13	330	35.0	20	10x10.5mm	SMD	105	SMD	\$ 0.39
158203	Jameco Valuepro	R470B16	470	16.0	20	8 x 11 x 3.5mm	Radial	105	Through Hole	\$ 0.35
2280023	Nippon Chemi Con	ELXV250ETD471MJ20	470	25.0	20	10x20x5mm	Radial	105	Through Hole	\$ 0.35
158289	Jameco Valuepro	R470B25	470	25.0	20	10 x 16 x 5mm	Radial	105	Through Hole	\$ 0.39
606854	Jameco Valuepro	UHE1H471MPD	470	50.0	20	13x25x5mm	Radial	105	Through Hole	\$ 0.59
2287791	Nichicon	UPM1J471MHH67N	470	63.0	20	10x26x7mm	Radial	105	Through Hole	\$ 0.25
2133430	Panasonic	EEU-FM1C681L	680	16.0	20	8x21x2.5mm	Radial	105	Through Hole	\$ 0.29
2129781	Jameco Valuepro	E681035SR1321	680	35.0	20	13x21x4mm	Radial	105	Through Hole	\$ 0.59
607355	Jameco Valuepro	UPW0J821MPD	820	6.3	20	8x11x4mm	Radial	105	Through Hole	\$ 0.39
606432	Jameco Valuepro	UHE0J102MPD	1000	6.3	20	8x14x3.5mm	Radial	105	Through Hole	\$ 0.35
607363	Jameco Valuepro	UPW1A102MPD6	1000	10.0	20	8x14x4mm	Radial	105	Through Hole	\$ 0.39
330722	Jameco Valuepro	RB1000/16-R	1000	16.0	20	10 x 20 x 5mm	Radial	105	Through Hole	\$ 0.49
158298	Jameco Valuepro	R1000B25-R	1000	25.0	20	10 x 17 x 5mm	Radial	105	Through Hole	\$ 0.49
1984494	Panasonic	EEU-EB1V102	1000	35.0	20	12.5mm X 25mm	Radial	105	Through Hole	\$ 0.59
158378	Jameco Valuepro	R1000B35-R	1000	35.0	20	13 x 21 x 5mm	Radial	105	Through Hole	\$ 0.59
609553	Jameco Valuepro	UVZ1H102MHD	1000	50.0	20	13x25x5mm	Radial	105	Through Hole	\$ 0.89
606627	Jameco Valuepro	UHE1C122MPD	1200	16.0	20	10x24x5mm	Radial	105	Through Hole	\$ 0.69
2287655	Jameco Valuepro	ECA1CFG152S	1500	16.0	20	16x16x8mm	Radial	105	Through Hole	\$ 0.79
2285543	Panasonic	EEV-FK1C152Q	1500	16.0	20	12.5x14mm	SMD	105	SMD	\$ 0.99
607742	Jameco Valuepro	UPW1E152MHD6	1500	25.0	20	13x25x5mm	Radial	105	Through Hole	\$ 0.95
606467	Jameco Valuepro	UHE0J182MHD	1800	6.3	20	10x20x5mm	Radial	105	Through Hole	\$ 0.59
609342	Jameco Valuepro	UVZ0J222MPD	2200	6.3	20	10x20x5mm	Radial	105	Through Hole	\$ 0.49
606563	Jameco Valuepro	UHE1A222MPD	2200	10.0	20	13x21x6mm	Radial	105	Through Hole	\$ 0.69
2229562	Arndt	CEVSM1E222(V)-J2	2200	25.0	20	16x38x7mm	Radial	105	Through Hole	\$ 0.79
2290615	Nichicon	UVZ1V222MHD1AA	2200	35.0	20	5x26x8mm(4.5mm Ld)	Radial	105	Through Hole	\$ 1.09
609705	Jameco Valuepro	UVZ1V222MHD	2200	35.0	20	16x26x8mm	Radial	105	Through Hole	\$ 1.25
158431	Illinois Capacitor	R2200B35	2200	35.0	20	18x36x8mm	Radial	105	Through Hole	\$ 1.25
158432	Jameco Valuepro	R2200B50-R	2200	50.0	20	16 x 32 x8mm	Radial	105	Through Hole	\$ 1.39
608278	Jameco Valuepro	E332035HR	3300	35.0	20	18x31x8mm	Radial	105	Through Hole	\$ 1.29
609588	Jameco Valuepro	UVZ1H332MHD	3300	50.0	20	18x36x8mm	Radial	105	Through Hole	\$ 1.95
607814	Jameco Valuepro	UPW1E472MHD	4700	25.0	20	18x35x8mm	Radial	105	Through Hole	\$ 1.95
163301	Jameco Valuepro	R4700/50	4700	50.0	20	22x36 x10mm	Radial	105	Through Hole	\$ 2.49
2203098	Arndt	R5600B6.3	5600	6.3	20	13x40x5mm	Radial	105	Through Hole	\$ 0.95
2125641	Nichicon	R5600B16	5600	16.0	20	16x40x7.5mm	Radial	105	Through Hole	\$ 1.49
609473	Jameco Valuepro	UVZ1C103MHD	10000	16.0	20	18x40.5x8mm	Radial	105	Through Hole	\$ 1.75