



[Click Here to Request a Large Quantity Quote](#)

TEST EQUIPMENT - OSCILLOSCOPES

Jameco Part#	Manufacturer	Manufacturer Part #	Description	Bandwidth	Sampling Rate	Number of Channels	Price 1
2283975	Digilent	410-321	Analog Discovery 2: 100MS/s USB Oscilloscope, Logic Analyzer and Variable Power Supply	30MHz	100MS/s	2	\$ 279.00
2283991	Digilent	410-324	OpenScope MZ: Open-source All-in-one Instrumentation	2MHz	6.25MS/s	-	\$ 89.00
2217393	Seeed Studios	109990013	DSO Nano v3 Pocket-Size 32bit Digital Storage Oscilloscope	200kHz	1MS/s	1	\$ 99.95
2205931	Gabotronics	GT-0015	Xminilab Portable Oscilloscope OLED	50kHz	1MS/s	2	\$ 117.95
2283191	Siglent Technologies	SDS1202X-E	SDS1202X-E Dual Channel Digital Oscilloscope 200MHz 1GS/sec	200MHz	1GS/s	2	\$ 379.00
2187454	Velleman	PCSU200	USB PC Oscilloscope and Signal Generator	12MHz	4KS/s	2	\$ 139.95
2289991	Digilent	ANALOG-DIS2-BUNDLE	Analog Discovery 2 Pro Bundle (240-123)	30MHz	100MS/s	2	\$ 299.99
2255461	Velleman	HPS140MK2	Handheld 40MS/s Digital Storage Oscilloscope with Hold Function	10MHz	40MS/s	1	\$ 142.49
2238215	BK Precision	2190E	100 MHz Digital Storage Oscilloscope	100MHz	1GS/s	2	\$ 459.95
2226732	Instek	GDS-2202E	200MHz 2-Channel Digital Storage Oscilloscope	200MHz	1GS/s	2	\$ 1,310.99
2170863	Instek	GDS-2102A	100MHz 2-Channel Visual Persistence Digital Storage Oscilloscope	100MHz	2GS/s	2	\$ 1,149.49
2284567	Siglent Technologies	SDS1204X-E	SDS1204X-E Super Phosphor Oscilloscope 200 MHz Four Channel Dual 1GS/s ADC 7" TFT	200MHz	1GS/s	4	\$ 759.00
2226724	Instek	GDS-2104E	100MHz 4-Channel Digital Storage Oscilloscope	100MHz	1GS/s	4	\$ 1,619.95
2170847	Instek	GDS-2072A	70MHz 2-Channel Visual Persistence Digital Storage Oscilloscope	70MHz	2GS/s	2	\$ 845.49
2282679	Fluke Corporation	FLUKE-123B/NA	Fluke 123B Industrial ScopeMeter® Hand-Held Oscilloscope (20 MHz)	20MHz	400ks/s	2	\$ 1,560.44
2170871	Instek	GDS-2104A	100MHz 4-Channel Visual Persistence Digital Storage Oscilloscope	100MHz	2GS/s	4	\$ 1,709.99
2170898	Instek	GDS-2204A	200 MHz 4-Channel Visual Persistence Digital Storage Oscilloscope	200MHz	2GS/s	4	\$ 1,994.99
2173546	Fluke Corporation	FLUKE-190-104/AM	Handheld Digital Oscilloscope with Probe 4 Channel 100MHz 1.25GS/s	100MHz	1.25GS/s	4	\$ 4,369.25
2173554	Fluke Corporation	FLUKE-190-104/AM/S	Handheld Digital Oscilloscope with Probe and SCC-290 Kit 4 Channel 100MHz 1.25GS/s	100MHz	1.25GS/s	4	\$ 4,785.37
2170855	Instek	GDS-2074A	70MHz 4-Channel Visual Persistence Digital Storage Oscilloscope	70MHz	2GS/s	4	\$ 1,443.99
2173562	Fluke Corporation	FLUKE-190-202/AM	Handheld Digital Oscilloscope with Probe 2 Channel 200MHz 2.5GS/s	200MHz	2.5GS/s	2	\$ 4,265.22
2170901	Instek	GDS-2302A	300MHz 2-Channel Visual Persistence Digital Storage Oscilloscope	300MHz	2GS/s	2	\$ 2,422.49
2173589	Fluke Corporation	FLUKE-190-204/AM	Handheld Digital Oscilloscope with Probe 4 Channel 200MHz 1.25GS/s	200MHz	1.25GS/s	4	\$ 4,993.43
2173597	Fluke Corporation	FLUKE-190-204/AM/S	Handheld Digital Oscilloscope with Probe and SCC-290 Kit 4 Channel 200MHz 1.25GS/s	200MHz	1.25GS/s	4	\$ 5,409.55
2173520	Fluke Corporation	FLUKE-190-102/AM	Handheld Digital Oscilloscope with Probe 2 Channel 100MHz 1.25GS/s	100MHz	1.25GS/s	2	\$ 3,849.10
2226791	Instek	GDS-1104B	100MHz 4-Channel Digital Storage Oscilloscope	100MHz	1GS/s	4	\$ 831.19
2226741	Instek	GDS-2204E	200MHz 4-Channel Digital Storage Oscilloscope	200MHz	1GS/s	4	\$ 1,576.99
2173571	Fluke Corporation	FLUKE-190-202/AM/S	Handheld Digital Oscilloscope with Probe and SCC-290 Kit 2 Channel 200MHz 2.5GS/s	200MHz	2.5GS/s	2	\$ 4,681.34
2170880	Instek	GDS-2202A	200MHz 2-Channel Visual Persistence Digital Storage Oscilloscope	200MHz	2GS/s	2	\$ 1,662.49
2247437	Instek	GDS-207	70MHz 2-Channel Full Touch Panel Digital Storage Oscilloscope	70MHz	1GS/s	2	\$ 794.95
2173503	Fluke Corporation	FLUKE-190-062/AM	Handheld Digital Oscilloscope 2 Channel 60MHz 625MS/s	60MHz	625MS/s	2	\$ 3,432.98
2170919	Instek	GDS-2304A	300MHz 4-Channel Visual Persistence Digital Storage Oscilloscope	300MHz	2GS/s	4	\$ 2,944.99
2247445	Instek	GDS-210	100MHz 2-Channel Full Touch Panel Digital Storage Oscilloscope	100MHz	1GS/s	2	\$ 994.95
2173511	Fluke Corporation	FLUKE-190-062/AM/S	Handheld Digital Oscilloscope with SCC-290 Kit 2 Channel 60MHz 625MS/s	60MHz	625MS/s	2	\$ 3,849.10
2247453	Instek	GDS-220	OSCILLOSCOPE,200MHz,2 CHANNEL,7" 800x480 LCD TOUCHSCREEN	200MHz	1GS/s	2	\$ 1,294.95
2226708	Instek	GDS-2074E	70MHz 4-Channel Digital Storage Oscilloscope	70MHz	1GS/s	4	\$ 1,158.99
2226716	Instek	GDS-2102E	100MHz 2-Channel Digital Storage Oscilloscope	100MHz	1GS/s	2	\$ 921.19
2173538	Fluke Corporation	FLUKE-190-102/AM/S	Handheld Digital Oscilloscope with Probe and SCC-290 Kit 2 Channel 100MHz 1.25GS/s	100MHz	1.25GS/s	2	\$ 4,265.22
2226716	Instek	GDS-2102E	100MHz 2-Channel Digital Storage Oscilloscope	100MHz	1GS/s	2	\$ 921.19
2173538	Fluke Corporation	FLUKE-190-102/AM/S	Handheld Digital Oscilloscope with Probe and SCC-290 Kit 2 Channel 100MHz 1.25GS/s	100MHz	1.25GS/s	2	\$ 4,265.22