



[Click Here to Request a Large Quantity Quote](#)

TRIMMER POTENTIOMETERS 3059 SERIES: 1/2 & 1 WATT ◦ 1-1/4" RECTANGULAR ◦ ±10% (-66°C to 125°C)

Jameco SKU	Mfr Name	Mfg. Series	Mfr P/N	Resistance (Ohms)	Power Rating	Tolerance (%)	Type	Number of Turns	Actuator Orientation	Termination Style	Price 1
2201050	BI Technologies	3059L	55LR50 (RJ11CL500) 3059L-1-500	50	1 W	10	1-1/4" Rectangular	22	Side	Wires	\$1.75
2201017	BI Technologies	3059L	55LR100 (RJ11CL101) 3059L-1-101	100	1 W	10	1-1/4" Rectangular	22	Side	Wires	\$1.75
2201041	BI Technologies	3059L	55LR200 (RJ11CL201) 3059L-1-201	200	1 W	10	1-1/4" Rectangular	22	Side	Wires	\$1.75
2201324	BI Technologies	3059L	55LBWR200 (RJ11CL201) 3059L-1-201	200	1 W	10	1-1/4" Rectangular	22	Side	Wires, Panel Mount	\$1.75
2200866	BI Technologies	3059L	78LR500 (3359L-1-501)	500	1 W	10	1-1/4" Rectangular	22	Side	Wires	\$1.75
2200840	BI Technologies	3059L	78LBWR200 (3059L-1-201)	2,000	1 W	10	1-1/4" Rectangular	22	Side	Wires	\$1.75
2198268	BI Technologies	3059L	78LR5K/370L5K (3059L-1-502)	5,000	1 W	10	1-1/4" Rectangular	22	Side	Wires	\$1.75
2198292	Bourns	3059L	78LR5K (3059L-1-502)	5,000	1 W	10	1-1/4" Rectangular	22	Side	Wires, Panel Mount	\$1.75
2162927	Clarostat/Honeywell	3059L	370L503 (3059L-1-503)	50,000	0.5 W	10	1-1/4" Rectangular	20	Side	Wires	\$1.49
2198276	BI Technologies	3059L	78LR50K (3059L-1-503)	50,000	1 W	10	1-1/4" Rectangular	22	Side	Wires	\$1.75
2201068	BI Technologies	3059L	55LR50K (RJ11CL503) 3059L-1-503	50,000	1 W	10	1-1/4" Rectangular	22	Side	Wires	\$1.75
2200410	BI Technologies	3059L	56LR250K (3059L-1-254)	250,000	1 W	10	1-1/4" Rectangular	22	Side	Wires	\$1.75
2162935	Spectrol/Vishay Corporation	3059L	370L500K (3059L-1-504)	500,000	0.5 W	10	1-1/4" Rectangular	20	Side	Wires	\$1.49
2200436	BI Technologies	3059L	56LR500K (3059L-1-504)	500,000	1 W	10	1-1/4" Rectangular	22	Side	Wires	\$1.75
2201033	BI Technologies	3059L	55LR2MEG (RJ11CP205) 3059L-1-205	2,000,000	1 W	10	1-1/4" Rectangular	22	Side	Wires	\$1.75
2201113	BI Technologies	3059P	55PR10 (RJ11CP100) 3059L-1-100	10	1 W	10	1-1/4" Rectangular	22	Side	Pin	\$1.75
2201164	BI Technologies	3059P	55PR50 (RJ11CP500) 3059L-1-500	50	1 W	10	1-1/4" Rectangular	22	Side	Pin	\$1.75
2194890	BI Technologies	3059P	56PR100 (3059P-1-101)	100	1 W	10	1-1/4" Rectangular	22	Side	Pin	\$1.75
2201121	BI Technologies	3059P	55PR100 (RJ11CP101) 3059P-1-101	100	1 W	10	1-1/4" Rectangular	22	Side	Pin	\$1.75
2201172	BI Technologies	3059P	55PR500(RJ11CP501) 3059P-1-501	500	1 W	10	1-1/4" Rectangular	22	Side	Pin	\$1.75
2194865	BI Technologies	3059P	56PR1K/70P102 (3059P-1-)	1,000	1 W	10	1-1/4" Rectangular	22	Side	Pin	\$1.75
2201092	BI Technologies	3059P	55PR1.5K (RJ11CP152) 3059P-1-152	1,500	1 W	10	1-1/4" Rectangular	22	Side	Pin	\$1.75
2201201	BI Technologies	3059P	55PR2K (RJ11CP202) 3059P-1-202	2,000	1 W	10	1-1/4" Rectangular	22	Side	Pin	\$1.75
2287495	Bourns	3059P	3059P-1-202LF	2,000	1 W	10	1-1/4" Rectangular	22	Side	Pin	\$3.95
2201148	BI Technologies	3059P	55PR2.5K (RJ11CP252) 3059P-1-252	2,500	1 W	10	1-1/4" Rectangular	22	Side	Pin	\$1.75
2178355	Spectrol/Vishay Corporation	3059P	70P203 (3059P-1-203)	20,000	0.5 W	10	1-1/4" Rectangular	20	Side	Pin	\$1.49
2178363	Spectrol/Vishay Corporation	3059P	70P503 (3059P-1-503)	50,000	0.5 W	10	1-1/4" Rectangular	20	Side	Pin	\$1.49
2201228	BI Technologies	3059P	55PR50K/RJ11CP503 (3059P-1-503)	50,000	1 W	10	1-1/4" Rectangular	22	Side	Pin	\$1.75
2201130	BI Technologies	3059P	55PR100K (RJ11CP104) 3059P-1-104	100,000	1 W	10	1-1/4" Rectangular	22	Side	Pin	\$1.75
2201156	BI Technologies	3059P	55PR200K (RJ11CP204) 3059P-1-204	200,000	1 W	10	1-1/4" Rectangular	22	Side	Pin	\$1.75
2200508	BI Technologies	3059P	58PR250K(3059P-1-254)	250,000	1 W	10	1-1/4" Rectangular	22	Side	Pin	\$1.75
2194873	BI Technologies	3059P	56PR500K (3059P-1-504)	500,000	1 W	10	1-1/4" Rectangular	22	Side	Pin	\$1.75
2200541	BI Technologies	3059S	58SR20 (3059S-1-200)	20	1 W	10	1-1/4" Rectangular	22	Side	J-Hook	\$1.75
2200567	BI Technologies	3059S	58SR200 (3059S-1-201)	200	1 W	10	1-1/4" Rectangular	22	Side	J-Hook	\$1.75
2198102	BI Technologies	3059S	78SR500 (3059S-1-501)	500	1 W	10	1-1/4" Rectangular	22	Side	J-Hook	\$1.75
2200559	BI Technologies	3059S	58SR20K (3059S-1-203)	2,000	1 W	10	1-1/4" Rectangular	22	Side	J-Hook	\$1.75
2201181	BI Technologies	3059S	55SR50K (RJ11CS503) 3059S-1-503	50,000	1 W	10	1-1/4" Rectangular	22	Side	J-Hook	\$1.75
2162943	Spectrol/Vishay Corporation	3059Y	70Y100 (3059Y-1-100)	10	0.5 W	10	1-1/4" Rectangular	20	Side	Pin	\$1.49
2198153	BI Technologies	3059Y	78PR20 (3359Y-1-200)	20	1 W	10	1-1/4" Rectangular	22	Side	Pin	\$1.75
2198188	BI Technologies	3059Y	78PR50 (3059Y-1-500)	50	1 W	10	1-1/4" Rectangular	22	Side	Pin	\$1.75
2162951	Spectrol/Vishay Corporation	3059Y	70Y101 (3059Y-1-101)	100	0.5 W	10	1-1/4" Rectangular	20	Side	Pin	\$1.49
2198137	BI Technologies	3059Y	78PR100 (3059Y-1-101)	100	1 W	10	1-1/4" Rectangular	22	Side	Pin	\$1.75
2198305	BI Technologies	3059Y	78PBWR100 (3059Y-1-101)	100	1 W	10	1-1/4" Rectangular	22	Side	Pins, Panel Mount	\$1.75
2198161	BI Technologies	3059Y	78PR200/70Y201(3359Y-1-201)	200	1 W	10	1-1/4" Rectangular	22	Side	Pins, Panel Mount	\$1.75
2163031	Spectrol/Vishay Corporation	3059Y	70Y501 (3059Y-1-501)	500	0.5 W	10	1-1/4" Rectangular	20	Side	Pin	\$1.49
2200461	BI Technologies	3059Y	58PR1K (3059Y-1-102)	1,000	1 W	10	1-1/4" Rectangular	22	Side	Pin	\$1.75
2162994	Spectrol/Vishay Corporation	3059Y	70Y202/3059Y-1-202	2,000	0.5 W	10	1-1/4" Rectangular	20	Side	Pin	\$1.49
2198145	BI Technologies	3059Y	78PR2K (3059Y-1-202)	2,000	1 W	10	1-1/4" Rectangular	22	Side	Pins, Panel Mount	\$1.75
2163022	Spectrol/Vishay Corporation	3059Y	70Y252 (3059Y-1-252)	2,500	0.5 W	10	1-1/4" Rectangular	20	Side	Pin	\$1.49
2178321	Spectrol/Vishay Corporation	3059Y	70Y502/3059Y-1-502	5,000	0.5 W	10	1-1/4" Rectangular	20	Side	Pin	\$1.49
2200516	BI Technologies	3059Y	58PR5K (3059Y-1-502)	5,000	1 W	10	1-1/4" Rectangular	22	Side	Pin	\$1.75
2198225	BI Technologies	3059Y	78PR10K-422E (3059Y-1-103)	10,000	1 W	10	1-1/4" Rectangular	22	Side	Pins, Thumb Adj.	\$1.75

[Click Here to Request a Large Quantity Quote](#)



TRIMMER POTENTIOMETERS 3059 SERIES: 1/2 & 1 WATT ◦ 1-1/4" RECTANGULAR ◦ ±10% (-66°C to 125°C)

Jameco SKU	Mfr Name	Mfg. Series	Mfr P/N	Resistance (Ohms)	Power Rating	Tolerance (%)	Type	Number of Turns	Actuator Orientation	Termination Style	Price 1
2200495	BI Technologies	3059Y	58PR20K (3059Y-1-203)	20,000	1 W	10	1-1/4" Rectangular	22	Side	Pin	\$1.75
2180375	Spectrol/Vishay Corporation	3059Y	70Y503/3059Y-1-503	50,000	0.5 W	10	1-1/4" Rectangular	20	Side	Pin	\$1.49
2200479	BI Technologies	3059Y	58PR100K (3059Y-1-104)	100,000	1 W	10	1-1/4" Rectangular	22	Side	Pin	\$1.75
2178339	Spectrol/Vishay Corporation	3059Y	70Y504/78PR500K (3059Y-1-	500,000	0.5 W	10	1-1/4" Rectangular	20	Side	Pin	\$1.49
2162978	Spectrol/Vishay Corporation	3059Y	70Y105/78PR1MEG (3059Y-1)	1,000,000	0.5 W	10	1-1/4" Rectangular	20	Side	Pin	\$1.49
2198170	BI Technologies	3059Y	78PR5MEG (3059Y-1-505)	5,000,000	1 W	10	1-1/4" Rectangular	22	Side	Pins, Panel Mount	\$1.75