



[Click Here to Request a Large Quantity Quote](#)

RV112BF SERIES: DUAL AUDIO & LINEAR TAPER POTENTIOMETER 11mm 50mW±20%

Jameco SKU	Mfr Name	Manufacturer Series	Mfr P/N	Resistance (Ohms)	Power Rating (W)	Tolerance (%)	Shaft Type	Shaft Length	Position	Termination Style	Taper	Body Diameter	Price 1
2269495	Taiwan Alpha	RV112BF	RV112BF-40-25A-A10K	10,000	0.05	20	D	0.980"	Vertical	PCB, Snap-In	Audio	11 mm	\$1.49
2269503	Taiwan Alpha	RV112BF	RV112BF-40E1-25A-A50K	50,000	0.05	20	D	0.980"	Vertical	PCB, Panel Mount	Audio	11 mm	\$1.49
2269935	Taiwan Alpha	RV112BF	RV112BCF-40-25F-A50K	50,000	0.05	20	D (.08" H Collar)	0.980"	Vertical	PCB, Snap-In	Audio	11 mm	\$1.49
2271647	Taiwan Alpha	RV112BF	RV112BF-40-25A-A50K	50,000	0.05	20	D (.19" H Collar)	0.980"	Vertical	PCB, Snap-In	Audio	11 mm	\$1.49
2272015	Taiwan Alpha	RV112BF	RV112BF-40-25A-A100K	100,000	0.05	20	D	0.980"	Vertical	PCB, Snap-In	Audio	11 mm	\$1.49
2272023	Taiwan Alpha	RV112BF	RV112BF-40-25A-A500K	500,000	0.05	20	D	0.980"	Vertical	PCB, Snap-In	Audio	11 mm	\$1.49
2272031	Taiwan Alpha	RV112BF	RV112BF-40-25A-A1M	1,000,000	0.05	20	D	0.980"	Vertical	PCB, Snap-In	Audio	11 mm	\$1.49
2272039	Taiwan Alpha	RV112BF	RV112BF-40-25A-B1K	1,000	0.05	20	D	0.980"	Vertical	PCB, Snap-In	Linear	11 mm	\$1.49
2271639	Taiwan Alpha	RV112BF	RV112BF-40E1-25A-B5K	5,000	0.05	20	D	0.980"	Vertical	PCB, Panel Mount	Linear	11 mm	\$1.49
2272047	Taiwan Alpha	RV112BF	RV112BF-40-25A-B10K	10,000	0.05	20	D	0.980"	Vertical	PCB, Snap-In	Linear	11 mm	\$1.49
2272071	Taiwan Alpha	RV112BF	RV112BF-40-25A-B50K	50,000	0.05	20	D	0.980"	Vertical	PCB, Snap-In	Linear	11 mm	\$1.49
2272055	Taiwan Alpha	RV112BF	RV112BF-40-25A-B100K	100,000	0.05	20	D	0.980"	Vertical	PCB, Snap-In	Linear	11 mm	\$1.49
2272063	Taiwan Alpha	RV112BF	RV112BF-40E1-25A-B1M	1,000,000	0.05	20	D	0.980"	Vertical	PCB, Panel Mount	Linear	11 mm	\$1.49