


[Click Here to Request a Large Quantity Quote](#)

TRIMMER POTENTIOMETERS 3296 SERIES: 1/2 WATT ◦ 3/8" SQUARE ◦ -10% (-55°C to +150°C)

Jameco SKU	Mfr Name	Mfg. Series	Mfr P/N	Resistance (Ohms)	Power Rating	Tolerance (%)	Type	Number of Turns	Actuator Orientation	Price 1
2180560	Spectrol/Vishay Corporation	3296P	64P500 (3296P-1-500)	50	0.5 W	10	3/8" Square	25	Side	\$1.95
2180615	Spectrol/Vishay Corporation	3296P	64P201 (3296P-1-201)	200	0.5 W	10	3/8" Square	25	Side	\$1.95
2180551	Spectrol/Vishay Corporation	3296P	64P501/67PR500 (3296P-1-)	500	0.5 W	10	3/8" Square	25	Side	\$1.95
2037982	BI Technologies	3296P	67PR102 (3296P-1-102)	1,000	0.5 W	10	3/8" Square	20	Side	\$1.95
2180607	Spectrol/Vishay Corporation	3296P	64P202/3296P-1-202VP	2,000	0.5 W	10	3/8" Square	25	Side	\$1.95
2180623	Spectrol/Vishay Corporation	3296P	64P252 (3296P-1-252)	2,500	0.5 W	10	3/8" Square	25	Side	\$1.95
769354	Spectrol/Vishay Corporation	3296P	64P502 (3296P-1-502)	5,000	0.5 W	10	3/8" Square	25	Side	\$1.95
853513	Spectrol/Vishay Corporation	3296P	64P/67PR103/3296P-1-103	10,000	0.5 W	10	3/8" Square	25	Side	\$1.95
769338	Spectrol/Vishay Corporation	3296P	64P203/67PR20K (3296P-1-)	20,000	0.5 W	10	3/8" Square	25	Side	\$1.95
2180586	Spectrol/Vishay Corporation	3296P	64P253 (3296P-1-253)	25,000	0.5 W	10	3/8" Square	25	Side	\$1.95
769362	Clarostat/Honeywell	3296P	364P503 (3296P-1-503)	50,000	0.5 W	10	3/8" Square	25	Side	\$1.95
2180578	Spectrol/Vishay Corporation	3296P	64P254 (3296P-1-254)	250,000	0.5 W	10	3/8" Square	25	Side	\$1.95
2038002	Clarostat/Honeywell	3296P	364R504 (3296P-1-504)	500,000	0.5 W	10	3/8" Square	25	Side	\$1.95
769320	Spectrol/Vishay Corporation	3296P	64P105 (3296P-1-105)	1,000,000	0.5 W	10	3/8" Square	25	Side	\$1.95
769371	Clarostat/Honeywell	3296W	364W10 (3296W-1-100)	10	0.5 W	10	3/8" Square	25	Top	\$1.95
1946421	BI Technologies	3296W	67WR50R (3296W-1-500)	50	0.5 W	20	3/8" Square	20	Top	\$1.95
853530	Spectrol/Vishay Corporation	3296W	64W101/364W101 (3296W-1-)	100	0.5 W	10	3/8" Square	25	Top	\$1.95
1156787	BI Technologies	3296W	67WR200 (3296W-1-201)	200	0.5 W	10	3/8" Square	20	Top	\$1.95
853759	BI Technologies	3296W	67WR500 (3296W-1-501)	500	0.5 W	10	3/8" Square	20	Top	\$1.95
853556	Weston Electronics	3296W	850W1K (3296W-1-102)	1,000	0.5 W	10	3/8" Square	25	Top	\$1.75
853652	BI Technologies	3296W	67WR2K/3296W-1-202VP	2,000	0.5 W	10	3/8" Square	20	Top	\$1.95
853775	BI Technologies	3296W	67WR5K/3296W-1-502VP	5,000	0.5 W	10	3/8" Square	20	Top	\$1.95
241146	Jameco Valuepro	3296W	3296W-1-103VP	10,000	0.5 W	10	3/8" Square	25	Top	\$1.95
853572	Bourns	3296W	3296W-1-103LF	10,000	0.5 W	10	3/8" Square	20	Top	\$2.29
853679	Spectrol/Vishay Corporation	3296W	3296W-1-203 (64W203/67WR20K)	20,000	0.5 W	10	3/8" Square	25	Top	\$1.95
853716	Bourns	3296W	3296W-1-253 (67WR25K)	25,000	0.5 W	10	3/8" Square	25	Top	\$1.95
853791	Bourns	3296W	3296W-1-503LF(67WR50K)	50,000	0.5 W	10	3/8" Square	25	Top	\$1.95
853599	BI Technologies	3296W	67WR100K/64T104/3296W-1	100,000	0.5 W	10	3/8" Square	20	Top	\$1.95
853695	BI Technologies	3296W	67WR200K (3296W-1-204)	200,000	0.5 W	10	3/8" Square	20	Top	\$1.95
1967248	Bourns	3296W	67WR250K (3296W-1-254)	250,000	0.5 W	10	3/8" Square	25	Top	\$1.95
853610	BI Technologies	3296W	67WR1MEG (3296W-1-105)	1,000,000	0.5 W	10	3/8" Square	20	Top	\$1.95
769514	Spectrol/Vishay Corporation	3296X	64X100 (3296X-1-100)	10	0.5 W	10	3/8" Square	25	Side	\$1.95
2195139	BI Technologies	3296X	67XR50 (3296X-1-500)	50	0.5 W	20	3/8" Square	20	Side	\$1.95
769531	Spectrol/Vishay Corporation	3296X	64X201 (3296X-1-201)	200	0.5 W	10	3/8" Square	25	Side	\$1.95
1156921	Spectrol/Vishay Corporation	3296X	3296X-1-205/64X205	500	0.5 W	10	3/8" Square	25	Side	\$1.95
853960	Spectrol/Vishay Corporation	3296X	64X501 (3296X-1-501)	500	0.5 W	10	3/8" Square	25	Side	\$1.95
853855	BI Technologies	3296X	67XR1K/364X1K(3296X-1-102)	1,000	0.5 W	10	3/8" Square	20	Side	\$1.95
769549	Spectrol/Vishay Corporation	3296X	64X2K (3296X-1-202)	2,000	0.5 W	10	3/8" Square	25	Side	\$1.95
853986	Spectrol/Vishay Corporation	3296X	64X502 (3296X-1-502)	5,000	0.5 W	10	3/8" Square	25	Side	\$1.95
853871	BI Technologies	3296X	67XR10K/364X10K/3296X-1VP	10,000	0.5 W	10	3/8" Square	20	Side	\$1.95



[Click Here to Request a Large Quantity Quote](#)

TRIMMER POTENTIOMETERS 3296 SERIES: 1/2 WATT ◦ 3/8" SQUARE ◦ -10% (-55°C to +150°C)

Jameco SKU	Mfr Name	Mfg. Series	Mfr P/N	Resistance (Ohms)	Power Rating	Tolerance (%)	Type	Number of Turns	Actuator Orientation	Price 1
853951	Spectrol/Vishay Corporation	3296X	64X203 (3296X-1-203)	20,000	0.5 W	10	3/8" Square	25	Side	\$1.95
1967264	Spectrol/Vishay Corporation	3296X	64X253/3296X-1-253VP	25,000	0.5 W	10	3/8" Square	25	Side	\$1.95
854006	Spectrol/Vishay Corporation	3296X	64X50K (3296X-1-503)	50,000	0.5 W	10	3/8" Square	25	Side	\$1.95
853898	Spectrol/Vishay Corporation	3296X	364/64X100K/3296X-1-104LF	100,000	0.5 W	10	3/8" Square	25	Side	\$1.95
769557	Spectrol/Vishay Corporation	3296X	64X200K (3296X-1-204)	200,000	0.5 W	10	3/8" Square	25	Side	\$1.95
769565	Spectrol/Vishay Corporation	3296X	64X254 (3296X-1-254)	250,000	0.5 W	10	3/8" Square	25	Side	\$1.95
853919	Spectrol/Vishay Corporation	3296X	64X105 (3296X-1-105)	1,000,000	0.5 W	10	3/8" Square	25	Side	\$1.95
240338	Spectrol/Vishay Corporation	3296Y	64Y100/3296Y-1-100LF	10	0.5 W	10	3/8" Square	25	Top	\$1.95
240725	BI Technologies	3296Y	67YR100 /64Y100/3296Y-1-1	100	0.5 W	10	3/8" Square	20	Top	\$1.95
240733	BI Technologies	3296Y	67YR200 (3296Y-1-201)	200	0.5 W	10	3/8" Square	20	Top	\$1.95
240389	Spectrol/Vishay Corporation	3296Y	64Y501 (3296Y-1-501)	500	0.5 W	10	3/8" Square	25	Top	\$1.95
240398	BI Technologies	3296Y	67YR1K(3296Y-1-102VP)	1,000	0.5 W	10	3/8" Square	20	Top	\$1.75
240750	Jameco Valuepro	3296Y	3296Y-1-102-VP/LF	1,000	0.5 W	10	3/8" Square	25	Top	\$1.95
240769	Mepco	3296Y	3296Y-1-202VP(8024E202)	2,000	0.5 W	10	3/8" Square	25	Top	\$1.95
240777	BI Technologies	3296Y	3296Y-1-502VP/LF	5,000	0.5 W	10	3/8" Square	20	Top	\$1.95
240427	BI Technologies	3296Y	67YR10K/3296Y-1-103VP/LF	10,000	0.5 W	10	3/8" Square	20	Top	\$1.75
240426	Bourns	3296Y	3296Y-1-103LF	10,000	0.5 W	10	3/8" Square	25	Top	\$1.95
240434	BI Technologies	3296Y	64Y203/67XR20K (3296Y-1-2	20,000	0.5 W	10	3/8" Square	20	Top	\$1.95
240813	BI Technologies	3296Y	67YR50K (3296Y-1-503)	50,000	0.5 W	10	3/8" Square	20	Top	\$1.95
769573	Clarostat/Honeywell	3296Y	364Y200K (3296Y-1-204)	200,000	0.5 W	10	3/8" Square	25	Top	\$1.95
240493	Spectrol/Vishay Corporation	3296Y	64Y1MEG (3296Y-1-105)	1,000,000	0.5 W	10	3/8" Square	25	Top	\$1.95
1157026	Spectrol/Vishay Corporation	3296Z	64Z100 (3296Z-1-100)	10	0.5 W	10	3/8" Square	25	Side	\$1.95
769637	Spectrol/Vishay Corporation	3296Z	64Z500R (3296Z-1-501)	500	0.5 W	10	3/8" Square	25	Side	\$1.95
854049	BI Technologies	3296Z	3296Z-1-102 (67ZR1K)	1,000	0.5 W	10	3/8" Square	20	Side	\$1.95
854081	Spectrol/Vishay Corporation	3296Z	64Z5K (3296Z-1-502)	5,000	0.5 W	10	3/8" Square	25	Side	\$1.95
854065	BI Technologies	3296Z	3296Z-1-103VP(67ZR10K)	10,000	0.5 W	10	3/8" Square	20	Side	\$1.95
769645	Spectrol/Vishay Corporation	3296Z	64Z504 (3296Z-1-504)	500,000	0.5 W	10	3/8" Square	25	Side	\$1.95