



[Click Here to Request a Large Quantity Quote](#)

RV4NAY SERIES: LINEAR TAPER POTENTIOMETERS 26/28mm 2W (±10%)

Jameco SKU	Mfr Name	Manufacturer Series	Mfr P/N	Resistance (Ohms)	Power Rating	Tolerance (%)	Shaft Type	Shaft Length	Bushing Thread	Termination Style	Taper	Body Diameter	Price
2291247	Clarostat/Honeywell	RV4NAY	RV4NAYSD500A	50	2	10	Round Slotted	0.866"	3/8"-32 NEF	Solder, Panel Mount	Linear	26 mm	\$10.95
241568	Clarostat/PEC	RV4NAY	RV4NAYSD101A	100	2	10	Round Slotted	0.866"	3/8"-32 NEF	Solder, Panel Mount	Linear	28 mm	\$10.95
241584	Clarostat/PEC	RV4NAY	RV4NAYSD251A	250	2	10	Round Slotted	0.866"	3/8"-32 NEF	Solder, Panel Mount	Linear	29 mm	\$10.95
183610	Clarostat/Honeywell	RV4NAY	RV4NAYSD501A	500	2	10	Round Slotted	0.866"	3/8"-32 NEF	Solder, Panel Mount	Linear	26 mm	\$10.95
13936	Clarostat/Honeywell	RV4NAY	RV4NAYSD102A	1,000	2	10	Round Slotted	0.866"	3/8"-32 NEF	Solder, Panel Mount	Linear	26 mm	\$10.95
241613	Clarostat/Honeywell	RV4NAY	RV4NAYSD202A	2,000	2	10	Round Slotted	0.866"	3/8"-32 NEF	Solder, Panel Mount	Linear	26 mm	\$10.95
2291263	Clarostat/Honeywell	RV4NAY	RV4NAYSD252A	2,500	2	10	Round Slotted	0.866"	3/8"-32 NEF	Solder, Panel Mount	Linear	28 mm	\$10.95
13995	Clarostat/PEC	RV4NAY	RV4NAYSD502A	5,000	2	10	Round Slotted	0.866"	3/8"-32 NEF	Solder, Panel Mount	Linear	26 mm	\$10.95
2160518	Jameco Valuepro	R24	R24KM-B10K	10,000	2	10	Round Slotted	0.787"	3/8"-32 NEF	Solder, Panel Mount	Linear	24 mm	\$6.95
13952	Clarostat/Honeywell	RV4NAY	RV4NAYSD103A	10,000	2	10	Round Slotted	0.866"	3/8"-32 NEF	Solder, Panel Mount	Linear	26 mm	\$10.95
241656	Clarostat/PEC	RV4NAY	RV4NAYSD203A	20,000	2	10	Round Slotted	0.866"	3/8"-32 NEF	Solder, Panel Mount	Linear	28 mm	\$10.95
241664	Clarostat/Honeywell	RV4NAY	RV4NAYSD253A	25,000	2	10	Round Slotted	0.866"	3/8"-32 NEF	Solder, Panel Mount	Linear	26 mm	\$10.95
95417	Clarostat/Honeywell	RV4NAY	RV4NAYSD503A	50,000	2	10	Round Slotted	0.866"	3/8"-32 NEF	Solder, Panel Mount	Linear	26 mm	\$10.95
13979	Clarostat/PEC	RV4NAY	RV4NAYSD104A	100,000	2	10	Round Slotted	0.866"	3/8"-32 NEF	Solder, Panel Mount	Linear	28 mm	\$10.95
2291271	Clarostat/PEC	RV4NAY	RV4NAYSD504A	500,000	2	10	Round Slotted	0.866"	3/8"-32 NEF	Solder, Panel Mount	Linear	28 mm	\$10.95
2291279	Clarostat/PEC	RV4NAY	RV4NAYSD105A	1,000,000	2	10	Round Slotted	0.866"	3/8"-32 NEF	Solder, Panel Mount	Linear	28 mm	\$10.95