



[Click Here to Request a Large Quantity Quote](#)

BULK CABLE FLAT RIBBON

Jameco Part#	Manufacturer	Manufacturer Part #	Wire Gauge (AWG)	Number of Conductors	Cable Length (feet)	Color	Rated Voltage (V)	Center Spacing	Price 1
643794	Jameco Valuepro	171-10-10	28	10	10.0	Gray	300	0.05"	\$ 3.49
643815	Jameco Valuepro	171-10-100	28	10	100.0	Gray	300	0.05"	\$ 22.95
643831	Jameco Valuepro	171-16-10	28	16	10.0	Gray	300	0.05"	\$ 4.49
643858	Jameco Valuepro	171-16-100	28	16	100.0	Gray	300	0.05"	\$ 34.95
643874	Jameco Valuepro	171-20-10	28	20	10.0	Gray	300	0.05"	\$ 5.49
643891	Jameco Valuepro	171-20-100	28	20	100.0	Gray	300	0.05"	\$ 39.95
643962	Jameco Valuepro	171-26-10	28	26	10.0	Gray	300	0.05"	\$ 7.95
643989	Jameco Valuepro	171-26-100	28	26	100.0	Gray	300	0.05"	\$ 57.95
644121	Jameco Valuepro	171-40-25	28	40	25.0	Gray	300	0.05"	\$ 26.95
644130	Jameco Valuepro	171-40-100	28	40	100.0	Gray	300	0.05"	\$ 79.95
644172	Jameco Valuepro	171-50-100	28	50	100.0	Gray	300	0.05"	\$ 89.95
639672	Jameco Valuepro	28RC10-10VP	28	10	10.0	Rainbow	300	0.05"	\$ 5.95
643508	Jameco Valuepro	28RC10-25VP	28	10	25.0	Rainbow	300	0.05"	\$ 11.95
643516	Jameco Valuepro	28RC10-100VP	28	10	100.0	Rainbow	300	0.05"	\$ 39.95
643532	Jameco Valuepro	28RC16-10VP	28	16	10.0	Rainbow	300	0.05"	\$ 8.95
643559	Jameco Valuepro	28RC16-100VP	28	16	100.0	Rainbow	300	0.05"	\$ 69.95
643575	Jameco Valuepro	28RC20-10VP	28	20	10.0	Rainbow	300	0.05"	\$ 9.95
643583	Jameco Valuepro	28RC20-25VP	28	20	25.0	Rainbow	300	0.05"	\$ 17.95
643591	Jameco Valuepro	28RC20-100VP	28	20	100.0	Rainbow	300	0.05"	\$ 69.95
643639	Jameco Valuepro	28RC25-100VP	28	25	100.0	Rainbow	300	0.05"	\$ 89.95
643698	Jameco Valuepro	28RC40-10VP	28	40	10.0	Rainbow	300	0.05"	\$ 24.95