


[Click Here to Request a Large Quantity Quote](#)

**TRIMMER POTENTIOMETERS 3386 SERIES: 1/2 WATT ◦ 3/8" SQUARE ◦ ±10% (-55°C to +125°C)**

Jameco SKU	Mfr Name	Mfg. Series	Mfr P/N	Resistance (Ohms)	Power Rating	Tolerance (%)	Type	Number of Turns	Actuator Orientation	1
770646	BI Technologies	3386B	72XWR50 (3386B-1-500)	50	0.5 W	10	3/8" Square	1	Side	\$1.25
854786	BI Technologies	3386B	3386B-1-101LF	100	0.5 W	10	3/8" Square	1	Side	\$1.25
2180674	Spectrol/Vishay Corporation	3386B	63V201 (3386B-1-201)	200	0.5 W	10	3/8" Square	1	Side	\$1.25
2180682	Spectrol/Vishay Corporation	3386B	63V102/72XWR1K (3386B-1-1	1,000	0.5 W	10	3/8" Square	1	Side	\$1.25
770638	BI Technologies	3386B	72XWR2500 (3386B-1-252)	2,500	0.5 W	10	3/8" Square	1	Side	\$1.25
2195243	BI Technologies	3386B	72XWR50K (3386B-1-503)	50,000	0.5 W	10	3/8" Square	1	Side	\$1.25
2180666	Spectrol/Vishay Corporation	3386B	63V104/72XWK100K (3386B-1	100,000	0.5 W	10	3/8" Square	1	Side	\$1.25
2287631	BI Technologies	3386B	72XWR250K(3386B-1-254)	250,000	0.5 W	10	3/8" Square	1	Side	\$1.25
2037587	BI Technologies	3386B	72XWR2MEG (3386B-1-205VP)	2,000,000	0.5 W	10	3/8" Square	1	Side	\$1.25
2162775	BI Technologies	3386C	72XLR500(3386C-1-501)	500	0.5 W	10	3/8" Square	1	Side	\$1.25
2180324	Spectrol/Vishay Corporation	3386C	63S1K/72XLR1K(3386C-1-102	1,000	0.5 W	10	3/8" Square	1	Side	\$1.09
2180332	Spectrol/Vishay Corporation	3386C	63S5K (3386C-1-502)	5,000	0.5 W	10	3/8" Square	1	Side	\$1.09
2198962	BI Technologies	3386C	72XLR5K (3386C-1-502)	5,000	0.5 W	10	3/8" Square	1	Side	\$1.25
2200997	BI Technologies	3386C	72XLR10K (3386C-1-103)	10,000	0.5 W	10	3/8" Square	1	Side	\$1.25
2198938	BI Technologies	3386C	72XLR20K (3386C-1-203)	20,000	0.5 W	10	3/8" Square	1	Side	\$1.25
2180341	Spectrol/Vishay Corporation	3386C	63S253 (3386C-1-253)	25,000	0.5 W	10	3/8" Square	1	Side	\$1.25
2198954	BI Technologies	3386C	72XLR25K (3386C-1-253)	25,000	0.5 W	10	3/8" Square	1	Side	\$1.25
2198989	BI Technologies	3386C	72XLR50K/72RXLR50K (3386C	50,000	0.5 W	10	3/8" Square	1	Side	\$1.25
2198920	Spectrol/Vishay Corporation	3386C	63S104/72XLR100K (3386C-1	100,000	0.5 W	10	3/8" Square	1	Side	\$1.25
2198946	BI Technologies	3386C	72XLR200K (3386C-1-204)	200,000	0.5 W	10	3/8" Square	1	Side	\$1.25
2198997	BI Technologies	3386C	72XLR500K (3386C-1-504)	500,000	0.5 W	10	3/8" Square	1	Side	\$1.25
2198911	BI Technologies	3386C	72XLR1MEG (3386C-1-105)	1,000,000	0.5 W	10	3/8" Square	1	Side	\$1.25
854823	BI Technologies	3386F	72PMR10 (3386F-1-100)	10	0.5 W	10	3/8" Square	1	Top	\$1.25
770654	Spectrol/Vishay Corporation	3386F	63M101 (3386F-1-101)	100	0.5 W	10	3/8" Square	1	Top	\$1.25
2235217	Jameco Valuepro	3386F	3386F-1-102VP	1,000	0.5 W	10	3/8" Square	1	Top	\$1.25
854989	BI Technologies	3386F	72PMR2K/3386F-1-202VP	2,000	0.5 W	10	3/8" Square	1	Top	\$1.25
855041	BI Technologies	3386F	72PMR2500 (3386F-1-252)	2,500	0.5 W	10	3/8" Square	1	Top	\$1.25
2180543	Spectrol/Vishay Corporation	3386F	63M252 (3386F-1-252)	2,500	0.5 W	10	3/8" Square	1	Top	\$1.09
2235225	Jameco Valuepro	3386F	3386F-1-103VP(72PMR10K)	10,000	0.5 W	10	3/8" Square	1	Top	\$1.25
2285615	Bourns	3386F	3386F-1-203LF	20,000	0.5 W	10	3/8" Square	1	Top	\$1.25
855017	Spectrol/Vishay Corporation	3386F	63M20K/363M20K (3386F-1-203)	20,000	0.5 W	10	3/8" Square	1	Top	\$1.09
2180535	Spectrol/Vishay Corporation	3386F	63M25K (3386F-1-253)	25,000	0.5 W	10	3/8" Square	1	Top	\$1.25
855105	BI Technologies	3386F	72PMR50K/63M503 (3386F-1	50,000	0.5 W	10	3/8" Square	1	Top	\$1.25
854920	BI Technologies	3386F	72PMR100K (3386F-1-104)	100,000	0.5 W	10	3/8" Square	1	Top	\$1.25
770697	BI Technologies	3386F	72PMR200K (3386F-1-204)	200,000	0.5 W	10	3/8" Square	1	Top	\$1.25
855076	BI Technologies	3386F	72PMR250K/3386F-1-254VP	250,000	0.5 W	10	3/8" Square	1	Top	\$1.25
770726	Clarostat/Honeywell	3386F	363M500K/72PMR500K (3386F	500,000	0.5 W	10	3/8" Square	1	Top	\$1.25
2180527	Spectrol/Vishay Corporation	3386F	63M205 (3386F-1-205)	2,000,000	0.5 W	10	3/8" Square	1	Top	\$1.25
1947634	BI Technologies	3386F	72PMR5MEG (3386F-1-505)	5,000,000	0.5 W	10	3/8" Square	1	Top	\$1.25
770785	BI Technologies	3386H	72RXR500 (3386H-1-501)	500	0.5 W	10	3/8" Square	1	Side	\$1.25
855130	BI Technologies	3386H	72RXR1K (3386H-1-102)	1,000	0.5 W	10	3/8" Square	1	Side	\$1.25






[Click Here to Request a Large Quantity Quote](#)

**TRIMMER POTENTIOMETERS 3386 SERIES: 1/2 WATT ◦ 3/8" SQUARE ◦ ±10% (-55°C to +125°C)**

Jameco SKU	Mfr Name	Mfg. Series	Mfr P/N	Resistance (Ohms)	Power Rating	Tolerance (%)	Type	Number of Turns	Actuator Orientation	1
770769	BI Technologies	3386H	72RXR2K (3386H-1-202)	2,000	0.5 W	10	3/8" Square	1	Side	\$1.25
770734	BI Technologies	3386H	72RXR10K/3386H-1-103LP	10,000	0.5 W	10	3/8" Square	1	Side	\$1.25
770777	Bourns	3386H	3386H-1-203LF	20,000	0.5 W	10	3/8" Square	1	Side	\$1.25
770654	Spectrol/Vishay Corporation	3386K	63M101 (3386K-1-101)	100	0.5 W	10	3/8" Square	1	Top	\$1.25
2199041	BI Technologies	3386M	72PXR50 (3386M-1-500)	50	0.5 W	10	3/8" Square	1	Top	\$1.25
2199084	BI Technologies	3386M	72RPXR500 (3386M-1-501)	500	0.5 W	10	3/8" Square	1	Top (Grey)	\$1.25
2199050	BI Technologies	3386M	72PXR500 (3386M-1-501)	500	0.5 W	10	3/8" Square	1	Top (White)	\$1.25
2199092	BI Technologies	3386M	72RPXR1K (3386M-1-102)	1,000	0.5 W	10	3/8" Square	1	Top	\$1.25
2199009	BI Technologies	3386M	72PXR2K (3386M-1-202)	2,000	0.5 W	10	3/8" Square	1	Top	\$1.25
2199068	BI Technologies	3386M	72RPXR5K (3386M-1-502)	5,000	0.5 W	10	3/8" Square	1	Top	\$1.25
2199017	BI Technologies	3386M	72PXR200K (3386M-1-204)	200,000	0.5 W	10	3/8" Square	1	Top	\$1.25
2199076	BI Technologies	3386M	72RPXR5MEG (3386M-1-505)	5,000,000	0.5 W	10	3/8" Square	1	Top	\$1.25
254298	BI Technologies	3386P	72PR10 (3386P-1-100)	10	0.5 W	10	3/8" Square	1	Top	\$1.25
855316	BI Technologies	3386P	72PR20 (3386P-1-200VP)	20	0.5 W	10	3/8" Square	1	Top	\$1.25
254289	Spectrol/Vishay Corporation	3386P	63P500/72PR50 (3386P-1-50)	50	0.5 W	10	3/8" Square	1	Top	\$1.25
254297	Spectrol/Vishay Corporation	3386P	63P101/72PR100 (3386P-1-)	100	0.5 W	10	3/8" Square	1	Top	\$1.25
254300	BI Technologies	3386P	72PR200 (3386P-1-201-VP)	200	0.5 W	10	3/8" Square	1	Top	\$1.25
2200911	BI Technologies	3386P	72PR250 (3386P-1-251)	250	0.5 W	10	3/8" Square	1	Top	\$1.25
2291047	Jameco Valuepro	3386P	3386P-1-LS500	500	0.5 W	10	3/8" Square	1	Top	\$1.39
43123	Spectrol/Vishay Corporation	3386P	63P501/72PR500 (3386P-1-5)	500	0.5 W	10	3/8" Square	1	Top	\$1.25
2291055	Jameco Valuepro	3386P	3386P-1-LS1K	1,000	0.5 W	10	3/8" Square	1	Top	\$1.39
42964	Jameco Valuepro	3386P	3386P-1-102VP/LF	1,000	0.5 W	10	3/8" Square	1	Top	\$1.25
43043	Spectrol/Vishay Corporation	3386P	63P202 (3386P-1-202)	2,000	0.5 W	10	3/8" Square	1	Top	\$1.25
2179307	Spectrol/Vishay Corporation	3386P	63P5K(T640) [3386P1-502]	5,000	0.5 W	10	3/8" Square	1	Top Thumb Wheel	\$0.79
2199121	BI Technologies	3386P	72PTR5K (3386P-1-502)	5,000	0.5 W	10	3/8" Square	1	Top	\$0.89
2291063	Jameco Valuepro	3386P	3386P-1-LS5K	5,000	0.5 W	10	3/8" Square	1	Top	\$1.39
43078	Murata	3386P	3104P-1-502/3386P-1-502	5,000	0.5 W	10	3/8" Square	1	Top	\$1.25
2200639	BI Technologies	3386P	72PSR10K (3386P-1-103)	10,000	0.5 W	10	3/8" Square	1	Top	\$1.09
2291071	Jameco Valuepro	3386P	3386P-1-LS10K	10,000	0.5 W	10	3/8" Square	1	Top	\$1.39
43001	BI Technologies	3386P	72PR10K (3386P-1-103)	10,000	0.5 W	10	3/8" Square	1	Top	\$1.25
43051	BI Technologies	3386P	72PR20K(3386P-1-203LF/VP)	20,000	0.5 W	10	3/8" Square	1	Top	\$1.25
254377	Spectrol/Vishay Corporation	3386P	63P25K/72PR25K/3386P-1-VP	25,000	0.5 W	10	3/8" Square	1	Top	\$1.25
43107	Spectrol/Vishay Corporation	3386P	3386P-1-503 (63P503)	50,000	0.5 W	10	3/8" Square	1	Top	\$1.25
2291079	Jameco Valuepro	3386P	3386P-1-LS100K	100,000	0.5 W	10	3/8" Square	1	Top	\$1.39
43027	Jameco Valuepro	3386P	3386P-1-104VP/LF	100,000	0.5 W	10	3/8" Square	1	Top	\$1.25
254406	BI Technologies	3386P	72PR200K (3386P-1-204)	200,000	0.5 W	10	3/8" Square	1	Top	\$1.25
2200903	BI Technologies	3386P	72PR250K (3386P-1-254)	250,000	0.5 W	10	3/8" Square	1	Top	\$1.25
43060	Jameco Valuepro	3386P	3386P-1-304VP (F300K)	300,000	0.5 W	10	3/8" Square	1	Top	\$1.25
2291087	Jameco Valuepro	3386P	3386P-1-LS500K	500,000	0.5 W	10	3/8" Square	1	Top	\$1.39
63212	Spectrol/Vishay Corporation	3386P	63P504 (3386P-1-504)	500,000	0.5 W	10	3/8" Square	1	Top	\$1.25
2291095	Jameco Valuepro	3386P	3386P-1-LS1MEG	1,000,000	0.5 W	10	3/8" Square	1	Top	\$1.39
42981	Allen Bradley	3386P	E2A1MEG/3386P-1-105VP	1,000,000	0.5 W	10	3/8" Square	1	Top	\$1.25
105216	Spectrol/Vishay Corporation	3386P	63P205 (3386P-1-205)	2,000,000	0.5 W	10	3/8" Square	1	Top	\$1.25






[Click Here to Request a Large Quantity Quote](#)

**TRIMMER POTENTIOMETERS 3386 SERIES: 1/2 WATT ◦ 3/8" SQUARE ◦ ±10% (-55°C to +125°C)**

Jameco SKU	Mfr Name	Mfg. Series	Mfr P/N	Resistance (Ohms)	Power Rating	Tolerance (%)	Type	Number of Turns	Actuator Orientation	1
2200938	BI Technologies	3386S	72RXWR750 (3386S-1-751)	750	0.5 W	10	3/8" Square	1	Side	\$1.25
770911	BI Technologies	3386S	72RXWR1K (3386S-1-102)	1,000	0.5 W	10	3/8" Square	1	Side	\$1.25
770929	BI Technologies	3386S	72RXWR2K/3386S-1-202LF	2,000	0.5 W	10	3/8" Square	1	Side	\$1.25
2038424	BI Technologies	3386S	72RXWR5K (3386S-1-502)	5,000	0.5 W	10	3/8" Square	1	Side	\$1.25
2200989	BI Technologies	3386S	72RXWR10K (3386S-1-103)	10,000	0.5 W	10	3/8" Square	1	Side	\$1.25
2285623	Bourns	3386S	3386S-1-504LF	500,000	0.5 W	10	3/8" Square	1	Side	\$1.25
2161385	Jameco Valuepro	3386T	3386T-1-LS500	500	0.5 W	10	3/8" Square	1	Top	\$1.39
2195227	BI Technologies	3386T	72PLR500 (3386T-1-501)	500	0.5 W	10	3/8" Square	1	Top	\$1.25
2118803	Jameco Valuepro	3386T	3386T-1-LS1K	1,000	0.5 W	10	3/8" Square	1	Top	\$1.39
2291031	Jameco Valuepro	3386T	3386T-1-102	1,000	0.5 W	10	3/8" Square	1	Top	\$1.25
2161393	Jameco Valuepro	3386T	3386T-1-LS5K	5,000	0.5 W	10	3/8" Square	1	Top	\$1.39
2291023	Jameco Valuepro	3386T	3386T-1-502	5,000	0.5 W	10	3/8" Square	1	Top	\$1.25
2118791	Jameco Valuepro	3386T	3386T-1-LS10K	10,000	0.5 W	10	3/8" Square	1	Top	\$1.39
2291007	Jameco Valuepro	3386T	3386T-1-103	10,000	0.5 W	10	3/8" Square	1	Top	\$1.25
2180316	Spectrol/Vishay Corporation	3386T	63T203 (3386T-1-203)	20,000	0.5 W	10	3/8" Square	1	Top	\$1.09
770937	BI Technologies	3386T	72PLR20K (3386T-1-203)	20,000	0.5 W	10	3/8" Square	1	Top	\$1.25
2161406	Jameco Valuepro	3386T	3386T-1-LS100K	100,000	0.5 W	10	3/8" Square	1	Top	\$1.39
2291015	Jameco Valuepro	3386T	3386T-1-104	100,000	0.5 W	10	3/8" Square	1	Top	\$1.25
2161414	Jameco Valuepro	3386T	3386T-1-LS500K	500,000	0.5 W	10	3/8" Square	1	Top	\$1.39
2161422	Jameco Valuepro	3386T	3386T-1-LS1MEG	1,000,000	0.5 W	10	3/8" Square	1	Top	\$1.39
2201084	BI Technologies	3386W	72RWR10 (3386W-1-100)	10	0.5 W	10	3/8" Square	1	Side	\$1.25
241411	BI Technologies	3386W	72RXLR500 (3386W-1-501)	500	0.5 W	10	3/8" Square	1	Side	\$1.25
241437	BI Technologies	3386W	72RWR2K/72RXR2K/3386W-1VP	2,000	0.5 W	10	3/8" Square	1	Side	\$1.25
770961	BI Technologies	3386W	72RWFR2K (3386W-1-202)	2,000	0.5 W	10	3/8" Square	1	Side	\$1.09
241445	Jameco Valuepro	3386W	3386W-1-502VP	5,000	0.5 W	10	3/8" Square	1	Side	\$1.25
2287383	Bourns	3386W	3386W-1-103LF	10,000	0.5 W	10	3/8" Square	1	Side	\$1.25
241461	BI Technologies	3386W	72RXLR20K (3386W-1-203)	20,000	0.5 W	10	3/8" Square	1	Side	\$1.25
2285631	Bourns	3386W	3386W-1-253LF	25,000	0.5 W	10	3/8" Square	1	Side	\$1.25
2201009	BI Technologies	3386W	72RWR50K (3386W-1-503)	50,000	0.5 W	10	3/8" Square	1	Side	\$1.25
241517	Jameco Valuepro	3386W	3386W-1-254VP/LF	250,000	0.5 W	10	3/8" Square	1	Side	\$1.25
771067	Spectrol/Vishay Corporation	3386X	63X500 (3386X-1-500)	50	0.5 W	10	3/8" Square	1	Side	\$1.25
771024	BI Technologies	3386X	72XR100/63X100/3386X-101L	100	0.5 W	10	3/8" Square	1	Side	\$1.25
264621	Spectrol/Vishay Corporation	3386X	63X200R/3386X-1-201LF	200	0.5 W	10	3/8" Square	1	Side	\$1.25
2180658	Spectrol/Vishay Corporation	3386X	63X251 (3386X-1-251)	250	0.5 W	10	3/8" Square	1	Side	\$1.25
771075	Spectrol/Vishay Corporation	3386X	63X500/72XR500 (3386X-1-5)	500	0.5 W	10	3/8" Square	1	Side	\$1.25
264647	Jameco Valuepro	3386X	72XR1K (3386X-1-102)	1,000	0.5 W	10	3/8" Square	1	Side	\$1.25
771041	Spectrol/Vishay Corporation	3386X	72XR2K/63X2K(3386X-1-202)	2,000	0.5 W	10	3/8" Square	1	Side	\$1.25
264699	BI Technologies	3386X	72XR2.5K(3386X-1-252VP/LP)	2,500	0.5 W	10	3/8" Square	1	Side	\$1.25
2200971	BI Technologies	3386X	72XR5K (3386X-1-502)	5,000	0.5 W	10	3/8" Square	1	Side	\$1.25
855771	Spectrol/Vishay Corporation	3386X	63X203/3386X-1-203LF	20,000	0.5 W	10	3/8" Square	1	Side	\$1.25
264698	Spectrol/Vishay Corporation	3386X	63X253/72XR25K/3386X-1-VP	25,000	0.5 W	10	3/8" Square	1	Side	\$1.25
264701	Spectrol/Vishay Corporation	3386X	63X50K (3386X-1-503)	50,000	0.5 W	10	3/8" Square	1	Side	\$1.25
771059	Spectrol/Vishay Corporation	3386X	63X204/3386X-1-204LF	200,000	0.5 W	10	3/8" Square	1	Side	\$1.25

[Click Here to Request a Large Quantity Quote](#)



**TRIMMER POTENTIOMETERS 3386 SERIES: 1/2 WATT ◦ 3/8" SQUARE ◦ ±10% (-55°C to +125°C)**

Jameco SKU	Mfr Name	Mfg. Series	Mfr P/N	Resistance (Ohms)	Power Rating	Tolerance (%)	Type	Number of Turns	Actuator Orientation	1
<a href="#">264735</a>	Spectrol/Vishay Corporation	3386X	63X254 (3386X-1-254)	250,000	0.5 W	10	3/8" Square	1	Side	\$1.25
<a href="#">264743</a>	Clarostat/Honeywell	3386X	363X500K/63X500K (3386X-1)	500,000	0.5 W	10	3/8" Square	1	Side	\$1.25
<a href="#">771032</a>	Spectrol/Vishay Corporation	3386X	63X105 (3386X-1-105)	1,000,000	0.5 W	10	3/8" Square	1	Side	\$1.25
<a href="#">264760</a>	Spectrol/Vishay Corporation	3386X	63X205/72XR2MEG (3386X-1)	2,000,000	0.5 W	10	3/8" Square	1	Side	\$1.25