

Distributed by:

**JAMECO**<sup>®</sup>  
ELECTRONICS

**www.Jameco.com ♦ 1-800-831-4242**

The content and copyrights of the attached  
material are the property of its owner.

Jameco Part Number 115617

**Modular Telephony Cords**


Flat Modular Cable – PVC Jacket  
Suitable for Telephony, VoIP Telephony Applications  
AWG28 7x36 (0.12mm) Stranded Conductors  
Cross-Wired for Telephone-Voice Applications

- 304-001IV** 4-Wire 8" Ivory Patch Cord for Wall-Mounted Phones
- 304-007IV** 4-Wire 7' Ivory Line Cord
- 304-007SL** 4-Wire 7' Silver Line Cord
- 304-007WH** 4-Wire 7' White Line Cord
- 304-015IV** 4-Wire 15' Ivory Line Cord
- 304-015SL** 4-Wire 15' Silver Line Cord
- 304-015WH** 4-Wire 15' White Line Cord
- 304-025BK** 4-Wire 25' Black Line Cord
- 304-025IV** 4-Wire 25' Ivory Line Cord
- 304-025SL** 4-Wire 25' Silver Line Cord
- 304-025WH** 4-Wire 25' White Line Cord
- 304-050BK** 4-Wire 50' Black Line Cord
- 304-050IV** 4-Wire 50' Ivory Line Cord
- 304-050SL** 4-Wire 50' Silver Line Cord
- 304-050WH** 4-Wire 50' White Line Cord
- 304-100BK** 4-Wire 100' Black Line Cord
- 304-100IV** 4-Wire 100' Ivory Line Cord
- 304-100SL** 4-Wire 100' Silver Line Cord
- 304-100WH** 4-Wire 100' White Line Cord
- 306-007SL** 6-Wire 7' Silver Line Cord
- 306-015SL** 6-Wire 15' Silver Line Cord
- 306-025SL** 6-Wire 25' Silver Line Cord
- 308-007SL** 8-Wire 7' Silver Line Cord
- 308-015SL** 8-Wire 15' Silver Line Cord
- 308-025SL** 8-Wire 25' Silver Line Cord
- 314-007SL** 4-Wire 7' Silver AWG26 UL Cord
- 314-015SL** 4-Wire 15' Silver AWG26 UL Cord
- 314-025SL** 4-Wire 25' Silver AWG26 UL Cord


**Modular Data Cables**

Flat Modular Cable – PVC Jacket  
AWG28 7x36 (0.12mm) Stranded Conductors  
Straight-Wired for Data Applications

- 304-707SL** 4-Wire 7' Silver Data Cable
- 304-715SL** 4-Wire 15' Silver Data Cable
- 304-725SL** 4-Wire 25' Silver Data Cable
- 304-750SL** 4-Wire 50' Silver Data Cable
- 306-707SL** 6-Wire 7' Silver Data Cable
- 306-715SL** 6-Wire 15' Silver Data Cable
- 306-725SL** 6-Wire 25' Silver Data Cable
- 308-707SL** 8-Wire 7' Silver Data Cable
- 308-715SL** 8-Wire 15' Silver Data Cable
- 308-725SL** 8-Wire 25' Silver Data Cable




**304-001IV** 8-inch Ivory



*Cross-Wired for Telephone-Voice Applications*

- 304-007** 4C 7' Ivory, Silver, White Non-UL
- 304-015** 4C 15' Ivory, Silver, White Non-UL
- 304-025** 4C 25' Black, Ivory, Silver, White Non-UL
- 304-050** 4C 50' Black, Ivory, Silver, White Non-UL
- 304-100** 4C 100' Black, Ivory, Silver, White Non-UL
- 306-007SL** 6C 7' Silver Non-UL
- 306-015SL** 6C 15' Silver Non-UL
- 306-025SL** 6C 25' Silver Non-UL
- 308-007SL** 8C 7' Silver Non-UL
- 308-015SL** 8C 15' Silver Non-UL
- 308-025SL** 8C 25' Silver Non-UL
- 314-007SL** 4C 7' Silver AWG26 UL
- 314-015SL** 4C 15' Silver AWG26 UL
- 314-025SL** 4C 25' Silver AWG26 UL



*Straight-Wired for Data Applications*

- 304-707SL** 4C 7' Silver Non-UL
- 304-715SL** 4C 15' Silver Non-UL
- 304-725SL** 4C 25' Silver Non-UL
- 304-750SL** 4C 50' Silver Non-UL
- 306-707SL** 6C 7' Silver Non-UL
- 306-715SL** 6C 15' Silver Non-UL
- 306-725SL** 6C 25' Silver Non-UL
- 308-707SL** 8C 7' Silver Non-UL
- 308-715SL** 8C 15' Silver Non-UL
- 308-725SL** 8C 25' Silver Non-UL