



EcoLine™ Flux Remover

General Purpose Defluxer
1621

Introduction

EcoLine™ Flux Remover is a unique combination of hydrocarbon solvents and alcohols making it an excellent defluxer. Safe on plastics and rapidly evaporating, the Flux Remover dissolves type R, RMA, SA and most no-clean fluxes. Can also be used as an all-purpose cleaner for removal of light oils, silicones, waxes, greases and similar contaminants.

Features / Benefits
 EPA SNAP Approved
 Non-Ozone Depleting
 Safe on Most Plastics
 Zero Residue
 Rapidly Evaporating
 Non-Corrosive

Physical Properties	
Boiling Point	80°C / 176°F
Flash Point (TCC)	53°F
Evaporation Rate	NIF
Surface Tension	
Kauri-Butanol (KB Value)	

Chemical Components

Isopropanol.....	(67-63-0)	50-55%
Ethanol.....	(64-17-5)	5-10%-Aerosol 6-11%-Bulk
2-Methyl-2-Propanol.....	(75-65-0)	<<1%-Aerosol 1.4%-Bulk
Dimethyl Ketone.....	(67-64-1)	10-12%
Cyclotetramethylene Oxide.....	(109-99-9)	20-25%
Acetic Acid, Propyl Ester.....	(109-60-4)	5-10%
Carbon Dioxide (Aerosol Propellant).....	(124-38-9)	1-5%

Plastic Compatibility

Material	Compatibility	Material	Compatibility
ABS	Excellent	PMMA	Excellent
Nylon	Excellent	POM	Excellent
Lexan	Excellent	PP	Excellent
HDPE	Excellent	PS	Excellent
CDPE	Excellent	PTFE	Excellent
C. E. Phenolic	Excellent	PVC	Excellent

Environmental Policy

Techspray® is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Packaging and Availability

EcoLine™ Flux Remover may be ordered in the following container sizes:

1621-4S	4 Ounce Aerosol
1621-10S	10 Ounce Aerosol
1621-G	1 Gallon in Metal
1621-5G	33 Pounds in Metal
1621-54G	340 Pounds in Metal

Resources

Techspray® products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray® products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

North America
Tech Spray L.P.
P.O. Box 949
Amarillo, TX 79105
800-858-4043
email: tsales@techspray.com

Europe
Techspray International
UNIT 4, 44/46 Bunyan Road, Kempston
Bedford MK42 8HL United Kingdom
+44 (0) 1234 855443
email: tseurope@techspray.com

Countries Outside US
Call to locate a distributor
in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray® be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.



Tech Spray, L.P.
P.O. Box 949
Amarillo, TX 79105
www.techspray.com

Aerosol MSDS
[English](#)
[French](#)
[German](#)
[Italian](#)
[Spanish](#)

Bulk MSDS
[English](#)
[French](#)
[German](#)
[Italian](#)
[Spanish](#)



Copyright 2004 Tech Spray, L. P.
For Commercial Use Only