

VISES

PANA PRESS

CCTV

CELLULAR

SPEAKER MOUNTS

VISE COMBINATIONS

[BACK](#)

We have selected some of our most versatile [heads](#), [bases](#) and [base mounts](#) and created a series of very popular combinations. All feature interchangeable [heads](#), so you can add additional [heads](#) to do other specialized work (except model 201 PV Jr. Mini PanaVise). All are compatible with all our 300 series [base mounts](#) (except model 381 Vacuum Base PanaVise). All our vises and work holding devices come with a ["lifetime warranty."](#)

PV Jr. Mini PanaVise - Model 201



- More like a tool than a vise, the grooved jaws open to 2 7/8" (73mm) and are made from fiber reinforced thermal composite alloy.
- Jaws are controlled with a fine/coarse adjusting knob which permits very delicate work.
- Head movement is through three planes (360° rotation, 360° swivel and 210° pivot) and is controlled with a single knob.
- Base is made of die cast zinc, with a 4 5/16" (109.5mm) bolt circle countersunk for 1/4" (6.3mm) flathead bolts (not included).
- Compatible with all 300 series [base mounts](#).
- This unique vise is 6 3/4" tall (171.4mm) tall and weighs 1 1/4lbs. (0.6kgs).
- [Neoprene Jaw Pads](#) are available for

- holding extremely delicate items.
- View [201 Specifications Page](#)
- View [201 In Use Examples](#)

Standard PanaVise - Model 301



- The 301 Standard PanaVise is an all-purpose work holding unit, perfect for both industrial and home hobbyist applications.
- A single knob controls the "tilt, turn and rotate" function of the patented split ball, which allows the head to move easily and conveniently through three planes (360° rotation, 360° swivel and 90° pivot).
- Jaws are 2 1/2" (63.5mm) wide and open to 2 1/4" (57.1mm), and the base features a 4 5/16" (109.5mm) bolt circle.
- The combination stands 6 3/4" (171.4mm) tall, weighs 2lbs. 11oz. (1.2kg) and features the [300 Standard Base](#), the [303 Standard Head](#), and the [343 Nylon Jaws](#).

Multi-Purpose Work Center - Model 350



- This is one of our most versatile combinations, perfect for home or hobby needs.
- We start with a [376 Self-Centering Extra-Wide Opening Head](#), we include the [300 Standard Base](#), and finish off with the [312 Parts Tray Base Mount](#).
- The 350 Multi-Purpose Work Center stands 7 7/8" (200mm) tall and weighs 5lbs. (2.3kgs).
- For electronics buffs, a [371 Solder Station](#) can be added for increased versatility.

Vacuum Base PanaVise - Model 381



- The 381 Vacuum Base PanaVise is a combination of the [380 Vacuum Base](#) and the [303 Standard Head](#).
- A half turn of the mount lever attaches or releases the powerful suction pad and allows rapid set-ups in a variety of locations (for use on smooth, non-porous surfaces only).
- This combination stands 6 1/8" (155.6mm) tall and weighs 2lbs. 13oz. (1.3kgs).

Micrometer Stand PanaVise - Model 391



- Micrometer Holder gently, yet firmly holds micrometers of all sizes.
- Neoprene pads open 1/2" (12.7mm).
- [305 Low-Profile Base](#) keeps micrometer close to work surface and out of the way.
- Base features a 4 5/16" (109.5mm) bolt circle countersunk for three 1/4" (6.3mm) flathead bolts (not included)
- Overall height 4.3" (109.2mm). Weight 1.6lbs (.7kgs)

Wide Opening Head PanaVise - Model 396



- The versatility of the PanaVise product line is evident in this combination: it's simply the [366 Wide Opening Head](#) with the [300 Standard Base](#). This provides a wide gripping head with the full "tilt, turn and rotate" capabilities of the split ball (found in every 300 and 400 series base)

- The 396 Wide Opening Head PanaVise stands 7 5/16" (185.7mm) tall and weighs 3lbs. (1.4kgs).



| [Vises](#) | [Pana Press](#) | [CCTV](#) | [Cellular](#) | [Speaker Mounts](#) | [Sales Reps](#) | [International](#) | [Trade Shows](#) | [History](#) | [Downloads](#) | [Purchase Spares](#) | [Site Map](#) | [Product Search](#) | [Request Catalog](#) | [Contact PanaVise](#) | [Home](#) |

Web Development - Flash, Graphics and Java Scripting by [Global Studio](#)

Send technical questions to info@globalstudio.com

Send questions about Site Content and about PanaVise Products to webmaster@panavise.com

Copyright 1996 - 2006 by PanaVise Products, Inc.

TOP OF PAGE