



## SET SCREW COUPLINGS - RC-SERIES

Bore Inch	BLACK OXIDE WITHOUT KEYWAY				BLACK OXIDE WITH KEYWAY		
	Climax	Ruland	Boston	Lovejoy	Climax	Ruland	Lovejoy
1/4	RC-025	SCX-4-4-F	CR4	SC-250			
5/16	RC-031		CR5	SC-312			
3/8	RC-037	SCX-6-6-F	CR6	SC-375	RC-037-KW	SCC-6-6-F	
1/2	RC-050	SCX-8-8-F	CR8		RC-050-KW	SCC-8-8-F	SC-500
5/8	RC-062	SCX-10-10-F	CR10		RC-062-KW	SCC-10-10-F	SC-625
3/4	RC-075	SCX-12-12-F	CR12		RC-075-KW	SCC-12-12-F	SC-750
7/8	RC-087	SCX-14-14-F	CR14		RC-087-KW	SCC-14-14-F	SC-875
1	RC-100	SCX-16-16-F	CR16		RC-100-KW	SCC-16-16-F	SC-1000
1 1/8	RC-112	SCX-18-18-F			RC-112-KW	SCC-18-18-F	SC-1125
1 1/4	RC-125	SCX-20-20-F	CR20		RC-125-KW	SCC-20-20-F	SC-1250
1 3/8	RC-137	SCX-22-22-F			RC-137-KW	SCC-22-22-F	SC-1375
1 1/2	RC-150	SCX-24-24-F			RC-150-KW	SCC-24-24-F	
1 3/4					RC-175-KW	SCC-28-28-F	
2					RC-200-KW	SCC-32-32-F	

## STAINLESS STEEL

## ALUMINUM

Bore Inch	WITHOUT KEYWAY		WITH KEYWAY		WITHOUT KEYWAY	
	Climax	Ruland	Climax	Ruland	Climax	
1/4	RC-025-S	SCX-4-4-SS			RC-025-A	Aluminum is Climax Unique
5/16	RC-031-S				RC-031-A	
3/8	RC-037-S	SCX-6-6-SS	RC-037-S-KW	SCC-6-6-SS	RC-037-A	
1/2	RC-050-S	SCX-8-8-SS	RC-050-S-KW	SCC-8-8-SS	RC-050-A	
5/8	RC-062-S	SCX-10-10-SS	RC-062-S-KW	SCC-10-10-SS	RC-062-A	
3/4	RC-075-S	SCX-12-12-SS	RC-075-S-KW	SCC-12-12-SS	RC-075-A	
7/8	RC-087-S	SCX-14-14-SS	RC-087-S-KW	SCC-14-14-SS	RC-087-A	
1	RC-100-S	SCX-16-16-SS	RC-100-S-KW	SCC-16-16-SS	RC-100-A	
1 1/4	RC-125-S	SCX-20-20-SS	RC-125-S-KW	SCC-20-20-SS	RC-125-A	

## METRIC SET SCREW COUPLINGS - MRC-SERIES

### BLACK OXIDE

### STAINLESS STEEL

Bore Size	WITHOUT KEYWAY		WITH KEYWAY		WITHOUT KEYWAY		WITH KEYWAY	
	Climax	Ruland	Climax	Ruland	Climax	Ruland	Climax	Ruland
10	MRC-10	MSCX-10-10-F	MRC-10-KW	MSCC-10-10-F	MRC-10-S	MSCX-10-10-SS	MRC-10-S-KW	MSCC-10-10-SS
12	MRC-12	MSCX-12-12-F	MRC-12-KW	MSCC-12-12-F	MRC-12-S	MSCX-12-12-SS	MRC-12-S-KW	MSCC-12-12-SS
15	MRC-15	MSCX-15-15-F	MRC-15-KW	MSCC-15-15-F	MRC-15-S	MSCX-15-15-SS	MRC-15-S-KW	MSCC-15-15-SS
20	MRC-20	MSCX-20-20-F	MRC-20-KW	MSCC-20-20-F	MRC-20-S	MSCX-20-20-SS	MRC-20-S-KW	MSCC-20-20-SS
25	MRC-25	MSCX-25-25-F	MRC-25-KW	MSCC-25-25-F	MRC-25-S	MSCX-25-25-SS	MRC-25-S-KW	MSCC-25-25-SS
30	MRC-30	MSCX-30-30-F	MRC-30-KW	MSCC-30-30-F	MRC-30-S	MSCX-30-30-SS	MRC-30-S-KW	MSCC-30-30-SS
35	MRC-35	MSCX-35-35-F	MRC-35-KW	MSCC-35-35-F	MRC-35-S	MSCX-35-35-SS	MRC-35-S-KW	MSCC-35-35-SS
40	MRC-40	MSCX-40-40-F	MRC-40-KW	MSCC-40-40-F	MRC-40-S	MSCX-40-40-SS	MRC-40-S-KW	MSCC-40-40-SS