



TOP

## ECP-1 ELECTRONICS EDUCATIONAL KIT

BOTTOM



- A - Photo resistors X 2 PCS
- B - 3A Automotive Fuse X 3 PCS
- C - Pushbutton SPST off-(on) X 1 PCS
- D - DPDT Non LATCHING Relay 12VDC X 2 PCS
- E - LED RGB 5mm X 2 PCS (Slow Flash)
- F - LED Green 5mm X 5 PCS
- G - LED Green 3mm X 5 PCS
- H - LED Red 5mm X 5 PCS
- I - LED Red 3mm X 5 PCS
- J - Transistor 2N6027 DIP TO-92 X 4 PCS
- K - NPN Transistor 2N2222 DIP TO-92 X 4 PCS
- L - Capacitors Ceramic 0.047uF X 4 PCS
- M - Capacitors Electrolytic 2.2uF/50V 105°C X 2 PCS
- N - Capacitors Electrolytic 22uF /50V 105°C X 1 PCS
- O - Capacitors Electrolytic 1000uF/25V 105°C X 2 PCS
- P - • Resistors 100R X 10 PCS
  - Resistors 180R X 10 PCS
  - Resistors 220R X 10 PCS
  - Resistors 470R X 10 PCS
  - Resistors 680R X 10 PCS
- Q - • Resistors 1K X 10 PCS
  - Resistors 2K X 10 PCS
  - Resistors 10K X 10 PCS
  - Resistors 15K X 10 PCS
  - Resistors 27K X 10 PCS
  - Resistors 33K X 10 PCS
  - Resistors 51K X 10 PCS
  - Resistors 100K X 10 PCS
  - Resistors 470K X 10 PCS

- A - Potentiometer 1M Linear X 1 PCS
- B - Potentiometer 2K Linear X 2 PCS
- C - DPDT Toggle Switches X 2 PCS
- D - Hookup Wire 22AWG ,25ft Red X 1 PCS
- E - Hookup Wire 22AWG ,25ft Black X 1 PCS
- F - Hookup Wire 22AWG ,25ft Green X 1 PCS
- G - Jumper Wires W/ Alligator Clips Attached X 1 PCS
- H - Loudspeaker 2" ,0.5W , 8 ohm X 1 PCS
- I - UNIVERSAL 7 OUTPUT AC/DC ADAPTER 500mA, I/P:110VAC X 1 PCS
- J - Red&Black Alligator Clips X 10 PCS
- K - 9V Battery Snap and Case X 1 PCS
- L - Single AA Battery Holder X 1 PCS
- M - Four AA Battery Holder X 1 PCS
- N - SOLDERLESS BREADBOARD 2 STRIPS, 1 DISTRIBUTION with Wire Kit JUMPER WIRE SET 70PCS X 1 PCS
- O - AA 1.5V Alkaline Battery X 6 PCS
- P - 9V Battery Alkaline Battery X 1 PCS