

Distributed by:

**JAMECO**<sup>®</sup>  
ELECTRONICS

**www.Jameco.com ♦ 1-800-831-4242**

The content and copyrights of the attached  
material are the property of its owner.

Jameco Part Number 216223

# Battery Holder

BH Series




For Six "AA" Cells

**BH-363A**  
 Lead wire (150mm)  
 Strip & Tin: 5mm+/-1mm  
 UL1007, AWG#26

**BH-363B**  
 Four-prong or six-prong snap terminal

**BH-363D**  
 With TAG (Solder, LUG) Terminal




For one "AA" Cell

**BH-311-2A**  
 Lead wire (150mm)  
 Strip & Tin: 5mm+/-1mm  
 UL1007, AWG#26

**BH-311-2D**  
 With TAG (Solder, LUG) Terminal

**BH-311-2P**  
 With Pin (PC Mounted)




For two "AA" Cells

**BH-321-2A**  
 Lead wire (150mm)  
 Strip & Tin: 5mm+/-1mm  
 UL1007, AWG#26

**BH-321-2AS**  
 Lead wire (150mm)  
 Strip & Tin: 5mm+/-1mm  
 UL1007, AWG#26  
 With Switch

**BH-321-2D**  
 With TAG (Solder, LUG) Terminal

**BH-321-2P**  
 With Pin (PC Mounted)




For two "AA" Cells

**BH-321-4A**  
 Lead wire (150mm)  
 Strip & Tin: 5mm+/-1mm  
 UL1007, AWG#26

**BH-321-4B**  
 Four-prong or six-prong snap terminal

**BH-321-4D**  
 With TAG (Solder, LUG) Terminal

**BH-321-4P**  
 With Pin (PC Mounted)



Sinotech Shanghai  
 Room 1404 1759 North Zhongshan Road, Putuo District,  
 Shanghai, China




For four "AA" Cells

**BH-341-2A**  
 Lead wire (150mm)  
 Strip & Tin: 5mm+/-1mm  
 UL1007, AWG#26

**BH-341-2B**  
 Four-prong or six-prong snap terminal

**BH-341-2D**  
 With TAG (Solder, LUG) Terminal

**BH-341-2P**  
 With Pin (PC Mounted)




For three "AA" Cells

**BH-331-A**  
 Lead wire (150mm)  
 Strip & Tin: 5mm+/-1mm  
 UL1007, AWG#26

**BH-331-B**  
 Four-prong or six-prong snap terminal

**BH-331-D**  
 With TAG (Solder, LUG) Terminal

**BH-331-P**  
 With Pin (PC Mounted)




For four "AA" Cells

**BH-343-1A**  
 Lead wire (150mm)  
 Strip & Tin: 5mm+/-1mm  
 UL1007, AWG#26

**BH-343-1B**  
 Four-prong or six-prong snap terminal


**BH-343-1D**  
 With TAG (Solder, LUG) Terminal



For six "AA" Cells

**BH-364-A**  
 Lead wire (150mm)  
 Strip & Tin: 5mm+/-1mm  
 UL1007, AWG#26

**BH-364-D**  
 With TAG (Solder, LUG) Terminal




# Battery Holder

BH Series



**BH-382-A**  
Lead wire (150mm)  
Strip & Tin: 5mm+/-1mm  
UL1007, AWG#26




**BH-382-B**  
Four-prong or six-prong snap terminal

**BH-382-D**  
With TAG (Solder, LUG) Terminal

For eight "AA" Cells



**BH-383-A**  
Lead wire (150mm)  
Strip & Tin: 5mm+/-1mm  
UL1007, AWG#26




**BH-383-B**  
Four-prong or six-prong snap terminal

**BH-383-D**  
With TAG (Solder, LUG) Terminal

For eight "AA" Cells



**BH-421-1A**  
Lead wire (150mm)  
Strip & Tin: 5mm+/-1mm  
UL1007, AWG#26



**BH-421-1B**  
Four-prong or six-prong snap terminal


**BH-421-1D**  
With TAG (Solder, LUG) Terminal

For two "AA" Cells

**BH-421-1P**  
With Pin (PC Mounted)



**BH431-1A**  
With lead wires 150mm  
Strip & Tin: 5mm+/-1mm  
UL1007, AWG#26



**BH431-1B**  
With 4prong or 6prongsnap terminal

**BH431-1D**  
With TAG(Solder,LUG)Terminal

For Three "AAA"Cells

**BH431-1P**  
With Pin(PC Mounted)

# Battery Holder


BH Series



BH9VA  
With lead wires 150mm  
Strip & Tin: 5mm +/- 1mm  
UL1007, AWG#26

BH9VD  
With TAG (Solder, LUG) Terminal

BH9VP  
With Pin (PC Mounted)



FOR 9V CELL